

FEATURES**2-input and 2-output crosspoint HDMI transceiver****8k30 RGB/YCbCr 4:4:4 or 4k120 RGB/YCbCr 4:4:4 10-bit video support****8k60 YCbCr 4:2:0 10-bit video support****HDMI receivers****Up to 40 Gbps FRL support****Up to 18 Gbps TMDS video support****eARC transmitter****EDID access in low power standby mode****EDID SRAM managed by internal MCU host processor****Fast switching between ports****HDMI transmitters****Up to 40 Gbps FRL support****Up to 18 Gbps TMDS video support****eARC receiver****HDCP****HDCP 1.4, HDCP 2.2, and HDCP 2.3 support****Independent HDCP on each transmitter and receiver port****Fully integrated HDCP 1.4, HDCP 2.2, and HDCP 2.3 repeater modes****On-chip key storage in OTP****Audio****2 independently configurable audio ports****8-channel, 192 kHz, 24-bit PCM audio support****24.576 Mb IEC61937 compressed audio support****eARC receiver or transmitter with multichannel PCM, HBR audio, and ARC support****Video****Crosspoint matrix switch, video mirror, video split, and video merge modes****FRL to TMDS and TMDS to FRL modes conversion****Variable refresh rate (VRR), fast vactive (FVA), and auto low latency mode (ALLM) support****Dual path color space conversion****Dynamic HDR passthrough support including HDMI dynamic HDR metadata, HDR10+, and Dolby Vision™****DSC 1.2a passthrough****Video test pattern generator****APPLICATIONS****TV****Home theater****Industrial switching****GENERAL DESCRIPTION**

The ADV7672 is a High-Definition Multimedia Interface (HDMI®) transceiver with crosspoint matrix switch, video mirror, video split, and video merge capabilities.

The ADV7672 supports 40 Gbps fixed rate link (FRL) and 18 Gbps transition minimized differential signaling (TMDS) video rates and provides two independent HDMI receiver ports, two independent HDMI transmitter ports, two audio ports, and an enhanced audio return channel (eARC) interface.

Each HDMI receiver and transmitter supports 8k30 RGB/YCbCr 4:4:4 10-bit video, 8k60 YCbCr 4:2:0 10-bit high definition video, and 4k120 4:4:4 10-bit high frame rate video.

Each audio port can be independently configured as either an audio extraction or audio insertion port. The audio ports support 8-channel, 192 kHz, 24-bit pulse coded modulation (PCM) and compressed audio formats including high bitrate formats.

The eARC interface can be configured as either an eARC transmitter or an eARC receiver. The eARC interface supports 8-channel 192 kHz PCM audio and high bit rate audio (HBR) compressed audio formats including Dolby TrueHD™ and DTS-HD™. Audio return channel (ARC) is also supported on the eARC interface.

The ADV7672 supports display stream compression (DSC) 1.2a data passthrough and high dynamic range (HDR) metadata passthrough for HDMI dynamic HDR, HDR10+, and Dolby Vision™.

The ADV7672 implements the High-bandwidth Digital Content Protection (HDCP) 2.3 specification to protect the delivery of premium content. HDCP 2.3 is applied in transmitter, receiver, and repeater configurations. HDCP 2.3 is backwards compatible with HDCP 2.2. HDCP 1.4 is also supported to provide interoperability with legacy devices.

The ADV7672 is configured via I²C using a high level host controller interface (API).

The ADV7672 is provided in a 108-lead, lead frame chip scale package (LFCSP) with an exposed paddle and is specified over a 0°C to 70°C temperature range.

Customers that wish to sample or purchase the ADV7672 must be licensed HDMI 2.1 adopters listed at HDMI.org and licensed HDCP 2.x adopters listed at Digital-CP.com.

For more information about the [ADV7672](#), contact your local Analog Devices, Inc., sales office at www.analog.com/sales.

Rev. SPrB

[Document Feedback](#)

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A.
Tel: 781.329.4700 ©2020 Analog Devices, Inc. All rights reserved.
[Technical Support](#) www.analog.com

NOTES

¹I²C refers to a communications protocol originally developed by Phillips Semiconductors (now NXP Semiconductors).

²HDMI, the HDMI Logo, and High-Definition Multimedia Interface are trademarks or registered trademarks of HDMI Licensing Administrator, Inc., in the United States and other countries.