

PRODUCT RELIABILITY REPORT
FOR

DS17285, -3 & -5, Rev A2

Dallas Semiconductor

4401 South Beltwood Parkway
Dallas, TX 75244-3292

Prepared by:

Ken Wendel

Ken Wendel
Reliability Engineering Manager
Dallas Semiconductor
4401 South Beltwood Pkwy.
Dallas, TX 75244-3292
Email : ken.wendel@dalsemi.com
ph: 972-371-3726
fax: 972-371-6016
mbl: 214-435-6610

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Dallas Semiconductor products:

DS17285, -3 & -5, Rev A2

In addition, Dallas Semiconductor's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maxim-ic.com/TechSupport/dsreliability.html>.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at http://dbserv.maxim-ic.com/l_datasheet3.cfm.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$$

AfT = Acceleration factor due to Temperature
tu = Time at use temperature (e.g. 55°C)
ts = Time at stress temperature (e.g. 125°C)
k = Boltzmann's Constant (8.617 x 10⁻⁵ eV/°K)
Tu = Temperature at Use (°K)
Ts = Temperature at Stress (°K)
Ea = Activation Energy (e.g. 0.7 eV)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7eV will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$$AfV = \exp(B * (Vs - Vu))$$

AfV = Acceleration factor due to Voltage
Vs = Stress Voltage (e.g. 7.0 volts)
Vu = Maximum Operating Voltage (e.g. 5.5 volts)
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$$Fr = X / (ts * AfV * AfT * N * 2)$$

X = Chi-Sq statistical upper limit
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$MTTF = 1/Fr$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

FAILURE RATE: **MTTF (YRS): 29401** **FITS: 3.9**

The parameters used to calculate this failure rate are as follows:

Cf: 60% **Ea: 0.7** **B: 0** **Tu: 25 °C** **Vu: 5.5 Volts**

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data.

Device Information:

Process: D8N-1P2M,LLVt,ND cap LOCOS:GOI
 Passivation: Laser/TEOS Ox - Pass/Nit -SRAM LaserPrb
 Die Size: 197 x 156
 Number of Transistors: 139000
 Interconnect: Aluminum / 1% Silicon / 0.5% Copper
 Gate Oxide Thickness: 175 Å

OPERATING LIFE

DESCRIPTION	DATE	CODE	CONDITION	READPOINT	QTY	FAILS	FA#
HIGH VOLTAGE LIFE	9921		125C, 7.0 VOLTS	1000 HRS	116	0	
HIGH VOLTAGE LIFE	9924		125C, 7.0 VOLTS	1000 HRS	116	1	990165
HIGH VOLTAGE LIFE	9926		125C, 5.5 VOLTS	1000 HRS	144	0	
HIGH VOLTAGE LIFE	0011		125C, 7.0 VOLTS	1000 HRS	116	1	No FA
HIGH VOLTAGE LIFE	0034		125C, 7.0 VOLTS	1000 HRS	116	0	
HIGH VOLTAGE LIFE	0223		125C, 7.0 VOLTS	1000 HRS	80	0	
HIGH VOLTAGE LIFE	0223		125C, 7.0 VOLTS	1000 HRS	160	0	
				Total:		2	

FAILURE RATE: **MTTF (YRS): 29401** **FITS: 3.9**