

10MHz, 6V/ μ s, Dual Rail-to-Rail Input and Output Precision C-Load Op Amp

DESCRIPTION

The **RH1498M** is a dual, rail-to-rail input and output precision C-Load™ op amp with a 10MHz gain-bandwidth product and a 6V/ μ s slew rate.

The RH1498 is designed to maximize input dynamic range by delivering precision performance over the full supply voltage. Using a patented technique, the input stages of the RH1498 are trimmed, one at the negative supply and the other at the positive supply. The resulting guaranteed common mode rejection is much better than other rail-to-rail input op amps. When used as a unity-gain buffer in front of single supply 12-bit A-to-D converters, the RH1498 is guaranteed to add less than 1LSB of error even in single 5V supply systems.

With 110dB of supply rejection, the RH1498 maintains its performance over a supply range of 4.5V to 36V. The inputs can be driven beyond the supplies without damage or phase reversal of the output. These op amps remain stable while driving capacitive loads up to 10,000pF.


The wafer lots are processed to Linear Technology's in-house Class S flow to yield circuits usable in stringent military and space applications.

ABSOLUTE MAXIMUM RATINGS

(Note 1)

Total Supply Voltage (V^+ to V^-)	36V
Input Current.....	$\pm 10\text{mA}$
Output Short-Circuit Duration (Note 2)	Continuous
Operating Temperature Range.....	-55°C to 125°C
Specified Temperature Range	-55°C to 125°C
Junction Temperature	150°C
Storage Temperature Range.....	-65°C to 150°C
Lead Temperature (Soldering, 10 sec)	300°C

BURN-IN CIRCUIT



PACKAGE INFORMATION




TABLE 1: ELECTRICAL CHARACTERISTICS(Preirradiation) $V_S = \pm 15V$, $V_{CM} = V_{OUT} = 0V$, unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS	NOTES	$T_A = 25^\circ C$			SUB-GROUP	$-55^\circ C \leq T_A \leq 125^\circ C$			SUB-GROUP	UNITS
				MIN	TYP	MAX		MIN	TYP	MAX		
V_{OS}	Input Offset Voltage	$V_{CM} = V^+, V^-$ $V_{CM} = 14.5V, -14.5V$			200	800	1		350	1100	2, 3	μV μV
	Input Offset Voltage Match (Channel-to-Channel) (Note 3)	$V_{CM} = V^+ \text{ to } V^-$ $V_{CM} = 14.5V \text{ to } -14.5V$	3		250	1400			450	1800		μV μV
I_B	Input Bias Current	$V_{CM} = V^+$ $V_{CM} = 14.5V$ $V_{CM} = V^-$ $V_{CM} = -14.5V$		0 -715	250 -250	715 0	1		500 -500	1200 0	2, 3	nA nA nA nA
	Input Bias Current Match (Channel-to-Channel) (Note 3)	$V_{CM} = V^+, V^-$ $V_{CM} = 14.5V, -14.5V$	3	0	12	200			50	400		nA nA
I_{OS}	Input Offset Current	$V_{CM} = V^+, V^-$ $V_{CM} = 14.5V, -14.5V$			6	70	1		40	300	2, 3	nA nA
	Input Voltage Range			-15		15		-14.5		14.5		V
	Input Noise Voltage	0.1Hz to 10Hz			400							nV _{p-p}
e_n	Input Noise Voltage Density	$f = 1kHz$			12							nV/ $\sqrt{Hz}$
i_n	Input Noise Current Density	$f = 1kHz$			0.3							pA/ $\sqrt{Hz}$
A_{VOL}	Large-Signal Voltage Gain	$V_O = -14.5V \text{ to } 14.5V$, $R_L = 10k$ $V_O = -10V \text{ to } 10V$, $R_L = 2k$		1000 500	5200 2300		4	60 25	400 100		5, 6	V/mV V/mV
$CMRR$	Common Mode Rejection Ratio	$V_{CM} = V^+ \text{ to } V^-$ $V_{CM} = 14.5V \text{ to } -14.5V$		90	102		1	86	102		2, 3	dB dB
	CMRR Match (Channel-to-Channel) (Note 3)	$V_{CM} = V^+ \text{ to } V^-$ $V_{CM} = 14.5V \text{ to } -14.5V$	3	84	103			80	100			dB dB
$PSRR$	Power Supply Rejection Ratio	$V_S = \pm 2V \text{ to } \pm 16V$		90	110		1	88			2, 3	dB
	PSRR Match (Channel-to-Channel) (Note 3)	$V_S = \pm 2V \text{ to } \pm 16V$	3	83	110			82	100			dB
V_{OL}	Output Voltage Swing (Low) (Note 4)	No Load $I_{SINK} = 1mA$ $I_{SINK} = 10mA$ $I_{SINK} = 5mA$	4		18 50 230	30 100 500	4	25 70 180	75 150 500		5, 6	mV mV mV mV
V_{OH}	Output Voltage Swing (High) (Note 4)	No Load $I_{SOURCE} = 1mA$ $I_{SOURCE} = 10mA$ $I_{SOURCE} = 5mA$	4		2.5 75 420	10 150 800	4	5 100 300	25 250 800		5, 6	mV mV mV mV
I_{SC}	Short-Circuit Current			± 15	± 30		1	± 7.5	± 12		2, 3	mA
I_S	Supply Current per Amp				1.8	2.5	1		2.2	3	2, 3	mA
GBW	Gain-Bandwidth Product	$f = 100kHz$		6.8	10.5			5.8	8.5			MHz
SR	Slew Rate	$A_V = -1$, $R_L = 10k$, $V_O = \pm 10V$, Measure at $V_O = \pm 5V$		3.5	6		4	2.2	4		5, 6	V/ μs

TABLE 1A: ELECTRICAL CHARACTERISTICS(Postirradiation) $V_S = \pm 15V$, $V_{CM} = 0V$, $T_A = 25^\circ C$, unless otherwise noted. (Note 5)

SYMBOL	PARAMETER	CONDITIONS	NOTES	10-Krad(Si)		20Krad(Si)		50Krad(Si)		100Krad(Si)		200Krad(Si)		UNITS
				MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
V_{OS}	Input Offset Voltage	$V_{CM} = V^+, V^-$			950		950		950		950		950	μV
I_B	Input Bias Current	$V_{CM} = V^+, V^-$			765		815		865		915		965	nA
I_{OS}	Input Offset Current	$V_{CM} = V^+, V^-$			100		100		100		100		100	nA
	Input Voltage Range			V^-	V^+	V^-	V^+	V^-	V^+	V^-	V^+	V^-	V^+	V
A_{VOL}	Large-Signal Voltage Gain	$V_O = -14.5V$ to $14.5V$, $R_L = 10k$		500		500		500		500		500		V/mV
		$V_O = -10V$ to $10V$, $R_L = 2k$		250		250		250		250		250		V/mV
CMRR	Common Mode Rejection Ratio	$V_{CM} = V^+$ to V^-		86		86		86		86		86		dB
	CMRR Match (Channel-to-Channel)	$V_{CM} = V^+$ to V^-	3	83		83		83		83		83		dB
PSRR	Power Supply Rejection Ratio	$V_S = \pm 2V$ to $\pm 16V$		90		90		90		90		90		dB
	PSRR Match (Channel-to-Channel)	$V_S = \pm 2V$ to $\pm 16V$	3	83		83		83		83		83		dB
V_{OUT}	Output Voltage Swing Low	No Load	4	60		60		60		60		60		mV
		$I_{SINK} = 1mA$		100		100		100		100		100		mV
		$I_{SINK} = 10mA$		500		500		500		500		500		mV
	Output Voltage Swing High	No Load	4	20		20		20		20		20		mV
		$I_{SOURCE} = 1mA$		150		150		150		150		150		mV
		$I_{SOURCE} = 10mA$		800		800		800		800		800		mV
I_{SC}	Short-Circuit Current			± 10		± 10		± 10		± 10		± 10		mA
I_S	Supply Current			2.5		2.5		2.5		2.5		2.5		mA
GBW	Gain-Bandwidth Product	$f = 100kHz$		4.5		4.5		4.5		4.5		4.5		MHz
SR	Slew Rate	$A_V = -1$, $R_L = 10k$, $V_O = \pm 10V$, Measure at $V_O = \pm 5V$		3		3		3		3		3		V/ μs

TABLE 2: ELECTRICAL CHARACTERISTICS(Preirradiation) $V_S = 5V$; $V_{CM} = V_{OUT} =$ half supply, unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS	NOTES	$T_A = 25^\circ C$			SUB-GROUP	$-55^\circ C \leq T_A \leq 125^\circ C$			SUB-GROUP	UNITS
				MIN	TYP	MAX		MIN	TYP	MAX		
V_{OS}	Input Offset Voltage	$V_{CM} = V^+, V^-$ $V_{CM} = V^+ - 0.5V, V^- + 0.5V$			150	800	1		300	1100	2, 3	μV μV
	Input Offset Voltage Match (Channel-to-Channel) (Note 3)	$V_{CM} = V^+$ to V^- $V_{CM} = V^+ - 0.5V, V^- + 0.5V$	3		200	1400			350	1800		μV μV
I_B	Input Bias Current	$V_{CM} = V^+$		0	250	650	1				2, 3	nA
		$V_{CM} = V^+ - 0.5V$						0	450	1100		nA
		$V_{CM} = V^-$		-650	-250	0		-1100	-450	0		nA
		$V_{CM} = V^- + 0.5V$										nA
	Input Bias Current Match (Channel-to-Channel) (Note 3)	$V_{CM} = V^+, V^-$ $V_{CM} = V^+ - 0.5V, V^- + 0.5V$	3	0	10	180		0	30	400		nA nA
I_{OS}	Input Offset Current	$V_{CM} = V^+, V^-$ $V_{CM} = V^+ - 0.5V, V^- + 0.5V$			5	65	1		15	300	2, 3	nA nA

TABLE 2: ELECTRICAL CHARACTERISTICS(Preirradiation) $V_S = 5V$; $V_{CM} = V_{OUT} = \text{half supply}$, unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS	NOTES	$T_A = 25^\circ\text{C}$			SUB-GROUP	$-55^\circ\text{C} \leq T_A \leq 125^\circ\text{C}$			SUB-GROUP	UNITS
				MIN	TYP	MAX		MIN	TYP	MAX		
	Input Voltage Range			V^-		V^+		$V^- + 0.5V$		$V^+ - 0.5V$		V
	Input Noise Voltage	0.1Hz to 10Hz			400							nV _{P-P}
e_n	Input Noise Voltage Density	$f = 1\text{kHz}$			12							nV/ $\sqrt{\text{Hz}}$
i_n	Input Noise Current Density	$f = 1\text{kHz}$			0.3							pA/ $\sqrt{\text{Hz}}$
C_{IN}	Input Capacitance				5							pF
A_{VOL}	Large-Signal Voltage Gain	$V_S = 5V$, $V_O = 75\text{mV}$ to $4.8V$, $R_L = 10k$		600	3800		4	60	210		5, 6	V/mV
CMRR	Common Mode Rejection Ratio	$V_S = 5V$, $V_{CM} = V^+$ to V^- $V_S = 5V$, $V_{CM} = 0.5V$ to $4.5V$		76	90			68	85			dB dB
	CMRR Match (Channel-to-Channel) (Note 3)	$V_S = 5V$, $V_{CM} = V^+$ to V^- $V_S = 5V$, $V_{CM} = 0.5V$ to $4.5V$	3	75	91			66				dB dB
PSRR	Power Supply Rejection Ratio	$V_S = 4.5V$ to $12V$, $V_{CM} = V_O = 0.5V$		88	105		1	86	104		2, 3	dB
	PSRR Match (Channel-to-Channel) (Note 3)	$V_S = 4.5V$ to $12V$, $V_{CM} = V_O = 0.5V$	3	82	120			80	118			dB
V_{OL}	Output Voltage Swing (Low) (Note 4)	No Load $I_{SINK} = 1\text{mA}$ $I_{SINK} = 2.5\text{mA}$	4		14	30	4		25	75	5, 6	mV
					50	100			65	150		mV
					90	200			110	220		mV
V_{OH}	Output Voltage Swing (High) (Note 4)	No Load $I_{SOURCE} = 1\text{mA}$ $I_{SOURCE} = 2.5\text{mA}$	4		2.5	10	4		5	25	5, 6	mV
					70	150			100	250		mV
					140	250			180	300		mV
I_{SC}	Short-Circuit Current	$V_S = 5V$		± 12.5	24		1	± 5	± 10		2, 3	mA
I_S	Supply Current per Amp				1.7	2.2	1		2	2.7	2, 3	mA
GBW	Gain-Bandwidth Product	$V_S = 5V$, $f = 100\text{kHz}$		6.8	10.5			5.8	8.5			MHz
SR	Slew Rate	$V_S = \pm 2.5V$, $A_V = -1$, $R_L = 10k$, $V_O = \pm 2V$, Measure at $V_O = \pm 1V$		2.6	4.5		4	2	3.6		5, 6	V/ μs

TABLE 2A: ELECTRICAL CHARACTERISTICS(Postirradiation) $V_S = 5V$; $V_{CM} = \text{half supply}$, $T_A = 25^\circ\text{C}$, unless otherwise noted. (Note 5)

SYMBOL	PARAMETER	CONDITIONS	NOTES	10Krad(Si)		20Krad(Si)		50Krad(Si)		100Krad(Si)		200Krad(Si)		UNITS
				MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
V_{OS}	Input Offset Voltage	$V_{CM} = V^+$, V^-			950		950		950		950		950	μV
I_B	Input Bias Current	$V_{CM} = V^+$, V^-			700		750		800		850		900	nA
I_{OS}	Input Offset Current	$V_{CM} = V^+$, V^-			65		65		65		65		65	nA
	Input Voltage Range			V^-	V^+	V^-	V^+	V^-	V^+	V^-	V^+	V^-	V^+	V
A_{VOL}	Large-Signal Voltage Gain	$V_O = 75\text{mV}$ to $V^+ - 0.2V$ $R_L = 10k$		300		300		300		300		300		V/mV
CMRR	Common Mode Rejection Ratio	$V_{CM} = V^+$ to V^-		70		70		70		70		70		dB
	CMRR Match (Channel-to-Channel)	$V_{CM} = V^+$ to V^-	3	70		70		70		70		70		dB
PSRR	Power Supply Rejection Ratio	$V_S = 4.5V$ to $12V$, $V_{CM} = V_O = 0.5V$		88		88		88		88		88		dB

TABLE 2A: ELECTRICAL CHARACTERISTICS(Postirradiation) $V_S = 5V$; $V_{CM} = \text{half supply}$, $T_A = 25^\circ\text{C}$, unless otherwise noted. (Note 5)

SYMBOL	PARAMETER	CONDITIONS	NOTES	10Krad(Si)		20Krad(Si)		50Krad(Si)		100Krad(Si)		200Krad(Si)		UNITS
				MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
	PSRR Match (Channel-to-Channel)	$V_S = 4.5V$ to $12V$, $V_{CM} = V_O = 0.5V$	3	82		82		82		82		82		dB
V_{OUT}	Output Voltage Swing Low	No Load $I_{SINK} = 1mA$ $I_{SINK} = 2.5mA$	4		60		60		60		60		60	mV
					100		100		100		100		100	mV
					200		200		200		200		200	mV
	Output Voltage Swing High	No Load $I_{SOURCE} = 1mA$ $I_{SOURCE} = 2.5mA$	4		20		20		20		20		20	mV
					150		150		150		150		150	mV
					250		250		250		250		250	mV
I_{SC}	Short-Circuit Current			± 8		± 8		± 8		± 8		± 8		mA
I_S	Supply Current				2.2		2.2		2.2		2.2		2.2	mA
SR	Slew Rate	$V_S = \pm 2.5V$, $A_V = -1$, $R_L = 10k$, $V_O = \pm 2V$, Measure at $V_O = \pm 1V$		2		2		2		2		2		V/ μs

Note 1: Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. Exposure to any Absolute Maximum Rating condition for extended periods may affect device reliability and lifetime.

Note 2: A heat sink may be required to keep the junction temperature below this absolute maximum rating when the output is shorted indefinitely.

Note 3: Matching parameters are the difference between amplifiers A and B.

Note 4: Output voltage swings are measured between the output and power supply rails.

Note 5: Device is characterized at 10Krad, 20Krad, 50Krad, 100Krad and 200Krad and is production tested at 100Krad only.

TABLE 2: ELECTRICAL TEST REQUIREMENTS


MIL-PRF-38535 TEST REQUIREMENTS	SUBGROUP
Final Electrical Test Requirements	1*,2,3,4,5,6
Group A Test Requirement	1,2,3,4,5,6
Group C End-Point Electrical Characteristics	1,2,3
Group D End-Point Electrical Characteristics	1,2,3
Group E End-Point Electrical Characteristics	1

*PDA applies to subgroup 1. See PDA Test Notes.

PDA Test Notes

The PDA is specified as 5% based on failures from group A, subgroup 1, tests after cooldown as the final electrical test in accordance with method 5004 of MIL-STD-883. The verified failures of group A, subgroup 1, after burn-in divided by the total number of devices submitted for burn-in in that lot shall be used to determine the percent for the lot.


Linear Technology Corporation reserves the right to test to tighter limits than those given.

TOTAL DOSE BIAS CIRCUIT

RH1498 TC


TYPICAL PERFORMANCE CHARACTERISTICS

Large-Signal Voltage Gain




RH1498 G01

Large-Signal Voltage Gain




RH1498 G02

Slew Rate




RH1498 G03

Supply Current per Amp




RH1498 G04

Input Offset Voltage




RH1498 G05

Input Offset Current




RH1498 G06

Input Bias Current




RH1498 G07

Common Mode Rejection Ratio



RH1498 G08


Power Supply Rejection Ratio



RH1498 G09


TYPICAL PERFORMANCE CHARACTERISTICS

Supply Current vs Supply Voltage




RH1498 G10

Supply Current vs Temperature




RH1498 G11

Input Bias Current vs Common Mode Voltage




RH1498 G12

Open-Loop Voltage Gain vs Temperature




RH1498 G13

Input Bias Current vs Temperature




RH1498 G14

Output Saturation Voltage vs Load Current (Output High)




RH1498 G15

Output Saturation Voltage vs Load Current (Output Low)



RH1498 G16

PACKAGE OUTLINE DRAWINGS



NOTES:

*THIS DIMENSION ALLOWS FOR OFF-CENTER LID, MENISCUS AND GLASS OVERRUN

**INCREASE DIMENSIONS BY 0.003 INCHES (0.076 mm) WHEN LEAD FINISH A IS APPLIED (SOLDER DIPPED)

W10 (GLASS) 0603

W Package
10-Lead Flatpak Glass Sealed (Hermetic)
(Reference LTC DWG # 05-08-1130)
Dimensions shown in inches and (millimeters)

REVISION HISTORY (Revision history begins at Rev F)

REV	DATE	DESCRIPTION	PAGE NUMBER
F	10/14	Corrected R1 to R _L in A _{YOL} specification.	2, 3
G	8/24	Changes to Table 2: Electrical Test Requirements	5
I	7/25	Changes to Table 1A: Electrical Characteristics and Table 2A: Electrical Characteristics	3–5
		Added Package Outline Drawings	8