

**RELIABILITY REPORT  
FOR**

**DS21Q552, Rev B1**

**Dallas Semiconductor**

**4401 South Beltwood Parkway  
Dallas, TX 75244-3292**

**Prepared by:**

**Ken Wendel  
Reliability Engineering Manager  
Dallas Semiconductor  
4401 South Beltwood Pkwy.  
Dallas, TX 75244-3292  
Email : ken.wendel@dalsemi.com  
ph: 972-371-3726  
fax: 972-371-6016  
mbl: 214-435-6610**

**Conclusion:**

The following qualification successfully meets the quality and reliability standards required of all Dallas Semiconductor products and processes:

DS21Q552, Rev B1

In addition, Dallas Semiconductor's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maxim-ic.com/TechSupport/dsreliability.html>.\*

**Module Description:**

A description of this Module can be found in the product data sheet. You can find the product data sheet at [http://dbserv.maxim-ic.com/l\\_datasheet3.cfm](http://dbserv.maxim-ic.com/l_datasheet3.cfm).\*

**Reliability Derating:**

A module device consists of one or more IC's in a single, upward integrated, package. This package is assembled to include batteries, crystals, and other piece parts that make up the configuration of the Module. Because of either the complexity of the package or the included piece parts, standard high temperature reliability testing is not possible. Therefore, in order to determine the reliability of module products, the reliability of each of the piece parts is individually determined, then summed to determine the reliability of the integrated module product. If there are "n" significant components in the module then:

$$Fr(\text{module}) = Fr(1) + Fr(2) + Fr(3) + \dots + Fr(n)$$

Fr (module) = Failure rate of module  
Fr(n) = Failure rate of the nth component

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$MTTF = 1/Fr$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this module/assembly is:

<b>Module Device:</b>	<b>Module Units:</b>	<b>Quantity:</b>	<b>Fails:</b>	<b>Ea:</b>	<b>MTTF (Yrs):</b>	<b>FITs:</b>
DS21552	4	1428	0	0.7	<u>28091</u>	<u>4.1</u>
<b>Totals:</b>					<b>28091</b>	<b>4.1</b>

The parameters used to calculate the module failure rate are as follows:

**Cf: 60%**      **Tu: 25 °C**

The reliability data follows. At the start of this data is the module assembly information. This is a description of the module. The next section is the detailed reliability data for each stress found in the qualification / monitor. If there are additional processes or assemblies used as part of this report, a description of each will follow which includes the respective reliability data for that process/ assembly. The reliability data section includes the latest data available. Some of this data may be generic with other packages or products.

\* Some proprietary products may be excepted from this requirement.

---

**Assembly Information:**

Assembly Site: Stats  
 Pin Count: 300  
 Package Type: MCMBGA  
 Body Size: 27x27x1.73  
 Mold Compound: Plaskon SMT-B1  
 Lead Frame: PCB; BT  
 Lead Finsh:  
 Die Attach: A8510AA Silverfilled Ablestik  
 Bond Wire / Size: Au / 1.2 mil  
 Flammability: UL 94-V0  
 Moisture Sensitivity Level 4  
 (JEDEC J-STD20A)  
 Date Code Range: 9844 to 9917

---

**MOISTURE SENSITIVITY LEVEL 4**

DESCRIPTION	DATE CD	CONDITION	READPOINT	QTY	FAILS	FA#
PRECONDITION U/S	9844	J-STD-020	175 DYS	8	0	
ULTRASOUND		J-STD-020	175 DYS	8	0	
STORAGE LIFE		125C	24 HRS	8		
MOISTURE SOAK		30C/60% R.H.	144 HRS	8		
CONVECTION REFLOW		220C	3 PASS	8	0	
EXTERNAL VISUAL		MIL-STD-883-2009	174 DYS	8	0	
PRECONDITION U/S	9917	J-STD-020	4 DYS	8	0	
ULTRASOUND		J-STD-020	4 DYS	8	0	
STORAGE LIFE		125C	24 HRS	8		
MOISTURE SOAK		30C/60% R.H.	144 HRS	8		
CONVECTION REFLOW		220C	3 PASS	8	0	
EXTERNAL VISUAL		MIL-STD-883-2009	3 DYS	8	0	
<b>Total:</b>					<b>0</b>	

---

**OPERATING LIFE**

DESCRIPTION	DATE CD	CONDITION	READPOINT	QTY	FAILS	FA#
INFANT LIFE	9844	125C, 3.5 VOLTS	48 HRS	200	0	
HIGH VOLTAGE LIFE	9844	125C, 3.5 VOLTS	2000 HRS	48	0	
INFANT LIFE	9917	125C, 3.5 VOLTS	48 HRS	200	0	
HIGH VOLTAGE LIFE	9917	125C, 3.5 VOLTS	2000 HRS	48	0	
<b>Total:</b>					<b>0</b>	

---

**PACKAGE TESTS**

DESCRIPTION	DATE CD	CONDITION	READPOINT	QTY	FAILS	FA#
-------------	---------	-----------	-----------	-----	-------	-----

CONSTRUCTION ANALYSIS	9844	TO BE DONE BY F/A	2	WKS	5	0
X-RAY	9844	MIL-STD-883-2012 : TOP & SIDE VIEW	1	DYS	6	0
PHYSICAL DIMENSIONS		MIL-STD-883-2016	2	DYS	6	0
MARK PERMANENCY		MIL-STD-883-2015	3	DYS	6	0
BALL SHEAR		TBD	4	DYS	6	0
X-RAY	9917	MIL-STD-883-2012 : TOP & SIDE VIEW	2	DYS	6	0
PHYSICAL DIMENSIONS		MIL-STD-883-2016	2	DYS	6	0
MARK PERMANENCY		MIL-STD-883-2015	2	DYS	6	0
BALL SHEAR		TBD	2	DYS	6	0
<b>Total:</b>						<b>0</b>

---

#### TEMPERATURE CYCLE

DESCRIPTION	DATE CD	CONDITION	READPOINT	QTY	FAILS	FA#
TEMP CYCLE	9844	-55C TO 125C	1000 CYS	77	0	
TEMP CYCLE	9917	-55C TO 125C	1000 CYS	83	0	
<b>Total:</b>					<b>0</b>	

---

#### TEMPERATURE HUMIDITY BIAS

DESCRIPTION	DATE CD	CONDITION	READPOINT	QTY	FAILS	FA#
BIASED MOISTURE	9844	85/85, 3.5 VOLTS	959 HRS	30	2	No FA
BIASED MOISTURE	9917	85/85, 3.5 VOLTS	959 HRS	27	0	
<b>Total:</b>					<b>2</b>	