

87654321

PRIMARY SIDE

REVISION

REVDESCRIPTIONDATEAPPROVED

AINITIAL RELEASE

SPECIFICATIONS:

MATERIALS:

MATERIAL FAMILY:

CLADDING:

SOLDER MASK:

SILK SCREEN:

SURFACE FINISH:

INTENTIONAL SHORTS:

TEST REQUIREMENTS:

ALL LAMINATES AND BONDING MATERIALS SHOULD BE SELECTED FROM IPC-4101 OR IPC-4103, MINIMUM Tg>130degC, Td>300degC, U.L. RATING OF 94 V-0

ISOLA 370HR OR EQUIVALENT

EXTERNAL LAYERS .5 OZ. COPPER, OVERPLATE TO 1.5 OZ. INTERNAL SIGNAL LAYERS .5 OZ. COPPER. INTERNAL PLANE LAYERS 1 OZ. COPPER.

NOTE: IF THE LAYER STACKUP CONFLICTS WITH THE ABOVE CLADDING SPECIFICATIONS THEN THE LAYER STACKUP SHALL TAKE PRECEDENCE.

SHALL BE LIQUID PHOTOIMAGEABLE (LPI) APPLIED ON BOTH SIDES OVER BARE COPPER OR GOLD AND SHALL MEET IPC-SM-840 (LATEST REV.) CLASS 3. COLOR BLUE.

SHALL BE PERMANENT NON-CONDUCTIVE EPOXY INK, COLOR: WHITE SYNTHETIC INKJET PRINTING ALLOWED FOR DENSE BOARDS, COLOR: WHITE

ENIG (Electroless Nickel/Immersion Gold) 2.54um (100 MICRO INCHES) NICKEL/ 0.0762um - 0.127um (3-5 MICRO INCHES) GOLD

IF SUPPLIED DATA INCLUDES A FILE "READ_ME.2", THEN INTENTIONAL NET SHORTS EXIST. CUSTOMER REVIEW AND APPROVAL IS REQUIRED IF SUPPLIED DATA REPORTS ANY CONDITION THAT DOES NOT MATCH "READ_ME.2" FILE PROVIDED.

100% NETLIST ELECTRICAL VERIFICATION USING CUSTOMER SUPPLIED IPC-D-356 NETLIST FOR OPENS AND SHORTS WHEN "GERBER DATA" IS PROVIDED. THIS VERIFICATION ALSO REQUIRED FOR "ODB++" DATA PER EMBEDDED NETLIST.

REQUIREMENTS:

1. REFER TO IPC-6010 SERIES (LATEST REV.), CLASS 2 FOR FABRICATION UNLESS OTHERWISE SPECIFIED.

2. ACCEPTABILITY PER ANALOG DEVICES, INC. SPECIFICATION TST00115, (LATEST REVISION.)

3. MODIFICATIONS TO THE ARTWORK ARE NOT ALLOWED WITHOUT WRITTEN AUTHORIZATION.

4. HOLE PATTERN TOLERANCES FOR UNDIMENSIONED HOLES SHALL BE A DIAMETER OF 0.127mm (0.005 INCHES) FROM THEIR TRUE POSITION.

5. PLATED HOLE WALL THICKNESS SHALL NOT BE LESS THAN 25um (0.001 INCH) MINIMUM AVERAGE, WITH NO READING LESS THAN 20um (.0008) BY CROSS SECTION.

6. HOLE DIAMETERS APPLY AFTER PLATING.

7. FINISHED CONDUCTOR WIDTHS SHALL NOT BE REDUCED FROM THE NOMINAL INDICATED ON THE MASTER PATTERN, BY MORE THAN THE CONDUCTOR THICKNESS.

8. MINIMUM DESIGN LINE WIDTH IS 0.15mm.

9. MINIMUM DESIGN SPACING IS 0.2mm.

10. NON-FUNCTIONAL PAD REMOVAL FROM INNER SIGNAL LAYERS MAY BE PERFORMED AFTER CUSTOMER APPROVAL.

11. IF PAD SIZES PROVIDED ARE NOT LARGE ENOUGH TO MAINTAIN ANNULAR RING REQUIREMENT, MFG. MAY REQUEST APPROVAL TO TEAR DROP PADS TO MAINTAIN ANNULAR RING. (AT PAD TO TRACE INTERSECTION ONLY AND ELECTRICAL INTEGRITY MUST BE MAINTAINED.)

12. THIEVING MAY BE ADDED TO COMPENSATE FOR LOW COPPER DENSITY AREAS ON THIS DESIGN ONLY AFTER REVIEW AND APPROVAL FROM THE CUSTOMER:

A. THIEVING TO CARD EDGE, FIDUCIALS, NON-PLATED THROUGH HOLES, ALL OTHER FEATURES TO BE 5.08MM (0.200 INCH) MINIMUM.

B. THERE SHALL BE NO THIEVING IN ANY AREAS FREE OF SOLDER MASK OR INTERNAL COPPER PLANES.

13. MFG. TO LEGIBLY ETCH OR STAMP/SCREEN WITH PERMANENT NON-CONDUCTIVE INK ON SECONDARY SIDE IN A CLEAR AREA UNLESS OTHERWISE INDICATED:

A. U.L. CODE-FLAMMABILITY RATING

B. DATE CODE (STAMP).

C. LOT NUMBER

D. MFG. LOGO

E. SUCCESSFUL ELECTRICAL TEST.

14. REPAIRS PER IPC-7711/21 (LATEST REV.) ARE ALLOWED.

15. ~~THRU VIAS FILLED WITH NON-CONDUCTIVE EPOXY AND PLATED OVER. COPLANAR ON BOTH SIDES WITHIN .001 INCH PRIOR TO FINAL PLATING.~~

4 LAYER STACKUP

NOMINAL FINISHED BOARD THICKNESS 1.6mm +/- 10%

PRIMARY SILKSCREEN

PRIMARY GOLD MASK

PRIMARY SOLDER MASK

PRIMARY SIDE (LAYER 1)

XXXXXXX PLANE (LAYER 2)

XXXXXXX PLANE (LAYER 3)

SECONDARY SIDE (LAYER 4)

SECONDARY SOLDER MASK

SECONDARY GOLD MASK

SECONDARY SILKSCREEN

57

2.25

52.5

2.25

49.54

70.29

20.75

HOLE TOLERANCE

UNLESS SPECIFIED

PLATED: +/- .003

NON PLATED: +/- .001

DRILL CHART: TOP to BOTTOM

ALL UNITS ARE IN MILLIMETERS

FIGURE	FINISHED SIZE	PLATED	QTY
•	0.254	PLATED	59
•	0.4064	PLATED	47
◦	1.143	PLATED	48
◈	1.27	PLATED	4
•	0.7112	NON-PLATED	1
^	1.0922	NON-PLATED	1
○	3.175	NON-PLATED	2

87654321

ART FILM - FAB

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MM TOLERANCES DECIMALS FRACTIONS ANGLES .00 -0.25 .000 -0.010 0° -90°

ASSEMBLY

APPROVALDATE

MATERIAL

DESIGNEDBY

CHECKED

DATE

FINISH

SIZE

FSCM NO

DRAWING NUMBER

REV

DO NOT SCALE DWG

SCALE

1/1

SHEET 1 OF 1

TITLE

EVAL - TempSense - ARDZ

ANALOG DEVICES

ANALOG DEVICES INTERNATIONAL ERDC Building ROBERTS BUILDING PARK Rahway, LIMERICK, IRELAND