

**PRODUCT RELIABILITY REPORT
FOR**

DS3501, Rev A2

Dallas Semiconductor

**4401 South Beltwood Parkway
Dallas, TX 75244-3292**

Prepared by:

**Ken Wendel
Reliability Engineering Manager
Dallas Semiconductor
4401 South Beltwood Pkwy.
Dallas, TX 75244-3292
Email : ken.wendel@dalsemi.com
ph: 972-371-3726
fax: 972-371-6016
mbl: 214-435-6610**

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Dallas Semiconductor products:

DS3501, Rev A2

In addition, Dallas Semiconductor's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maxim-ic.com/TechSupport/dsreliability.html>.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at http://dbserv.maxim-ic.com/l_datasheet3.cfm.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$$

AfT = Acceleration factor due to Temperature
tu = Time at use temperature (e.g. 55°C)
ts = Time at stress temperature (e.g. 125°C)
k = Boltzmann's Constant (8.617 x 10⁻⁵ eV/°K)
Tu = Temperature at Use (°K)
Ts = Temperature at Stress (°K)
Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$$AfV = \exp(B * (Vs - Vu))$$

AfV = Acceleration factor due to Voltage
Vs = Stress Voltage (e.g. 7.0 volts)
Vu = Maximum Operating Voltage (e.g. 5.5 volts)
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$$Fr = X / (ts * AfV * AfT * N * 2)$$

X = Chi-Sq statistical upper limit
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$MTTF = 1/Fr$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

FAILURE RATE:	MTTF (YRS):	54287	FITS:	2.1
	DEVICE HOURS:	462000	FAILS:	0

Only data from Operating Life or similar stresses are used for this calculation.

The parameters used to calculate this failure rate are as follows:

Cf: 60% **Ea: 0.7** **B: 0** **Tu: 25 °C** **Vu: 5.5 Volts**

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. "*" after DATE CODE denotes specific product data.

Device Information:

Process: E6WA-2P2M,HPVt,E2,EPROGVt,TCZ,PF ALOCOS:GOI
 Passivation: Passivation w/Nov TEOS Oxide-Nitride
 Die Size: 62 x 87
 Number of Transistors: 0
 Interconnect: Aluminum / 1% Silicon / 0.5% Copper
 Gate Oxide Thickness: 150 Å

ELECTRICAL CHARACTERIZATION

DESCRIPTION	DATE CODE	CONDITION	READPOINT	QTY	FAILS	FA#
ESD SENSITIVITY	0645 *	EOS/ESD S5.1 HBM 500 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0645 *	EOS/ESD S5.1 HBM 1000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0645 *	EOS/ESD S5.1 HBM 2000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0645 *	EOS/ESD S5.1 HBM 4000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0645 *	EOS/ESD S5.1 HBM 8000 VOLTS	1 PUL'S	3	3	No FA
LATCH-UP	0645 *	JESD78, I-TEST 125C		6	0	
LATCH-UP	0645 *	JESD78, V-SUPPLY TEST 125C		6	0	
ESD SENSITIVITY	0645 *	JESD22-A115 MM 50 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0645 *	JESD22-A115 MM 100 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0645 *	JESD22-A115 MM 200 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0645 *	JESD22-A115 MM 400 VOLTS	1 PUL'S	3	3	No FA
ESD SENSITIVITY	0645 *	JESD22-C101 CDM 100 VOLTS	3 PUL'S	3	0	
ESD SENSITIVITY	0645 *	JESD22-C101 CDM 200 VOLTS	3 PUL'S	3	0	
ESD SENSITIVITY	0645 *	JESD22-C101 CDM 500 VOLTS	3 PUL'S	3	0	
ESD SENSITIVITY	0645 *	JESD22-C101 CDM 1000 VOLTS	3 PUL'S	3	0	

ESD SENSITIVITY	0645 *	JESD22-C101 CDM 2000 VOLTS	3	PUL'S	3	3	No FA
				Total:		9	

OPERATING LIFE

DESCRIPTION	DATE	CODE	CONDITION	READPOINT	QTY	FAILS	FA#
HIGH TEMP OP LIFE	0548		125C, 5.5V (PSA) & 3.6V (PSB)	1000 HRS	77	0	
HIGH TEMP OP LIFE	0549		125C, 5.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	0552		125C, +5.5V (PSA), +5.5V (PSD)	1000 HRS	77	0	
HIGH TEMP OP LIFE	0612		125C, 5.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	0623		125C, 5.5V (PSA), -7.0V (PSC) & +7.0V (PSD)	1000 HRS	77	0	
HIGH TEMP OP LIFE	0645 *		125C, 5.5 VOLTS	1000 HRS	77	0	
				Total:		0	

W/E ENDURANCE AND DATA RET'N

DESCRIPTION	DATE	CODE	CONDITION	READPOINT	QTY	FAILS	FA#
WRITE CYCLE STRESS (KCYS)	0548		70 C, 5.5V (PSA) & 3.6V (PSB)	50 KCYS	77	0	
STORAGE LIFE			150C	1000 HRS	77	0	
WRITE CYCLE STRESS (KCYS)	0549		85 C, 5.5 VOLTS	30 KCYS	77	0	
STORAGE LIFE			150C	1000 HRS	77	0	
WRITE CYCLE STRESS (KCYS)	0552		70C, +5.5V (PSA), +5.5V (PSD)	30 KCYS	77	0	
STORAGE LIFE			150C	1000 HRS	77	0	
WRITE CYCLE STRESS (KCYS)	0612		70 C, 5.5 VOLTS	30 KCYS	77	0	
STORAGE LIFE			150C	1000 HRS	77	0	
WRITE CYCLE STRESS (KCYS)	0623		70C, 5.5V (PSA), -7.0V (PSC) & +7.0V (PSD)	30 KCYS	77	0	
STORAGE LIFE			150C	1000 HRS	77	0	
WRITE CYCLE STRESS (KCYS)	0709 *		25 C, 5.5 VOLTS	200 KCYS	77	0	
STORAGE LIFE		*	150C	96 HRS	77	0	
				Total:		0	

FAILURE RATE:	MTTF (YRS):	54287	FITS:	2.1
	DEVICE HOURS:	462000	FAILS:	0