

PRODUCT RELIABILITY REPORT
FOR

DS1339U, Rev A2

Dallas Semiconductor

4401 South Beltwood Parkway
Dallas, TX 75244-3292

Prepared by:

Ken Wendel

Ken Wendel
Reliability Engineering Manager
Dallas Semiconductor
4401 South Beltwood Pkwy.
Dallas, TX 75244-3292
Email : ken.wendel@dalsemi.com
ph: 972-371-3726
fax: 972-371-6016
mbl: 214-435-6610

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Dallas Semiconductor products:

DS1339U, Rev A2

In addition, Dallas Semiconductor's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maxim-ic.com/TechSupport/dsreliability.html>.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at http://dbserv.maxim-ic.com/l_datasheet3.cfm.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$$

AfT = Acceleration factor due to Temperature
tu = Time at use temperature (e.g. 55°C)
ts = Time at stress temperature (e.g. 125°C)
k = Boltzmann's Constant (8.617 x 10⁻⁵ eV/°K)
Tu = Temperature at Use (°K)
Ts = Temperature at Stress (°K)
Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$$AfV = \exp(B * (Vs - Vu))$$

AfV = Acceleration factor due to Voltage
Vs = Stress Voltage (e.g. 7.0 volts)
Vu = Maximum Operating Voltage (e.g. 5.5 volts)
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$$Fr = X / (ts * AfV * AfT * N * 2)$$

X = Chi-Sq statistical upper limit
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$MTTF = 1/Fr$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

FAILURE RATE: **MTTF (YRS): 6451** **FITS: 17.7**

The parameters used to calculate this failure rate are as follows:

Cf: 60% **Ea: 0.7** **B: 0** **Tu: 55 °C** **Vu: 5.5 Volts**

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. "*" after DATE CODE denotes specific product data.

Device Information:

Process: E6H-2P2M,HPVt,TCN1 PBL:GOI
 Passivation: Passivation w/Nov TEOS Oxide-Nitride
 Die Size: 58 x 84
 Number of Transistors: 12000
 Interconnect: Aluminum / 1% Silicon / 0.5% Copper
 Gate Oxide Thickness: 150 Å

ELECTRICAL CHARACTERIZATION

DESCRIPTION	DATE CODE	CONDITION	READPOINT	QTY	FAILS	FA#
ESD SENSITIVITY	0224 *	EOS/ESD S5.1 HBM 500 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0224 *	EOS/ESD S5.1 HBM 1000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0224 *	EOS/ESD S5.1 HBM 2000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0224 *	EOS/ESD S5.1 HBM 4000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0224 *	EOS/ESD S5.1 HBM 8000 VOLTS	1 PUL'S	3	0	
LATCH-UP	0224 *	JESD78, I-TEST 125C		3	0	
LATCH-UP	0224 *	JESD78, Vsupply TEST 125C		3	0	
Total:					0	

OPERATING LIFE

DESCRIPTION	DATE CODE	CONDITION	READPOINT	QTY	FAILS	FA#
INFANT LIFE	9918	125C, 6.0 VOLTS	48 HRS	746	0	
HIGH VOLTAGE LIFE	9935	125C, 6.0 VOLTS	1000 HRS	120	0	
INFANT LIFE	0027	125C, 5.0 VOLTS	48 HRS	315	0	
HIGH VOLTAGE LIFE	0027	125C, 5.0 VOLTS	1000 HRS	149	0	
HIGH VOLTAGE LIFE	0047	125C, 6.0 VOLTS	1000 HRS	150	0	
HIGH VOLTAGE LIFE	0106	125C, 6.0 VOLTS	192 HRS	77	0	
HIGH VOLTAGE LIFE	0145	125C, 6.0 VOLTS	240 HRS	77	0	
HIGH VOLTAGE LIFE	0210	125C, 6.0 VOLTS	1000 HRS	80	0	

HIGH VOLTAGE LIFE	0224	*	125C, 6.0 VOLTS	1000	HRS	80	0
HIGH VOLTAGE LIFE	0224	*	125C, 6.0 VOLTS	1000	HRS	80	0
HIGH VOLTAGE LIFE	0227		125C, 6.0 VOLTS	1000	HRS	77	0
HIGH VOLTAGE LIFE	0227		125C, 6.0 VOLTS	1000	HRS	77	0
HIGH VOLTAGE LIFE	0227		125C, 6.0 VOLTS	1000	HRS	77	0
HIGH VOLTAGE LIFE	0238		125C, 6.0 VOLTS	1000	HRS	45	2 FREQUENCY
HIGH VOLTAGE LIFE	0241		125C, 6.0 VOLTS	1000	HRS	77	0
HIGH VOLTAGE LIFE	0247		125C, 6.0 VOLTS	1000	HRS	77	0
HIGH VOLTAGE LIFE	0302		125C, 6.0 VOLTS	1000	HRS	77	0
HIGH VOLTAGE LIFE	0306		125C, 4.9 V (PSA) & 3.6 V (PSB)	1000	HRS	45	0
HIGH VOLTAGE LIFE	0307		125C, 6.0 VOLTS	1000	HRS	77	0
HIGH VOLTAGE LIFE	0308		125C, 6.0 VOLTS	1000	HRS	77	0
HIGH VOLTAGE LIFE	0310		125C, 6.0 VOLTS	1000	HRS	80	0
HIGH VOLTAGE LIFE	0310		125C, 6.0 VOLTS	1000	HRS	45	0
HIGH VOLTAGE LIFE	0310		125C, 6.0 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0311		125C, 3.5 VOLTS	1000	HRS	77	0
HIGH TEMP OP LIFE	0312		125C, 3.3 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0318		125C, 5.5 VOLTS	1000	HRS	77	0
HIGH TEMP OP LIFE	0324		125C, 5.25 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0403		125C, 3.6 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0403		125C, 5.5 VOLTS	1000	HRS	77	0
HIGH TEMP OP LIFE	0412		125C, 3.5 VOLTS	1000	HRS	64	0
HIGH TEMP OP LIFE	0421		125C, 5.5 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0421		125C, 5.5 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0422		125C, 5.5 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0424		125C, 5.5 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0434		85 C, 3.3 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0440		85 C, 3.3 VOLTS	1000	HRS	45	0
HIGH TEMP OP LIFE	0440		85 C, 3.3 VOLTS	1000	HRS	45	0
HIGH VOLTAGE LIFE	0530		125C, 4.9 V (PSA) & 3.6 V (PSB)	192	HRS	45	

Total: 2

FAILURE RATE:

MTTF (YRS): 6451

FITS: 17.7