



11/18/2011

**PRODUCT RELIABILITY REPORT
FOR**

DS1347

Maxim Integrated Products

**4401 South Beltwood Parkway
Dallas, TX 75244-3292**

Prepared by:

**Don Lipps
Manager, Reliability Engineering
Maxim Integrated Products
4401 South Beltwood Pkwy.
Dallas, TX 75244-3292
Email: don.lipps@maxim-ic.com
ph: 972-371-3739**

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Maxim products:

DS1347

In addition, Maxim's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maxim-ic.com/TechSupport/dsreliability.html>.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at http://dbserv.maxim-ic.com/l_datasheet3.cfm.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$$

AfT = Acceleration factor due to Temperature
tu = Time at use temperature (e.g. 55°C)
ts = Time at stress temperature (e.g. 125°C)
k = Boltzmann's Constant (8.617 x 10⁻⁵ eV/°K)
Tu = Temperature at Use (°K)
Ts = Temperature at Stress (°K)
Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$$AfV = \exp(B * (Vs - Vu))$$

AfV = Acceleration factor due to Voltage
Vs = Stress Voltage (e.g. 7.0 volts)
Vu = Maximum Operating Voltage (e.g. 5.5 volts)
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$$Fr = X / (ts * AfV * AfT * N * 2)$$

X = Chi-Sq statistical upper limit
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$\text{MTTF} = 1/\text{Fr}$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

FAILURE RATE: **MTTF (YRS):** **78609** **FITS:** **1.5**
DEVICE HOURS: **630971254** **FAILS:** **0**

Only data from Operating Life or similar stresses are used for this calculation.

The parameters used to calculate this failure rate are as follows:

Cf: 60% **Ea: 0.7** **B: 0** **Tu: 25 °C** **Vu: 5.5 Volts**

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. **Bold** Product Number denotes specific product data.

Device Information:

Process: SA E6H, 2P2M,HPVt,PF-Ring,TCZ,ALOCOS:GOI
 Passivation: TEOS Oxide-Nitride Passivation
 Die Size: 70 x 63
 Number of Transistors: 12352
 Interconnect: Aluminum / 0.5% Copper
 Gate Oxide Thickness: 150 Å

ESD CDM

DESCRIPTION	DATE CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
ESD SENSITIVITY	1129 DS1347 ZS167344AD	JESD22-C101 CDM 250 VOLTS	3 PUL'S	5	0	
ESD SENSITIVITY	1129 DS1347 ZS167344AD	JESD22-C101 CDM 500 VOLTS	6 PUL'S	5	0	
ESD SENSITIVITY	1129 DS1347 ZS167344AD	JESD22-C101 CDM 750 VOLTS	9 PUL'S	5	0	
Total:					0	

ESD HBM

DESCRIPTION	DATE CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
ESD SENSITIVITY	1129 DS1347 ZS167344AD	JESD22-A114 HBM 500 VOLTS	3 PUL'S	5	0	
ESD SENSITIVITY	1129 DS1347 ZS167344AD	JESD22-A114 HBM 1000 VOLTS	3 PUL'S	5	0	
ESD SENSITIVITY	1129 DS1347 ZS167344AD	JESD22-A114 HBM 1500 VOLTS	3 PUL'S	5	0	
ESD SENSITIVITY	1129 DS1347 ZS167344AD	JESD22-A114 HBM 2000 VOLTS	3 PUL'S	5	0	
ESD SENSITIVITY	1129 DS1347 ZS167344AD	JESD22-A114 HBM 2500 VOLTS	3 PUL'S	5	0	
Total:					0	

LATCH-UP

DESCRIPTION	DATE	CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
LATCH-UP I	1129	DS1347	ZS167344AD JESD78A, I-TEST 25C 100mA		6	0	
LATCH-UP I	1129	DS1347	ZS167344AD JESD78A, I-TEST 25C 250mA		6	0	
LATCH-UP V	1129	DS1347	ZS167344AD JESD78A, V-SUPPLY TEST 25C		6	0	
Total:						0	

OPERATING LIFE

DESCRIPTION	DATE	CODE/PRODUCT/LOT	CONDITION	READPOIN	QTY	FAILS	FA#
HIGH TEMP OP LIFE	0906	DS5250	WK942982D 125C, 5.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	0921	DS7865	WQ946139A 125C, 5.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	0923	DS5250	WK947706A 125C, 5.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	0923	DS1748	WN945795L 125C, 5.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	0925	DS21Q50	WK945230A 125C, 3.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	0940	DS80C320	WK048689A 125C, 5.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	0944	DS80C320	WK049844A 125C, 5.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	0947	DS1341	WD048116A 125C, 5.5 VOLTS	192 HRS	77	0	
HIGH TEMP OP LIFE	0949	DS80C320	WK049846A 125C, 5.5 VOLTS	1000 HRS	77	0	
HIGH TEMP OP LIFE	1022	MAX34405	QD056611A 125C, 3.6 VOLTS	192 HRS	45	0	
HIGH TEMP OP LIFE	1037	DS1340	WD157959A 125C, 5.5 VOLTS	192 HRS	77	0	
HIGH TEMP OP LIFE	1129	DS1347	ZS167344AD 125C, 5.5 VOLTS	192 HRS	77	0	
Total:						0	

FAILURE RATE:**MTTF (YRS):****78609****FITS:****1.5****DEVICE HOURS:****630971254****FAILS:****0**