



10/8/2008

**PRODUCT RELIABILITY REPORT  
FOR**

**DS1875, Rev A2**

**Maxim Integrated Products**

**4401 South Beltwood Parkway  
Dallas, TX 75244-3292**

**Prepared by:**

**Don Lipps  
Staff Reliability Engineer  
Maxim Integrated Products  
4401 South Beltwood Pkwy.  
Dallas, TX 75244-3292  
Email: don.lipps@maxim-ic.com  
ph: 972-371-3739  
fax: 972-371-6016**

**Conclusion:**

The following qualification successfully meets the quality and reliability standards required of all Maxim products:

DS1875, Rev A2

In addition, Maxim's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maxim-ic.com/TechSupport/dsreliability.html>.

**Device Description:**

A description of this device can be found in the product data sheet. You can find the product data sheet at [http://dbserv.maxim-ic.com/l\\_datasheet3.cfm](http://dbserv.maxim-ic.com/l_datasheet3.cfm).

**Reliability Derating:**

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$$

AfT = Acceleration factor due to Temperature  
tu = Time at use temperature (e.g. 55°C)  
ts = Time at stress temperature (e.g. 125°C)  
k = Boltzmann's Constant (8.617 x 10<sup>-5</sup> eV/°K)  
Tu = Temperature at Use (°K)  
Ts = Temperature at Stress (°K)  
Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$$AfV = \exp(B * (Vs - Vu))$$

AfV = Acceleration factor due to Voltage  
Vs = Stress Voltage (e.g. 7.0 volts)  
Vu = Maximum Operating Voltage (e.g. 5.5 volts)  
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$$Fr = X / (ts * AfV * AfT * N * 2)$$

X = Chi-Sq statistical upper limit  
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$MTTF = 1/Fr$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

|                      |                      |               |               |            |
|----------------------|----------------------|---------------|---------------|------------|
| <b>FAILURE RATE:</b> | <b>MTTF (YRS):</b>   | <b>63249</b>  | <b>FITS:</b>  | <b>1.8</b> |
|                      | <b>DEVICE HOURS:</b> | <b>538272</b> | <b>FAILS:</b> | <b>0</b>   |

Only data from Operating Life or similar stresses are used for this calculation.

The parameters used to calculate this failure rate are as follows:

|                |                |             |                  |                      |
|----------------|----------------|-------------|------------------|----------------------|
| <b>Cf: 60%</b> | <b>Ea: 0.7</b> | <b>B: 0</b> | <b>Tu: 25 °C</b> | <b>Vu: 4.2 Volts</b> |
|----------------|----------------|-------------|------------------|----------------------|

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. "\*" after DATE CODE denotes specific product data and SEQ No. to identify specific line items in the report for comments when required.

**Device Information:**

Process: E35X-3P3M,DPE2,CrSi,DSD,PDES,DRES,Cap,ENPN,DPT,HTO,SgHalo  
 Passivation: TEOS Ox-Nit Passivation for E35X; Full BEOL at SA; PT only in Dallas  
 Die Size: 134 x 152  
 Number of Transistors: 105346  
 Interconnect: Aluminum / 0.5% Copper  
 Gate Oxide Thickness: 120 Å

**DATA RETENTION**

| DESCRIPTION   | DATE CODE/SEQ | CONDITION | READPOINT | QTY | FAILS    | FA# |
|---------------|---------------|-----------|-----------|-----|----------|-----|
| STORAGE LIFE  | 0632          | 150C      | 1000 HRS  | 77  | 0        |     |
| STORAGE LIFE  | 0651          | 150C      | 1000 HRS  | 77  | 0        |     |
| STORAGE LIFE  | 0711          | 150C      | 1000 HRS  | 77  | 0        |     |
| STORAGE LIFE  | 0715          | 150C      | 1000 HRS  | 77  | 0        |     |
| STORAGE LIFE  | 0747          | 150C      | 1000 HRS  | 77  | 0        |     |
| STORAGE LIFE  | 0827          | 150C      | 192 HRS   | 77  | 0        |     |
| <b>Total:</b> |               |           |           |     | <b>0</b> |     |

**ELECTRICAL CHARACTERIZATION**

| DESCRIPTION     | DATE CODE/SEQ | CONDITION                   | READPOINT | QTY | FAILS | FA# |
|-----------------|---------------|-----------------------------|-----------|-----|-------|-----|
| ESD SENSITIVITY | 0810 * 1      | EOS/ESD S5.1 HBM 500 VOLTS  | 1 PUL'S   | 3   | 0     |     |
| ESD SENSITIVITY | 0810 * 2      | EOS/ESD S5.1 HBM 1000 VOLTS | 1 PUL'S   | 3   | 0     |     |
| ESD SENSITIVITY | 0810 * 3      | EOS/ESD S5.1 HBM 2000 VOLTS | 1 PUL'S   | 3   | 0     |     |
| ESD SENSITIVITY | 0810 * 4      | EOS/ESD S5.1 HBM 4000 VOLTS | 1 PUL'S   | 3   | 0     |     |
| ESD SENSITIVITY | 0810 * 5      | EOS/ESD S5.1 HBM 8000 VOLTS | 1 PUL'S   | 3   | 0     |     |

|               |      |     |                            |  |          |          |
|---------------|------|-----|----------------------------|--|----------|----------|
| LATCH-UP      | 0810 | * 6 | JESD78, I-TEST 125C        |  | 6        | 0        |
| LATCH-UP      | 0810 | * 7 | JESD78, V-SUPPLY TEST 125C |  | 6        | 0        |
| <b>Total:</b> |      |     |                            |  | <b>0</b> | <b>0</b> |

**OPERATING LIFE**

| DESCRIPTION       | DATE CODE/SEQ | CONDITION                     | READPOINT | QTY | FAILS    | FA#      |
|-------------------|---------------|-------------------------------|-----------|-----|----------|----------|
| HIGH TEMP OP LIFE | 0626          | 125C, 5.5 VOLTS               | 1000 HRS  | 77  | 0        |          |
| HIGH TEMP OP LIFE | 0632          | 125C, 3.6V (PSA) & 3.9V (PSB) | 1000 HRS  | 45  | 0        |          |
| HIGH TEMP OP LIFE | 0651          | 125C, 3.6 VOLTS               | 1000 HRS  | 45  | 0        |          |
| HIGH TEMP OP LIFE | 0711          | 125C, 3.0V (PSB) & 3.6V (PSA) | 1000 HRS  | 45  | 0        |          |
| HIGH TEMP OP LIFE | 0715          | 125C, 3.6 VOLTS               | 1000 HRS  | 45  | 0        |          |
| HIGH TEMP OP LIFE | 0715          | 125C, 3.6 VOLTS               | 1000 HRS  | 77  | 0        |          |
| HIGH TEMP OP LIFE | 0719          | 125C, 3.6 VOLTS               | 408 HRS   | 45  | 0        |          |
| HIGH TEMP OP LIFE | 0719          | 125C, 3.6 VOLTS               | 408 HRS   | 32  | 0        |          |
| HIGH TEMP OP LIFE | 0732          | 125C, 5.5 VOLTS               | 408 HRS   | 45  | 0        |          |
| HIGH TEMP OP LIFE | 0732          | 125C, 5.5 VOLTS               | 408 HRS   | 32  | 0        |          |
| HIGH TEMP OP LIFE | 0745          | 125C, 5.5 VOLTS               | 240 HRS   | 45  | 0        |          |
| HIGH TEMP OP LIFE | 0747          | 125C, 3.6V (PSA) & 3.0V (PSB) | 1000 HRS  | 45  | 0        |          |
| HIGH TEMP OP LIFE | 0810          | * 1 125C, 5.5 VOLTS           | 1000 HRS  | 77  | 0        |          |
| HIGH TEMP OP LIFE | 0827          | 125C, 3.6 VOLTS               | 192 HRS   | 45  | 0        |          |
| <b>Total:</b>     |               |                               |           |     | <b>0</b> | <b>0</b> |

**W/E ENDURANCE AND DATA RET'N**

| DESCRIPTION               | DATE CODE/SEQ | CONDITION           | READPOINT | QTY | FAILS    | FA#      |
|---------------------------|---------------|---------------------|-----------|-----|----------|----------|
| WRITE CYCLE STRESS (KCYS) | 0626          | 85 C, 5.5 VOLTS     | 50 KCYS   | 77  | 0        |          |
| STORAGE LIFE              | 0626          | 150C                | 1000 HRS  | 77  | 0        |          |
| WRITE CYCLE STRESS (KCYS) | 0715          | 85 C, 3.6 VOLTS     | 50 KCYS   | 77  | 0        |          |
| STORAGE LIFE              | 0715          | 150C                | 1000 HRS  | 77  | 0        |          |
| WRITE CYCLE STRESS (KCYS) | 0810          | * 2 85 C, 5.5 VOLTS | 30 KCYS   | 77  | 0        |          |
| STORAGE LIFE              | 0810          | * 2 150C            | 96 HRS    | 76  | 0        |          |
| <b>Total:</b>             |               |                     |           |     | <b>0</b> | <b>0</b> |

|                      |                      |               |               |            |
|----------------------|----------------------|---------------|---------------|------------|
| <b>FAILURE RATE:</b> | <b>MTTF (YRS):</b>   | <b>63249</b>  | <b>FITS:</b>  | <b>1.8</b> |
|                      | <b>DEVICE HOURS:</b> | <b>538272</b> | <b>FAILS:</b> | <b>0</b>   |