



4/8/2008

**PRODUCT RELIABILITY REPORT
FOR**

DS33X42, Rev B1

Maxim Integrated Products

**4401 South Beltwood Parkway
Dallas, TX 75244-3292**

Prepared by:

**Don Lipps
Staff Reliability Engineer
Maxim Integrated Products
4401 South Beltwood Pkwy.
Dallas, TX 75244-3292
Email: don.lipps@maxim-ic.com
ph: 972-371-3739
fax: 972-371-6016**

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Maxim products:

DS33X42, Rev B1

In addition, Maxim's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maxim-ic.com/TechSupport/dsreliability.html>.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at http://dbserv.maxim-ic.com/l_datasheet3.cfm.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$$

AfT = Acceleration factor due to Temperature
tu = Time at use temperature (e.g. 55°C)
ts = Time at stress temperature (e.g. 125°C)
k = Boltzmann's Constant (8.617 x 10⁻⁵ eV/°K)
Tu = Temperature at Use (°K)
Ts = Temperature at Stress (°K)
Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$$AfV = \exp(B * (Vs - Vu))$$

AfV = Acceleration factor due to Voltage
Vs = Stress Voltage (e.g. 7.0 volts)
Vu = Maximum Operating Voltage (e.g. 5.5 volts)
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$$Fr = X / (ts * AfV * AfT * N * 2)$$

X = Chi-Sq statistical upper limit
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$\text{MTTF} = 1/\text{Fr}$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

FAILURE RATE:	MTTF (YRS):	64157	FITS:	1.8
	DEVICE HOURS:	546000	FAILS:	0

Only data from Operating Life or similar stresses are used for this calculation.

The parameters used to calculate this failure rate are as follows:

Cf: 60% **Ea: 0.7** **B: 0** **Tu: 25 °C** **Vu: 3.5 Volts**

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. "*" after DATE CODE denotes specific product data and SEQ No. to identify specific line items in the report for comments when required.

Device Information:

Process: TSMC Fab8B 0.18um Logic General Purpose 1P6M Salicide 1.8V/3.3V, Phase II
 Passivation: Laser/TEOS Ox - Pass/Nit -PreLP+GenLP
 Die Size: 236 x 239
 Number of Transistors: 7400000
 Interconnect: Aluminum / 0.5% Copper
 Gate Oxide Thickness: 32 Å

ELECTRICAL CHARACTERIZATION

DESCRIPTION	DATE CODE/SEQ	CONDITION	READPOINT	QTY	FAILS	FA#
ESD SENSITIVITY	0744 * 1	EOS/ESD S5.1 HBM 500 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0744 * 2	EOS/ESD S5.1 HBM 1000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0744 * 3	EOS/ESD S5.1 HBM 2000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0744 * 4	EOS/ESD S5.1 HBM 3000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0744 * 5	EOS/ESD S5.1 HBM 4000 VOLTS	1 PUL'S	3	3	No FA
LATCH-UP	0744 * 6	JESD78, I-TEST 125C		6	0	
LATCH-UP	0744 * 7	JESD78, V-SUPPLY TEST 125C		6	0	
Total:					3	

OPERATING LIFE

DESCRIPTION	DATE CODE/SEQ	CONDITION	READPOINT	QTY	FAILS	FA#
HIGH TEMP OP LIFE	0642	125C, 2.0V (PSA) & 3.5V (PSB)	1000 HRS	45	0	
HIGH TEMP OP LIFE	0647	125C, 2.0V (PSB) & 3.5V (PSA)	1000 HRS	45	0	
HIGH TEMP OP LIFE	0648	125C, 2.0V (PSB) & 3.5V (PSA)	1000 HRS	45	0	
HIGH TEMP OP LIFE	0649	125C, 2.0V (PSB) & 3.5V (PSA)	1000 HRS	45	0	

HIGH TEMP OP LIFE	0705	125C, 3.5V (PSA) & 2.0V (PSB)	1000 HRS	45	0
HIGH TEMP OP LIFE	0705	125C, 3.5V (PSA) & 2.0V (PSB)	1000 HRS	48	0
HIGH TEMP OP LIFE	0708	125C, 2.0V (PSA) & 3.5V (PSB)	1000 HRS	45	0
HIGH TEMP OP LIFE	0709	125C, 2.0V (PSB) & 3.5V (PSA)	1000 HRS	48	0
HIGH TEMP OP LIFE	0720	125C, 2.0V (PSB) & 3.5V (PSA)	1000 HRS	45	0
HIGH TEMP OP LIFE	0731	125C, 3.5V (PSA) & 2.0V (PSB)	1000 HRS	45	0
HIGH TEMP OP LIFE	0743	125C, 2.0V (PSA) & 3.5V (PSB)	1000 HRS	45	0
HIGH TEMP OP LIFE	0744	* 1 125C, 2.0V (PSB) & 3.5V (PSA)	1000 HRS	45	0

Total: 0

FAILURE RATE: MTTF (YRS): 64157 FITS: 1.8

DEVICE HOURS: 546000 FAILS: 0