



5/26/2009

**PRODUCT RELIABILITY REPORT
FOR**

DS3605, Rev A5

Maxim Integrated Products

**4401 South Beltwood Parkway
Dallas, TX 75244-3292**

Prepared by:

**Don Lipps
Manager, Reliability Engineering
Maxim Integrated Products
4401 South Beltwood Pkwy.
Dallas, TX 75244-3292
Email: don.lipps@maxim-ic.com
ph: 972-371-3739
fax: 972-371-6016**

Conclusion:

The following qualification successfully meets the quality and reliability standards required of all Maxim products:

DS3605, Rev A5

In addition, Maxim's continuous reliability monitor program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards. The current status of the reliability monitor program can be viewed at <http://www.maxim-ic.com/TechSupport/dsreliability.html>.

Device Description:

A description of this device can be found in the product data sheet. You can find the product data sheet at http://dbserv.maxim-ic.com/l_datasheet3.cfm.

Reliability Derating:

The Arrhenius model will be used to determine the acceleration factor for failure mechanisms that are temperature accelerated.

$$AfT = \exp((Ea/k) * (1/Tu - 1/Ts)) = tu/ts$$

AfT = Acceleration factor due to Temperature
tu = Time at use temperature (e.g. 55°C)
ts = Time at stress temperature (e.g. 125°C)
k = Boltzmann's Constant (8.617 x 10⁻⁵ eV/°K)
Tu = Temperature at Use (°K)
Ts = Temperature at Stress (°K)
Ea = Activation Energy (e.g. 0.7 ev)

The activation energy of the failure mechanism is derived from either internal studies or industry accepted standards, or activation energy of 0.7ev will be used whenever actual failure mechanisms or their activation energies are unknown. All deratings will be done from the stress ambient temperature to the use ambient temperature.

An exponential model will be used to determine the acceleration factor for failure mechanisms, which are voltage accelerated.

$$AfV = \exp(B * (Vs - Vu))$$

AfV = Acceleration factor due to Voltage
Vs = Stress Voltage (e.g. 7.0 volts)
Vu = Maximum Operating Voltage (e.g. 5.5 volts)
B = Constant related to failure mechanism type (e.g. 1.0, 2.4, 2.7, etc.)

The Constant, B, related to the failure mechanism is derived from either internal studies or industry accepted standards, or a B of 1.0 will be used whenever actual failure mechanisms or their B are unknown. All deratings will be done from the stress voltage to the maximum operating voltage. Failure rate data from the operating life test is reported using a Chi-Squared statistical model at the 60% or 90% confidence level (Cf).

The failure rate, Fr, is related to the acceleration during life test by:

$$Fr = X / (ts * AfV * AfT * N * 2)$$

X = Chi-Sq statistical upper limit
N = Life test sample size

Failure Rates are reported in FITs (Failures in Time) or MTTF (Mean Time To Failure). The FIT rate is related to MTTF by:

$$MTTF = 1/Fr$$

NOTE: MTTF is frequently used interchangeably with MTBF.

The calculated failure rate for this device/process is:

FAILURE RATE:	MTTF (YRS):	46673	FITS:	2.4
	DEVICE HOURS:	397208	FAILS:	0

Only data from Operating Life or similar stresses are used for this calculation.

The parameters used to calculate this failure rate are as follows:

Cf: 60% **Ea: 0.7** **B: 0** **Tu: 25 °C** **Vu: 3.6 Volts**

The reliability data follows. At the start of this data is the device information. The next section is the detailed reliability data for each stress. The reliability data section includes the latest data available and may contain some generic data. **Bold** Product Number denotes specific product data.

Device Information:

Process: E35X-3P3M,DPE2,CrSi,DSD,PDES,D,PDRES,Cap,ENPN,DPT,HTO,SgHalo
 Passivation: TEOS Ox-Nit Passivation for E35X; Full BEOL at SA; PT only in Dallas
 Die Size: 104 x 113
 Number of Transistors: 43755
 Interconnect: Aluminum / 0.5% Copper
 Gate Oxide Thickness: 120 Å

DATA RETENTION

DESCRIPTION	DATE	CODE/PRODUCT/LOT	CONDITION	READPOINT	QTY	FAILS	FA#
STORAGE LIFE	0711	DS3650 QK647632	150C	1000 HRS	77	0	
STORAGE LIFE	0715	DS3605 QK726201	150C	1000 HRS	77	0	
STORAGE LIFE	0747	DS3655 QS709624	150C	1000 HRS	77	0	
STORAGE LIFE	0822	MAX17041 QJ839631B	150C	1000 HRS	77	0	
STORAGE LIFE	0827	DS3610 QK813039	150C	1000 HRS	77	0	
STORAGE LIFE	0830	DS3645 QC845089	150C	1000 HRS	77	0	
Total:						0	

ELECTRICAL CHARACTERIZATION

DESCRIPTION	DATE	CODE/PRODUCT/LOT	CONDITION	READPOINT	QTY	FAILS	FA#
ESD SENSITIVITY	0715	DS3605 QK726201	EOS/ESD S5.1 HBM 500 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0715	DS3605 QK726201	EOS/ESD S5.1 HBM 1000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0715	DS3605 QK726201	EOS/ESD S5.1 HBM 2000 VOLTS	1 PUL'S	3	0	
ESD SENSITIVITY	0715	DS3605 QK726201	EOS/ESD S5.1 HBM 3000 VOLTS	1 PUL'S	3	3	No FA
ESD SENSITIVITY	0715	DS3605 QK726201	EOS/ESD S5.1 HBM 4000 VOLTS	1 PUL'S	3	3	No FA

LATCH-UP	0715	DS3605	QK726201	JESD78, I-TEST 125C	6	0
LATCH-UP	0715	DS3605	QK726201	JESD78, V-SUPPLY TEST 125C	6	0
Total:					6	0

OPERATING LIFE

DESCRIPTION	DATE	CODE/PRODUCT/LOT	CONDITION	READPOINT	QTY	FAILS	FA#
HIGH TEMP OP LIFE	0702	DS1865	QJ631615A 125C, 5.5 VOLTS	192 HRS	77	0	
HIGH TEMP OP LIFE	0711	DS3650	QK647632 125C, 3.0V (PSB) & 3.6V (PSA)	1000 HRS	45	0	
HIGH TEMP OP LIFE	0715	DS3605	QK726201 125C, 3.6 VOLTS	1000 HRS	45	0	
HIGH TEMP OP LIFE	0719	DS1091L	QJ721459A 125C, 3.6 VOLTS	1000 HRS	45	0	
HIGH TEMP OP LIFE	0719	DS1091L	QJ721459A 125C, 3.6 VOLTS	1000 HRS	32	0	
HIGH TEMP OP LIFE	0732	DS1099	IJ611604AF 125C, 5.5 VOLTS	408 HRS	45	0	
HIGH TEMP OP LIFE	0732	DS1099	IJ611604AF 125C, 5.5 VOLTS	408 HRS	32	0	
HIGH TEMP OP LIFE	0745	DS1099	VD736413A 125C, 5.5 VOLTS	240 HRS	45	0	
HIGH TEMP OP LIFE	0747	DS3655	QS709624 125C, 3.6V (PSA) & 3.0V (PSB)	1000 HRS	45	0	
HIGH TEMP OP LIFE	0810	DS1875	QJ751639A 125C, 5.5 VOLTS	192 HRS	77	0	
HIGH TEMP OP LIFE	0822	MAX17041	QJ839631B 125C, 5.5V (PSA) & 9.2V (PSB)	192 HRS	45	0	
HIGH TEMP OP LIFE	0827	DS3610	QK813039 125C, 3.6 VOLTS	1000 HRS	45	0	
HIGH TEMP OP LIFE	0830	DS3645	QC845089 125C, 3.6V (PSA) & 3.3V (PSB)	1000 HRS	45	0	
HIGH TEMP OP LIFE	0832	DS2776	QJ823626B 125C, 8.4V (PSB) & 4.2V (PSA)	192 HRS	77	0	
Total:						0	

FAILURE RATE:	MTTF (YRS):	46673	FITS:	2.4
	DEVICE HOURS:	397208	FAILS:	0