



The **LT<sup>®</sup>1016** data sheet has been modified. The packaging information has been updated. Change  $T_{JMAX}$  for the N8 package and the S8 package from 100°C to **125°C**. Change  $\theta_{JA}$  for the S8 package from 120°C/W to **150°C/W**. Also, **omit Note #2** for the S8 package, "LEAD MATERIAL: A-42, TIN PLATED." The correct version for this page is shown below.

 LTC and LT are registered trademarks of Linear Technology Corporation.

## PACKAGE INFORMATION

Dimensions in inches (millimeters) unless otherwise noted.


### N8 Package 8-Lead PDIP (Narrow 0.300) (LTC DWG # 05-08-1510)



\*THESE DIMENSIONS DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS.  
MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED 0.010 INCH (0.254mm)

$$T_{JMAX} = 125^{\circ}\text{C}, \theta_{JA} = 130^{\circ}\text{C}$$

### S8 Package 8-Lead Plastic Small Outline (Narrow 0.150) (LTC DWG # 05-08-1610)



\*DIMENSION DOES NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.006" (0.152mm) PER SIDE

\*\*DIMENSION DOES NOT INCLUDE INTERLEAD FLASH. INTERLEAD FLASH SHALL NOT EXCEED 0.010" (0.254mm) PER SIDE

$$T_{JMAX} = 125^{\circ}\text{C}, \theta_{JA} = 150^{\circ}\text{C/W}$$

NOTE:

1. PKG MATERIAL: PLASTIC

For further information regarding this specification notice contact:

Linear Technology Corporation  
 1630 McCarthy Blvd.  
 Milpitas, California 95035-7417  
 Attn: Product Marketing Manager  
 Phone: (408) 432-1900, Ext. 2456