



RELIABILITY REPORT
FOR
MAX6673AXK+
PLASTIC ENCAPSULATED DEVICES

July 13, 2010

MAXIM INTEGRATED PRODUCTS

120 SAN GABRIEL DR.
SUNNYVALE, CA 94086

| |
|----------------------------------|
| Approved by |
| Don Lipps |
| Quality Assurance |
| Manager, Reliability Engineering |

Conclusion

The MAX6673AXK+ successfully meets the quality and reliability standards required of all Maxim products. In addition, Maxim's continuous reliability monitoring program ensures that all outgoing product will continue to meet Maxim's quality and reliability standards.

Table of Contents

| | |
|--|---|
| I.Device Description | V.Quality Assurance Information |
| II.Manufacturing Information | VI.Reliability Evaluation |
| III.Packaging Information | IV.Die Information |
|Attachments | |

I. Device Description

A. General

The MAX6672/MAX6673 are low-current temperature sensors with a single-wire output. These temperature sensors convert the ambient temperature into a 1.4kHz PWM output, which contains the temperature information in its duty cycle. The MAX6672 has an open-drain output and the MAX6673 has a push-pull output. The MAX6672/MAX6673 operate from 2.4V to 5.5V with a maximum supply current of 150 μ A. Both devices feature a single-wire output that minimizes the number of pins necessary to interface with a microprocessor. The MAX6672/MAX6673 are available in 5-pin SC70 packages.

II. Manufacturing Information

| | |
|----------------------------------|---|
| A. Description/Function: | PWM Output Temperature Sensors in SC70 Packages |
| B. Process: | B8 |
| C. Number of Device Transistors: | |
| D. Fabrication Location: | California or Texas |
| E. Assembly Location: | Malaysia, Thailand |
| F. Date of Initial Production: | October 25, 2002 |

III. Packaging Information

| | |
|--|--------------------------|
| A. Package Type: | 5-pin SC70 |
| B. Lead Frame: | Alloy42 |
| C. Lead Finish: | 100% matte Tin |
| D. Die Attach: | Conductive |
| E. Bondwire: | Au (1 mil dia.) |
| F. Mold Material: | Epoxy with silica filler |
| G. Assembly Diagram: | #05-2901-0032 |
| H. Flammability Rating: | Class UL94-V0 |
| I. Classification of Moisture Sensitivity per JEDEC standard J-STD-020-C | Level 1 |
| J. Single Layer Theta Ja: | 324°C/W |
| K. Single Layer Theta Jc: | 115°C/W |
| L. Multi Layer Theta Ja: | n/a |
| M. Multi Layer Theta Jc: | n/a |

IV. Die Information

| | |
|----------------------------|---|
| A. Dimensions: | 31 X 30 mils |
| B. Passivation: | Si ₃ N ₄ /SiO ₂ (Silicon nitride/ Silicon dioxide) |
| C. Interconnect: | Al/0.5%Cu with Ti/TiN Barrier |
| D. Backside Metallization: | None |
| E. Minimum Metal Width: | 0.8 microns (as drawn) |
| F. Minimum Metal Spacing: | 0.8 microns (as drawn) |
| G. Bondpad Dimensions: | 5 mil. Sq. |
| H. Isolation Dielectric: | SiO ₂ |
| I. Die Separation Method: | Wafer Saw |

V. Quality Assurance Information

- A. Quality Assurance Contacts: Don Lipps (Manager, Reliability Engineering)
Bryan Preeshl (Managing Director of QA)
- B. Outgoing Inspection Level: 0.1% for all electrical parameters guaranteed by the Datasheet.
0.1% For all Visual Defects.
- C. Observed Outgoing Defect Rate: < 50 ppm
- D. Sampling Plan: Mil-Std-105D

VI. Reliability Evaluation

A. Accelerated Life Test

The results of the 135°C biased (static) life test are shown in Table 1. Using these results, the Failure Rate (λ) is calculated as follows:

$$\lambda = \frac{1}{\text{MTTF}} = \frac{1.83}{192 \times 4340 \times 76 \times 2} \quad (\text{Chi square value for MTTF upper limit})$$

(where 4340 = Temperature Acceleration factor assuming an activation energy of 0.8eV)

$$\lambda = 14.5 \times 10^{-9}$$
$$\lambda = 14.5 \text{ F.I.T. (60\% confidence level @ 25°C)}$$

The following failure rate represents data collected from Maxim's reliability monitor program. Maxim performs quarterly life test monitors on its processes. This data is published in the Reliability Report found at <http://www.maxim-ic.com/qa/reliability/monitor>. Cumulative monitor data for the B8 Process results in a FIT Rate of 0.06 @ 25C and 0.99 @ 55C (0.8 eV, 60% UCL)

B. Moisture Resistance Tests

The industry standard 85°C/85%RH or HAST testing is monitored per device process once a quarter.

C. E.S.D. and Latch-Up Testing

The TS14-1 die type has been found to have all pins able to withstand a HBM transient pulse of +/-1500V per Mil-Std 883 Method 3015.7. Latch-Up testing has shown that this device withstands a current of +/-250mA.

Table 1
Reliability Evaluation Test Results

MAX6673AXK+

| TEST ITEM | TEST CONDITION | FAILURE IDENTIFICATION | SAMPLE SIZE | NUMBER OF FAILURES |
|-----------------------------------|---|-------------------------------|-------------|--------------------|
| Static Life Test (Note 1) | | | | |
| | Ta = 135°C Biased Time = 192 hrs. | DC Parameters & functionality | 76 | 0 |
| Moisture Testing (Note 2) | | | | |
| HAST | Ta = 130°C RH = 85% Biased Time = 96hrs. | DC Parameters & functionality | 77 | 0 |
| Mechanical Stress (Note 2) | | | | |
| Temperature Cycle | -65°C/150°C 1000 Cycles Method 1010 | DC Parameters & functionality | 77 | 0 |

Note 1: Life Test Data may represent plastic DIP qualification lots.

Note 2: Generic Package/Process data