



WIDEBAND SDLVAs

Analog & Mixed-Signal ICs, Modules, Subsystems & Instrumentation

Tiny SDLVAs Tackle 20-GHz Bandwidth



Tiny SDLVAs Tackle 20-GHz Bandwidth

These high-performance successive-detection log-video amplifiers (SDLVAs) offer outstanding wide frequency ranges and dynamic ranges with low power consumption in compact housings.

Military system designers are often faced with processing input signals over a wide dynamic range. With many systems, such as direct-finding (DF) receivers, electronic-intelligence (ELINT) receivers, electronic-countermeasures (ECM) systems, radar warning receivers (RWRs), and commercial instrumentation, it is often necessary to capture and analyze narrow pulses with large variations in amplitude. Traditionally, the successive detection log video amplifier (SDLVA) is the component of choice for this task.

Today, when system designers need a high-performance SDLVA, they have two more choices with outstanding performance over the wide frequency range of 0.1 to 20.0 GHz. The SDLVA models HMC613LC4B and HMC-C052 from Hittite Microwave Corp. (Chelmsford, MA) are supplied in a compact 4 x 4 mm ceramic package and miniature hermetic module. Respectively, both offer the signal-processing capability needed to capture and analyze narrow, high-speed RF pulses over wide dynamic ranges. The small size and low power requirements of these SDLVA solutions allows designers to incorporate this function into systems once limited to alternative signal-processing approaches, such as portable systems.



Figure 1. Model HMC613LC4B is a surface-mount SDLVA (shown mounted to a PCB) that operates from 100 MHz to 20 GHz.



Figure 2. Model HMC-C052 is a miniature connectorized SDLVA module that operates from 1 to 20 GHz.

The HMC613LC4B SDLVA operates over the 0.1 to 20 GHz frequency range and provides a logging range of 62 dB. It consumes only 83 mA current from a single +3.3V DC supply when processing RF signals at -30 dBm input power. Ideal for EW and ELINT applications, the HMC613LC4B is capable of processing RF pulses in the 0.1 to 20.0 GHz frequency band with amplitudes from -57 to +5 dBm with only 4 ns rise times and 26 ns of recovery time.

The HMC613LC4B employs a successive compression topology which delivers extremely high dynamic range and conversion accuracy over its wide input frequency range (Fig. 3). As the input power is increased, successive RF amplifier stages move into saturation one by one creating an accurate approximation of the logarithmic function. The output of a series of detectors is summed into a single video amplifier for the purpose of providing a single detected output. When the HMC613LC4B is used in detection mode, the VIDEO OUT pin is connected to the Video FB pin via a 0Ω resistor, providing a nominal logarithmic slope of 14 mV/dB and a typical intercept of -119 dBm at 10 GHz. The output gain stage of the HMC613LC4B may be modified by connecting appropriate

TINY SDLVAs TACKLE 20 GHz BANDWIDTH!

Wideband SDLVAs, 0.01 - 20 GHz




Figure 3. This block diagram shows the various functions of the HMC613LC4B SMT SDLVA.

external resistors between the VIDEO OUT and the VIDEO FB pin, and also between the VIDEO FB pin and ground. The HMC613LC4B also provides an EN (enable) pin, which is connected to Vcc (+3.3 VDC) during normal operation. If the enable pin is connected to ground, the SDLVA is disabled, and the total supply current is reduced to less than 3 mA. This is a useful feature for controlling total system power, particularly in high-speed channelized receiver designs, where multiple channels/SDLVAs are deployed.

Figures 4 and 5 show the typical logarithmic error and video output voltage performance of the HMC613LC4B over the -40 to +85°C operating temperature range at 2 and 20 GHz. The typical flatness over the 2-to-20-GHz band from -55 to +5 dBm is shown in Fig. 6. Measurements on the HMC613LC4B typically reveal better than ± 2 dB flatness to 20 GHz at a -30-dBm input-power level. The maximum temperature-related deviation is ± 1 dB at any given frequency and power level over the full operating temperature range.

The HMC-C052 integrates the HMC613 bare die, a linear regulator IC, and off-chip components within a hermetically sealed package that can be used as a connectorized module (2.92 mm or SMP connectors) or as a MIC drop-in design. The HMC-C052 operates from 1 to 20 GHz and draws only 86 mA of current from a single +7 to +16 VDC supply. (The table compares the key specifications of the HMC613LC4B and the HMC-C052 SDLVAs.) The HMC-C052 operates from -55 to +85°C and is housed in a miniature 22.6 x 21.6 x 5.84 mm package.

The miniature HMC-C052 module represents a space savings of more than 85 percent compared with existing typical broadband connectorized SDLVA modules with similar performance (Fig. 7). The connectorized HMC-C052 module can immediately replace existing broadband SDLVA modules, resulting in a lower-cost,




Figure 4. This plot shows the video output and log error vs. input power at 2 GHz for the HMC613LC4B SDLVA.




Figure 5. This plot shows the video output and log error vs. input power at 20 GHz for the HMC613LC4B SDLVA.




Figure 6. This plot shows gain error flatness vs. input power from 0.1 to 20 GHz for the HMC613LC4B SDLVA.

TINY SDLVAs TACKLE 20 GHz BANDWIDTH!

Wideband SDLVAs, 0.01 - 20 GHz

Figure 7. A traditional, MIC hybrid-based SDLVA (top) requiring both positive and negative DC power supplies is shown with the HMC-C052 SDLVA module and the HMC613LC4B SMT SDLVA.



reduced-power-dissipation (heat) solution occupying a significantly smaller form factor.

Hittite Microwave's design philosophy involves the careful selection of the best semiconductor processes and design techniques available for each component solution ensuring the delivery of market-leading product performance. This performance improvement allows the systems designer to maximize the true potential of the design to ultimately deliver a superior product. The block diagram for a RWR (Fig. 8) shows how a system design can be optimized by careful selection of Hittite Microwave catalog components. In this application example, the

RWR combines signal filtering, amplification, detection, and frequency measurement into one multifunction unit. In such a design, a system engineer is often seeking to reduce power consumption along with the overall size and weight of the RWR module. Any reduction in power consumption and weight renders a double benefit, particularly in airborne or unmanned-aerial-vehicle (UAV) applications, as a smaller, lighter power supply is required. The HMC613LC4B or the HMC-C052 SDLVAs are key components required to implement the RWR function, and compared with traditional SDLVA solutions, provide significant savings in both power consumption and size for equivalent performance.

Table: Comparing the HMC613LC4B and HMC-C052.

| Parameter | HMC613LC4B | HMC-C052 |
|--|----------------------|------------------------|
| Input frequency range | 0.1 to 20.0 GHz | 1.0 to 20.0 GHz |
| Logging range | 62 dB | 59 dB |
| Logarithmic range (± 3 dB) ¹ | -57 to +5 dBm | -54 to +5 dBm |
| Logarithmic slope | 14 mV/dB | 14 mV/dB |
| Frequency flatness at -30 dBm RF input power | ± 2 dB | ± 2 dB |
| Logarithmic error over temperature | ± 1 dB | ± 1 dB |
| Rise/fall time | 4/18 ns ² | 2/7 ns ³ |
| Recovery time | 26 ns | 21 ns |
| Output voltage | 1.0 to 1.8 V | 0.9 to 1.5 V |
| Bias supply | +3.3 VDC at 83 mA | +7 to +12 VDC at 86 mA |


Note 1: Based on linear regression of error curve from input power of -40 dBm to input power of -10 dBm.

Note 2: Rise/fall times measured from no power to 0 dBm.

Note 3: Rise/fall times measured from no power to -20 dBm.

TINY SDLVAs TACKLE 20 GHz BANDWIDTH!

Wideband SDLVAs, 0.01 - 20 GHz



The HMC613LC4B or the HMC-C052 SDLVA can be combined with a number of additional high-performance catalog components from Hittite Microwave to implement an RWR capable of measuring signals from 2 to 20 GHz. The simplified block diagram of Fig. 8 shows two amplitude measurement channels which allow direction finding by comparing the signal amplitude of the adjacent antennas. One of the amplitude channels is selected via the HMC547LP3E single-pole, double-throw (SPDT) switch and feeds the RWR's instantaneous-frequency-measurement (IFM) circuit, thus performing a frequency measurement on an antenna pair. The HMC613LC4B SDLVAs provide the logarithmic video voltage signals which are usually digitized with a series of comparator circuits, prior to further processing. To meet military/high-reliability or ruggedized system requirements, the RWR function may be implemented with hermetically sealed, connectorized modules (labeled in red) which are available as stock items.

The SDLVA models HMC613LC4B and HMC-C052 combine wide input bandwidths, wide dynamic range, and fast rise/fall times with extremely compact packaging for system-level designers seeking alternatives to traditional microwave-integrated-circuits (MIC) hybrid and discrete-based SDLVAs. The HMC613LC4B and HMC-C052 facilitate accurate logarithmic power measurement of RF signals in the 0.1-to-20-GHz and 1-to-20-GHz frequency ranges, respectively, in commercial, military, and space applications, especially where DC power is a constraining factor. These SDLVAs are also ideal for a myriad of applications

including RWRs, DF receivers, IFM receivers, EW and ECM systems, phased-array antennas, radar altimeters, digital frequency discriminator circuits, and RF test and measurement equipment.

In addition to these new SDLVA products, Hittite Microwave continues to expand its product portfolio and designers can now choose from more than 700 standard products spanning the frequency range from DC to 110 GHz. The portfolio includes 18 product lines: amplifiers, attenuators, data converters, frequency dividers and detectors, frequency multipliers, high-speed logic, interface ICs, modulators and demodulators, mixers and converters, oscillators, passive devices, phase shifters, phase-locked loops (PLLs), power detectors, sensors, switches, frequency synthesizers, and variable-gain amplifiers (VGAs). Data sheets and detailed product information for all Hittite products are available on-line at the Hittite Microwave Corp. website at www.hittite.com.

Hittite Microwave Corporation
 20 Alpha Road Chelmsford, MA 01824
 Phone: (978) 250-3343 Fax: (978) 250-3373
sales@hittite.com www.hittite.com



CONNECTING OUR WORLD THROUGH INTEGRATED SOLUTIONS

SALES CONTACT INFORMATION:

Hittite Microwave Worldwide Sales Offices

**Hittite Microwave Corporation
USA Corporate Headquarters**
Phone: 978-250-3343
Fax: 978-250-3373
sales@hittite.com

Central North America
Phone: 817-727-7146
usa-central@hittite.com

Eastern North America
Phone: 978-337-1226
usa-east@hittite.com

Western North America
Phone: 978-808-0652
usa-west@hittite.com

**Western & Southern Europe
Hittite Microwave Europe Limited**
Phone: +44 870 7664355
Fax: +44 870 7664356
europe@hittite.com

**Northern Europe
Hittite Microwave Europe Limited**
Phone: +44-7811-267418
Fax: +978-250-3373
nordic@hittite.com

**Central & Eastern Europe
Hittite Microwave Deutschland GmbH**
Phone: +49 8031-97654
Fax: +49 8031-98883
germany@hittite.com

**Republic of Korea
Hittite Microwave Asia Co., Limited**
Phone: +82 2559-0638
Fax: +82 2559-0639
korea@hittite.com

**Peoples Republic of China
Hittite Microwave Co., Limited**
Shanghai Office
Phone: +86 21 6209-8809
Fax: +86 21 6209-6730
china@hittite.com

Shenzhen Office
Phone: +86 755 3322-2116
Fax: +86 755 3322-2117
shenzhen@hittite.com

**Japan
Hittite KK**
Phone: +81-3-6853-6654
japan@hittite.com

Hittite Microwave Sales Representatives

NORTH AMERICA

CANADA;

Repwave
Calgary, Ottawa & Montreal:
+613-270-9811
Toronto:
+647-883-7360
Vancouver:
+604-929-8541

USA North East & Mid-Atlantic;

CT, MA, ME, E. PA, NH,
So. NJ, RI & VT:
Microwave Marketing Specialist
978-392-0110
GTEK, LLC (Instrumentation Only)
978-692-4954
Western NY:
Zimmerman Sales
585-385-2103
So. CT, Metro LI & No. NJ:
Comp Tech
201-288-7400
W. PA
Schillinger Associates, Inc.
765-457-7241
DC, DE, MD, VA & WV:
Vincent Pirro Electronics
410-489-9554

USA Mid-West;

IA
Essig & Associates
319-363-8703
KS & W. MO
Quad State Sales & Marketing
978-499-1711
IL & WI:
TEQ Sales
847-742-3767

IN, KY, MI & OH:
Schillinger Associates, Inc.
765-457-7241

MN, ND, SD & NE:
HMC Central
817-727-7146

USA South East;

FL:
Spartech South
321-727-8045
GA, NC, SC, TN, AL & MS:
RFM Marketing Inc.
770-267-1295

USA South West;

TX, OK, LA & AR:
NW Sales, LP.
817-483-5676
AZ & NM:
Saguaro Technical Sales, Inc.
480-947-3724

USA West;

No. CA & NV:
Custom & Wireless Sales
408-371-0222
So. CA:
Acetec
858-784-0900
OR & WA:
Sea-Port Technical Sales
425-702-8300
CO, ID, UT, MT & WY:
Hittite Central North America
978-817-727-7146

EUROPE, MID-EAST & AFRICA

Benelux, Greece & Turkey:
Hittite Microwave Europe Limited
+44 870 7664355

Slovenia, Serbia Montenegro,
Croatia, Bosnia Herzegovina,
Bulgaria, Macedonia & Romania,
IC Electronika
+386(0) 1 568-01-20

Sweden, Finland, Norway & Denmark:
Hittite Microwave Europe Limited
+44-7811-267418

Finland:
LKC OY
+358-400-460-646

France:
Salies SA
+33-1-69-02-2560
MB Electronique
(Fiber Optic & Instrumentation Only)
+011-39-67-6759

Germany, Austria, Latvia, Lithuania, Estonia,
Poland, Czech Republic, Slovakia, Hungary,
& Switzerland:

Hittite Microwave Deutschland GmbH
+49 8031-97654

Israel:
Starlight Technologies, Inc.
+972-3-9410555

Italy:
Special-Ind SPA
+39-02-6074741

Norway:
Bredengen AS
+47-2100-9100

Russia
Radiant-Elcom Ltd.
+7(495) 725-0404

Spain & Portugal:
Altaix Electronica S.A.I.
+34-91-636-39-39

South Africa:
RF Design Laboratory CC
+27-21-555-8400

United Kingdom & Ireland:
Link Microtek Ltd
+44-1256-355-771

ASIA & SOUTH PACIFIC

Australia & New Zealand:
Braemac
+61-8-8301-8450

China & Hong Kong:
Secom Telecom Co., Ltd.
+86-755-25155888

Wai Tat Electronics Ltd.
+852-2799-7393

India:
Syratron
+91-802-5591107/5591031

Indonesia, Malaysia,
Philippines & Singapore
MEDs Technologies, Pte., Ltd.
+65-6453-8313

Japan:
Saint Technology
+81-3-5330-6411
AMT Incorporated
+81-742-30-0070

Korea:
JS Commtech
+82-2-574-6100
EZ Hightech
+82-031-382-6500

Taiwan R.O.C.:
Bandtek International Co., Ltd.
+886-2-2657-2615

Order On-line at: www.hittite.com

© 2008, Hittite Microwave Corporation, All Rights Reserved.
20 Alpha Road, Chelmsford, MA 01824 Phone: 978-250-3343 Fax: 978-250-3373

Boston • Colorado Springs • Istanbul • Tokyo • London
Munich • Ottawa • Seoul • Shanghai