Condition-Based Monitoring

Complete System-Level Solutions from Sensing to Artificial Intelligence

Condition-based monitoring (CbM), often referred to as condition monitoring, enables early detection and diagnosis of machine and system abnormalities in real time. Identifying and isolating these issues creates opportunities for optimizing replacement part inventories, scheduling downtime for planned maintenance, and making run-time process adjustments that can extend the useful life of the equipment.

The Impact of Condition Monitoring





Increased Asset Life



Reduced Maintenance Cost



11

Reduced Downtime



VISIT ANALOG.COM



Vibration, current, and temperature all provide key insights into the health of equipment ranging from motors and pumps to bearings and encoders. Vibration measurements are also a source of additional data by further isolating mechanical noise from electrical noise, improving machine diagnostics.

These machine health insights result in increased productivity, improved efficiency, and maximized uptime, accelerating the path to Industry 4.0. Data from a multitude of sensors are often fused to deliver cutting edge insights into asset health.



Sensing Modalities

ADI's accelerometers and iSensor® MEMS accelerometer subsystems provide accurate detection while measuring acceleration, tilt, shock, and vibration in performance driven applications.



Edge Processing

oold hote

Maxim Integrated's ultra low power MCUs offer intelligence at the edge nodes for condition monitoring applications by enabling local decision making, thereby extending battery life.

Power Management

| _ | |
|----|--|
| | |
| 14 | |
| 7/ | |
| گ | |

Analog Devices and Maxim Integrated low complexity power management solutions help our customers accelerate time to market while achieving high efficiency performance.

Artificial Intelligence at the Edge

MILT



ADI's artificial intelligence solution enables continuous real-time monitoring of any asset at the edge, using sound and vibrations, leveraging AI models designed with the ADI OtoSense visual toolkit.

Data Acquisition

ADI provides an unrivalled portfolio of precision converters that enable the detection of potential fault conditions earlier in their life cycle.

Wired/Wireless Connectivity




Tan

SmartMesh[®], IO-Link[®], Industrial Ethernet, and other wireless and wired connectivity options from Analog Device and Maxim Integrated enable seamless connectivity that delivers critical data with high reliability.


Asset Monitoring

Our asset monitoring solutions detect, measure, and communicate critical information to enable predictive maintenance for assets.






Analog Devices accelerometers accurately detect and measure acceleration, tilt, shock, and vibration in condition monitoring applications. ADI's portfolio leads the industry in power, noise, bandwidth, and temperature specifications, and it offers a range of MEMS sensor and signal conditioning integration on chip.




Analog Devices provides an unrivaled portfolio of precision converters that enable the detection of potential fault conditions earlier in their life cycle. Extend the life of equipment and maximize operational efficiency with precision technology from ADI.

| | ADI Precision Products | The ADI Advantage | | | | |
|------------|--|-----------------------------|---------------------------------------|--|--|--|
| AD7768-1 | 1-channel, 24-bit, 255 kSPS, simultaneous sampling ADC with power scaling | 0 0 | ŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢŢ | | | |
| AD7768-4 | 4-channel, 24-bit, 255 kSPS, simultaneous sampling ADC with power scaling | Repeatibility and Stability | Small Footprint | | | |
| AD4008 | 1-channel, 16-bit, 500 kSPS, pseudo differential SAR ADCs | Repeatibility and Stability | | | | |
| ADAQ7768-1 | 1-channel, 24-bit 256 kSPS, μModule° data acquisition system | | | | | |
| ADAQ7988 | 1-channel, 16-bit, 500 kSPS, μModule data acquisition system | Low Power | Wide Resolution Range | | | |
| | | | | | | |

Data Acquisition-System Architecture Options






³ IO Link and Low Power Processing

IO-Link combines with low power processing to simplify communication to smart CbM sensors in smart manufacturing. By joining signaling power over-cable technology, IO-Link also eases installation. Analog Devices and Maxim Integrated provide solutions for both device PHY and master PHY interfaces.

IO-Link in condition monitoring applications enables simplified installation by removing the need for control cabinets and extensive wiring while providing accurate asset health data with automated alerts to monitor the health of assets.




(•)) Wireless

ADI's SmartMesh[®] technology enables highly scalable, self-forming mesh networking for sensors in a tough Industrial Ethernet of Things environment.

- ► >99.999% data reliability in the most challenging RF environments.
- >10-year battery life, so sensors can be placed anywhere with the lowest cost.
- Encryption, authentication, and message integrity checks for a secured network.
- A complete wireless mesh solution, so no network stack development is required.

| LTC5800-WHM | SmartMesh WirelessHART mote-on-chip |
|-------------|--|
| LTP5901-WHM | SmartMesh IP Wireless 802.15.4e PCBA module with antenna connector |

SmartMesh Network with Voyager 3 Motes






Industrial Ethernet

Robust Ethernet connectivity will dramatically change the automation industry by significantly improving operational efficiency through seamless Ethernet connectivity to field-level assets. Ethernet will enable new asset health insights that were previously unavailable and seamlessly communicate them to the control layer and to the cloud/private server.

These new insights will awaken new possibilities for data analysis, operational insights, and productivity improvements through a converged Ethernet network from the field assets to the cloud or private server.

Physical Layer Devices

| | Bandwidth (Mbps) | Interface | Typical Power Consumption (mW) |
|----------|---------------------|----------------|--------------------------------------|
| ADIN1110 | 10 | SPI | 42 |
| ADIN1100 | 10 | MII/RMII/RGMII | 39 |
| ADIN1200 | 10/100 | MII/RMII/RGMII | 139 |




Power Management

+ -

Our high performance power management solutions meet stringent power requirements with leading-edge design and packaging technologies, including unmatched power densities, ultralow noise technology, and superior reliability.

These features ensure systems operate at their optimal efficiency, speed, and power levels, while increasing feature density and reducing cost of ownership.

ADI and Maxim Integrated's low complexity power management solutions help our customers accelerate time-to-market while delivering best-in-class performance.



Your Trusted Power Solutions Partner



ADP5054 LT8604 LT8604 ADP5054 High Efficiency, 42 V/120 mA Quad Buck Regulator Integrated Power Solution Synchronous Buck -ANALOG ADP7118 LT3502 ADP7118 LT3502 20 V, 200 mA, Low Noise, 1.1 MHz, 500 mA Step-Down Regulator CMOS LDO Linear Regulator in a 2 mm × 2 mm DFN Package



Condition-Based Monitoring Development Platforms Ecosystem


Condition-based monitoring reference designs and development platforms combine the necessary technologies with the tools and software required to quickly collect data, perform analysis, and customize solution designs for specific applications.

Development

Hardware design files and firmware/software source code is made available, enabling customized development based on the underlying evalution system.

Support

All the supporting documentation, including hardware and software files, is available from Analog Devices. Alternatively, you can reach out to us via EngineerZone.[®]



ADI CbM Reference Designs and Platforms

| | Sensor | Signal Chain | Signal Processing | Communications | Mechanical Sensor Attach | System Enclosure Rating | Machine Learning/ Algorithms | AI | Design Files |
|--|------------|----------------------|----------------------|------------------------|--------------------------------|--|--|----|--|
| CN0533 | ADXL1002 | | | 4 mA to 20 mA | | | | | Image: A second s |
| CN0549—CbM Vibration Development Platform | ADXL1002 | ~ | ~ | IEPE | ~ | | | | ~ |
| EVAL-CN0532-EBZ | ADXL1002 | | | Wired-EPE | | | | | |
| EVAL-CN0540-ARDZ | IEPE Type | | | Wired–IEPE, SPI | | | | | |
| EV-CBM-VOYAGER3 | ADXL356 | ~ | | Wireless— SmartMesh | ~ | | | | ~ |
| EV-CBM-PIONEER1-1Z | ADcmXL3021 | | | Wired-RS-485 | | | | | Image: A second s |
| ADI OtoSense SMS | ADXL1002 | | | Wireless-WiFi | | Image: A second s | Image: A second s | ~ | |

EV-CBM-VOYAGER3

MEMS-based wireless vibration monitoring kit for accelerating asset monitoring and solution development.



CN0549 CN0549 provides a high performance sensor and data acquisition system for real-time data analysis.



EV-CBM-PIONEER1

The platform provides a complete plug and play solution for operating the ADcmXL3021 on an RS-485 network.



ADI OtoSense SMS

ADI OtoSense Smart Motor Sensor (SMS) detects anomalies and defects in motors by analyzing the real-time data, thereby reducing unplanned downtime.





For regional headquarters, sales, and distributors or to contact customer service and technical support, visit analog.com/contact.

Ask our ADI technology experts tough questions, browse FAQs, or join a conversation at the EngineerZone Online Support Community. Visit ez.analog.com.

©2021 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners. VISIT ANALOG.COM

BR22920-9/21