

REVISIONS			
REV	DESCRIPTION	APPROVED	DATE

NOTES: UNLESS OTHERWISE SPECIFIED

1. DIMENSIONS ARE IN INCHES (EXCEPT WHERE NOTED).

MATERIAL: (USE CHECKED ITEMS FOR MATERIAL)

2. BOARD MATERIAL:

(X) ISOLA 370HR OR EQUIVALENT

() ISOLA-FR408HR OR EQUIVALENT

() NELCO-4000-13

() MEGTRON 6

() ROGERS 4350B

() ROGERS 4003C

() OTHER _____

3. THE PCB SHALL BE FABRICATED TO IPC-6012, TYPE K, CLASS 2.

WORKMANSHIP SHALL CONFORM TO IPC-A-600, CLASS 2, CURRENT REVISIONS.

4. BOARD MATERIAL & CONSTRUCTION SHALL MEET THE REQUIREMENTS OF UL796 WITH FLAMMABILITY RATING OF 94V-0.

5. OVERALL BOARD THICKNESS REFER TO LAMINATION DIAGRAM. TOLERANCE APPLIES AFTER ALL LAMINATION AND PLATING PROCESSES. IT IS TO BE MEASURED FROM TOP PCB METAL TO BOTTOM PCB METAL UNLESS OTHERWISE SPECIFIED.

6. BOW & TWIST NOT TO EXCEED 0.0075 IN. (0.75%) PER LINEAR INCH. BOW & TWIST SHOULD BE MEASURED PER IPC-TM-650, METHOD 2.4.2.2.

TOOLING: (USE CHECKED ITEMS FOR TOOLING)

7. PHOTO ETCH CIRCUITRY PER ENCLOSED GERBER RS274X OR ODB++ FORMAT FILE. DRILL LOCATION AND SIZE CONTROLLED BY EXCELLEN CNC DRILL FILE.

8. IF STATED IN THE LAMINATION DIAGRAM, THE DIELECTRIC THICKNESS OF ANY CONTROLLED IMPEDANCE LAYER IS FOR REFERENCE ONLY. FINAL ACCEPTANCE SHALL BE DETERMINED BY THESE LAYERS HAVING A CHARACTERISTIC IMPEDANCE OF +/-10% OHMS AS STATED IN THE LAMINATION DIAGRAM. THE VENDOR CAN MAKE ADJUSTMENTS AS LONG AS THE STATED IMPEDANCE AND OVERALL BOARD THICKNESS IS MAINTAINED. ANY ADJUSTMENT MADE TO TRACE WIDTH OR SPACING MUST HAVE PRIOR WRITTEN APPROVAL FROM MAXIM.

9. ALL TRACES FILLETED OPTION TO ENHANCE RELIABILITY AT PAD JUNCTIONS WHERE SPACING PERMITS, UNLESS OTHERWISE SPECIFIED

() FILLETED

(X) NOT FILLETED

10. LAYER TO LAYER REGISTRATIONS SHALL BE WITHIN .003 INCHES. LEGEND TO LEGEND +/- .007 INCHES

FINISH: (USE CHECKED ITEMS FOR PLATING)

11. PLATING SPECIFICATION:

(X) STARTING COPPER WEIGHT FOR OUTER LAYERS TO BE (1 OZ), THE FINISH COPPER WEIGHT IS (1 OZ), FOR OUTER LAYERS WHERE SPACING PREVENTS THE USE OF (1 OZ) AS A STARTING WEIGHT THE STARTING WEIGHT CAN BE (0.5 OZ) AS LONG AS THE FINISH COPPER WEIGHT IS (1 OZ) UNLESS OTHERWISE SPECIFIED

() STARTING COPPER WEIGHT FOR OUTER LAYERS TO BE (1 OZ), THE FINISH COPPER WEIGHT IS (2 OZ), FOR OUTER LAYERS WHERE SPACING PREVENTS THE USE OF (1 OZ) AS A STARTING WEIGHT, THE STARTING WEIGHT CAN BE (0.5 OZ) AS LONG AS THE FINISH COPPER WEIGHT IS (2 OZ), UNLESS OTHERWISE SPECIFIED

() STARTING COPPER WEIGHT FOR OUTER LAYERS TO BE (2 OZ), THE FINISH COPPER WEIGHT IS (2 OZ) OR FOR OUTER LAYERS WHERE SPACING PREVENTS THE USE OF (2 OZ) AS A STARTING WEIGHT, THE STARTING WEIGHT CAN BE (<2 OZ) AS LONG AS THE FINISH COPPER WEIGHT IS (2 OZ), UNLESS OTHERWISE SPECIFIED

() OTHER _____

12. CHECK ALL THAT APPLY

() ELECTRODEPOSITED HARD GOLD PLATE, TYPE I (99.7% MIN GOLD), GRADE C (KINDUR HARDNESS 100-200), CLASS I (50-100 MICRO INCHES THICK) IN ACCORDANCE WITH MIL-G-45 (GENERAL SURFACING REQUIREMENTS MUST MEET ANSI/JPC-A-600(CURRENT REV) SECTION 4.0, CLASS 3 (50-100 MICROINCHES THICK) OVER ELECTRODEPOSITED NICKEL PLATE IN ACCORDANCE WITH ANSI/JPC-A-600D, SECTION 4.0, CLASS 3 (200-600 MICROINCHES THICK).

() FINISH CONDUCTOR SURFACES: IMMERSION GOLD, 3-8 MICRO INCHES OVER 100 MICRO INCHES MINIMUM OF ELECTROLESS NICKEL.

() FINISH CONDUCTOR SURFACES: IMMERSION GOLD, 2-5 MICRO INCHES OVER 118-236 MICRO INCHES MINIMUM OF ELECTROLESS NICKEL.

() FINGERS TO BE GOLD PLATED.

(X) LEAD FREE AND ROHS COMPLIANT PLATING.

() OTHER _____

13. DRILL SIZES ARE FINISHED HOLE SIZES. ALL HOLES SHALL BE LOCATED WITHIN .005 DTP. MINIMUM BARREL PLATING OF .001 IN. PLATED HOLES SHALL NOT BE ROUGH OR IRREGULAR SO AS TO HINDER PROPER SOLDER WELDING.

14. CHECK ALL THAT APPLY

(X) GREEN SOLDERMASK OVER BARE COPPER/BARE GOLD (BOTH SIDES) WITH LIQUID PHOTO IMAGEABLE INK PER ARTWORK.

() GREEN TAIYO PSR-4000

() OTHER _____

15. CHECK ALL THAT APPLY

(X) APPLY SILKSREEN USING A NON-CONDUCTIVE, WHITE EPOXY BASED INK PER ARTWORK.

() OTHER _____

16. VENDOR LOGO & DATE CODE REQUIRED IN INK ON BOTTOM SIDE ONLY. DATE CODE FORMAT MUST BE YYYY MM DD.

TESTING:

17. FINAL ELECTRICAL TEST TO BE PERFORMED USING PROVED IPC-D-356A NETLIST OR ODB++ FORMAT FILE. (REQUIRED UNLESS OTHERWISE SPECIFIED IN QUOTE)

THE PCB SHALL HAVE A VERIFICATION STAMP.

18. A TIME DOMAIN REFLECTOMETER REPORT FOR EACH IMPEDANCE CONTROLLED LAYER AND A CERTIFICATE OF COMPLIANCE SHALL BE PROVIDED BY VENDOR AT TIME OF SHIPMENT.

MISCELLANEOUS:

19. IF PRESENT, ALL BLIND/BURRED VIAS WITH AN ASPECT RATIO <1:1 TO BE PLATED SHUT WITH COPPER WHEN USED AS VIA-IN PAD OR AS A STACKED VIA. BLIND/BURRED VIAS WITH AN ASPECT RATIO >1:1 TO BE FILLED WITH NON-CONDUCTIVE EPOXY, UNLESS OTHERWISE SPECIFIED.

20. FOR ALL DRILL INFORMATION REFER TO DRILL CHART.

() NON-CONDUCTIVE EPOXY, FILL AND CAP ALL 0.1XX INCH DRILLED VIAS.

() SILVER, FILL AND CAP ALL 0.1XX INCH DRILLED VIAS.

21. FINISHED SURFACE CONTACTS AND FILLED VIAS TO BE FREE OF ANY PITS, SCRATCHES, PROBE MARKS OR OTHER DEFECTS THAT COULD EFFECT THE APPEARANCE AND PERFORMANCE OF THE CONTACT SURFACE. CONTACTS ARE TO BE AS FLAT AS POSSIBLE, NOT TO EXCEED +/- 0.001" OF FLATNESS.

22. THEIVING:

() SUPPLIER MAY ADD THEIVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS ON THIS DESIGN.


(X) SUPPLIER MAY ADD THEIVING TO COMPENSATE FOR LOW COPPER DENSITY AREAS ON THIS DESIGN.

23. PENNUT



() PENNUTS TO BE INSTALLED BY SUPPLIER.


() PENNUTS NOT TO BE INSTALLED BY SUPPLIER.


(X) NOT APPLICABLE

LAMINATION DIAGRAM					
LAYER NUMBER	LAYER NAME	FINISHED CU WEIGHT (OZ)	DIELECTRIC THICKNESS (IN.)	DIELECTRIC MATERIAL	
1	TOP	1		FOIL	
2	LAYER2	1		TB0	ISOLA 370HR/EQUIVALENT
3	LAYER3	1		TB0	ISOLA 370HR/EQUIVALENT
4	LAYER4	1		TB0	ISOLA 370HR/EQUIVALENT
5	BOTTOM	1			FOIL

THE FINISHED PCB THICKNESS TO BE: 0.0625" +/- 0.010"

DRILL CHART: TOP to BOTTOM				
ALL UNITS ARE IN MILS				
FIGURE	SIZE	TOLERANCE	PLATED	QTY
	12.0	+3.0/-10.0	PLATED	111
	68.898	+3.0/-3.0	PLATED	4



TOLERANCES UNLESS OTHERWISE SPECIFIED			 maxim integrated™		
FRACTIONS	DECIMALS	ANGLES			
1/16	.0625	16°			
MATERIAL:			THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO MAXIM. THE INFORMATION IN THIS DOCUMENT IS NOT TO BE SHOWN, REPRODUCED, OR DISCLOSED TO ANYONE OUTSIDE OF MAXIM WITHOUT PRIOR WRITTEN PERMISSION FROM MAXIM.		
SEE NOTES			DRAWN BY:	DATE:	HARDWARE NAME: MAXREFDES119 24VIN 5VOUT 9W FLYBACK CONVERTER
FINISH:			CHECKED BY:	DATE:	
SEE NOTES			APPR. BY:	DATE:	
			APPR. BY:	DATE:	HARDWARE NUMBER: <div> <div>NOT TO SCALE</div> <div>TEMPLATE REV B</div> <div>SHEET 1 OF 1</div> </div>