



ADRV9026

Quad-Channel, Wideband RF Transceiver Platform

200 MHz Bandwidth Integrated Radio Transceiver Solution

Smallest Size, Lowest Power Transceiver Solution for Base Transceiver Stations (BTS)

- ▶ Smallest size reduces footprint and enhances form factor flexibility
- ▶ 50% power consumption reduction over previous generation [ADRV9009](#) for increased radio density
- ▶ Enables ORAN small cell designs with lowest system power and cost

Highly Integrated, High Performance Software-Defined Radio

- ▶ 2× integration over [ADRV9009](#)
- ▶ Supports up to 200 MHz bandwidth and covers all bands from 650 MHz to 6 GHz¹

Common Platform Design for 3G/4G/5G Reduces Complexity, Development Costs, and Time to Market


- ▶ Single-chip FDD/TDD solution simplifies hardware and software development
- ▶ Common API across multiple applications
- ▶ Reduces product development cycles for band and power variants
- ▶ Enables modular architecture for scalable radio solutions

¹See page 3 for future enhancements in the ADRV902x family roadmap

Applications

- ▶ Macro base stations
- ▶ Massive MIMO
- ▶ Small cell designs





ADRV9026 Overview

- ▶ Four differential transmitters
- ▶ Four differential receivers
- ▶ Two observation receivers with two inputs each
- ▶ Center frequency: 650 MHz to 6000 MHz
- ▶ Maximum receiver bandwidth: 200 MHz
- ▶ Maximum transmitter bandwidth: 200 MHz
- ▶ Maximum transmitter synthesis bandwidth: 450 MHz
- ▶ Maximum observation receiver bandwidth: 450 MHz
- ▶ Fully integrated independent fractional-N radio frequency synthesizers
- ▶ Fully integrated clock synthesizer
- ▶ Multichip phase synchronization for all local oscillators and baseband clocks
- ▶ Support of TDD/FDD 3G/4G/5G applications
- ▶ 16 Gbps JESD204B/C digital interface

See roadmap below for future enhancements

ADRV9026 Family Roadmap

Enhanced features and functions will be added to the [ADRV9026](#) over time, including:

- ▶ 25 Gbps SERDES support
- ▶ Extending LO frequency range down to 75 MHz
- ▶ Support for an external LO
- ▶ Filter Wizard to generate custom profiles

An enhanced version from the [ADRV902x](#) family will be released in 2020 with integrated DPD and CFR, reducing FPGA requirements, as well as lowering total system power and cost.

RadioVerse Ecosystem and Partnerships

RadioVerse® is a design and technology ecosystem for advanced radio design and development. We offer market-leading integrated transceiver technology, software tools, evaluation and prototyping platforms, a range of reference designs, and radio solutions. RadioVerse is building up a global partnership network to provide customers all levels of design support. ADRV9026's partner network and reference design ecosystem will be launched on analog.com/radioverse in 2020.



Evaluation System

The evaluation system comprises an FPGA carrier board ADS9-V2EBZ and a radio daughtercard, coming with two frequency bands of matching: –HB for 2.8 GHz to 6 GHz and –MB for 650 MHz to 2.8 GHz. Compatible evaluation software is provided for download, including API library, Windows GUI, and a binary image for FPGA configuration.

	Radio Cards	Carrier Boards	Software and Driver
Evaluation System	<ul style="list-style-type: none"> ▶ ADRV902X-HB/PCBZ (for 2.8 GHz to 6 GHz) ▶ ADRV902X-MB/PCBZ (for 650 MHz to 2.8 GHz) 	<ul style="list-style-type: none"> ▶ ADS9-V2EBZ (FPGA motherboard with Xilinx® UltraScale+™) 	<ul style="list-style-type: none"> ▶ Operating system-agnostic API source in ANSI C ▶ Windows GUI for transceiver configuration and data capture ▶ Binary image for FPGA configuration

EngineerZone® Online Support Community

Engage with the Analog Devices technology experts in our online support community. Ask your tough design questions, browse FAQs, or join a conversation.

Visit ez.analog.com



Circuits from the Lab Reference Designs

Circuits from the Lab® reference designs are built and tested by ADI engineers with comprehensive documentation and factory-tested evaluation hardware.

Visit analog.com/cft/

Circuits from the Lab® Reference Designs



AHEAD OF WHAT'S POSSIBLE™

VISIT ANALOG.COM

For regional headquarters, sales, and distributors or to contact customer service and technical support, visit analog.com/contact.

Ask our ADI technology experts tough questions, browse FAQs, or join a conversation at the EngineerZone Online Support Community. Visit ez.analog.com.

©2019 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners.

PH21775-11/19(A)