

ADP3623/ADP3624/ADP3625/ADP3633/ ADP3634/ADP3635

High Speed, Dual, 4 A MOSFET Driver with Thermal Protection

FEATURES

- ▶ Industry-standard-compatible pinout
- ▶ High current drive capability
- ▶ Precise threshold shutdown comparator
- ▶ UVLO with hysteresis
- ▶ Overtemperature warning signal
- ▶ Overtemperature shutdown
- ▶ 3.3 V-compatible inputs
- ▶ 10 ns typical rise time and fall time @ 2.2 nF load
- ▶ Matched propagation delays between channels
- ▶ Fast propagation delay
- ▶ 9.5 V to 18 V supply voltage (ADP3633/ADP3634/ADP3635)
- ▶ 4.5 V to 18 V supply voltage (ADP3623/ADP3624/ADP3625)
- ▶ Parallelable dual outputs
- ▶ Rated from -40°C to +85°C ambient temperature
- ▶ Thermally enhanced packages, [8-lead SOIC_N_EP](#) and [8-lead MINI_SO_EP](#)

APPLICATIONS

- ▶ AC-to-dc switch mode power supplies
- ▶ DC-to-dc power supplies
- ▶ Synchronous rectification
- ▶ Motor drives

FUNCTIONAL BLOCK DIAGRAM




Figure 1.

TABLE OF CONTENTS

Features.....	1	Input Drive Requirements (INA, \overline{INA} , INB, \overline{INB} , and SD).....	12
Applications.....	1	Low-Side Drivers (OUTA, OUTB).....	12
General Description.....	1	Shutdown (SD) Function.....	12
Functional Block Diagram.....	1	Overtemperature Protections.....	12
Specifications.....	3	Supply Capacitor Selection.....	13
Timing Diagrams.....	4	PCB Layout Considerations.....	13
Absolute Maximum Ratings.....	6	Parallel Operation.....	13
ESD Caution.....	6	Thermal Considerations.....	14
Pin Configuration and Function Descriptions.....	7	Outline Dimensions.....	16
Typical Performance Characteristics.....	9	Ordering Guide.....	16
Test Circuit.....	11	UVLO Options.....	17
Theory of Operation.....	12		

REVISION HISTORY**1/2026—Rev. A to Rev. B**

Updated Outline Dimensions.....	16
Changes to Ordering Guide.....	16
Added UVLO Options.....	17

SPECIFICATIONS

$V_{DD} = 12$ V, $T_J = -40^\circ\text{C}$ to $+125^\circ\text{C}$, unless otherwise noted. All limits at temperature extremes guaranteed via correlation using standard statistical quality control (SQC) methods.

Table 1.

Parameter	Symbol	Test Conditions/Comments	Min	Typ	Max	Unit
SUPPLY						
Supply Voltage Range	V_{DD}	ADP3633/ADP3634/ADP3635	9.5	18		V
	V_{DD}	ADP3623/ADP3624/ADP3625	4.5	18		V
Supply Current	I_{DD}	No switching, INA, $\overline{\text{INA}}$, INB, and $\overline{\text{INB}}$ disabled		1.2	3	mA
Standby Current	I_{SBY}	SD = 5 V		1.2	3	mA
UVLO						
Turn-On Threshold Voltage	V_{UVLO_ON}	V_{DD} rising, $T_A = 25^\circ\text{C}$, ADP3633/ADP3634/ADP3635	8.0	8.7	9.5	V
	V_{UVLO_ON}	V_{DD} rising, $T_A = 25^\circ\text{C}$, ADP3623/ADP3624/ADP3625	3.8	4.2	4.5	V
Turn-Off Threshold Voltage	V_{UVLO_OFF}	V_{DD} falling, $T_A = 25^\circ\text{C}$, ADP3633/ADP3634/ADP3635	7.0	7.7	8.5	V
	V_{UVLO_OFF}	V_{DD} falling, $T_A = 25^\circ\text{C}$, ADP3623/ADP3624/ADP3625	3.5	3.9	4.3	V
Hysteresis		ADP3633/ADP3634/ADP3635		1.0		V
		ADP3623/ADP3624/ADP3625		0.3		V
DIGITAL INPUTS (INA, $\overline{\text{INA}}$, INB, $\overline{\text{INB}}$, SD)						
Input Voltage High	V_{IH}		2.0			V
Input Voltage Low	V_{IL}			0.8		V
Input Current	I_{IN}	$0 \text{ V} < V_{IN} < V_{DD}$	-20	+20		μA
SD Threshold High	V_{SD_H}		1.19	1.28	1.38	V
	V_{SD_H}	$T_A = 25^\circ\text{C}$	1.21	1.28	1.35	V
SD Threshold Low	V_{SD_L}	$T_A = 25^\circ\text{C}$	0.95	1.0	1.05	V
SD Hysteresis	V_{SD_HYST}	$T_A = 25^\circ\text{C}$	240	280	320	mV
Internal Pull-Up/Pull-Down Current				6		μA
OUTPUTS (OUTA, OUTB)						
Output Resistance, Unbiased		$V_{DD} = \text{PGND}$	80			$\text{k}\Omega$
Peak Source Current		See Figure 20	4			A
Peak Sink Current		See Figure 20	-4			A
SWITCHING TIME						
OUTA, OUTB Rise Time	t_{RISE}	$C_{LOAD} = 2.2 \text{ nF}$, see Figure 3 and Figure 4	10	25		ns
OUTA, OUTB Fall Time	t_{FALL}	$C_{LOAD} = 2.2 \text{ nF}$, see Figure 3 and Figure 4	10	25		ns
OUTA, OUTB Rising Propagation Delay	t_{D1}	$C_{LOAD} = 2.2 \text{ nF}$, see Figure 3 and Figure 4	14	30		ns
OUTA, OUTB Falling Propagation Delay	t_{D2}	$C_{LOAD} = 2.2 \text{ nF}$, see Figure 3 and Figure 4	22	35		ns
SD Propagation Delay Low	t_{dL_SD}	See Figure 2	32	45		ns
SD Propagation Delay High	t_{dH_SD}	See Figure 2	48	75		ns
Delay Matching Between Channels				2		ns
OVERTEMPERATURE PROTECTION						
Overtemperature Warning Threshold	T_W	See Figure 6	120	135	150	$^\circ\text{C}$
Overtemperature Shutdown Threshold	T_{SD}	See Figure 6	150	165	180	$^\circ\text{C}$
Temperature Hysteresis for Shutdown	T_{HYS_SD}	See Figure 6		30		$^\circ\text{C}$
Temperature Hysteresis for Warning	T_{HYS_W}	See Figure 6		10		$^\circ\text{C}$
Overtemperature Warning Low	V_{OTW_OL}	Open drain, $-500 \mu\text{A}$			0.4	V

SPECIFICATIONS

TIMING DIAGRAMS




Figure 2. Shutdown Timing Diagram




Figure 3. Output Timing Diagram (Noninverting)




Figure 4. Output Timing Diagram (Inverting)




Figure 5. UVLO Function

SPECIFICATIONS




Figure 6. Overtemperature Warning and Shutdown

ABSOLUTE MAXIMUM RATINGS

Table 2.

Parameter	Rating
VDD	-0.3 V to +20 V
OUTA, OUTB	
DC	-0.3 V to V_{DD} + 0.3 V
<200 ns	-2 V to V_{DD} + 0.3 V
INA, \bar{INA} , INB, \bar{INB} , and SD	-0.3 V to V_{DD} + 0.3 V
ESD	
Human Body Model (HBM)	3.5 kV
Field Induced Charged Device Model (FICDM)	
SOIC_N_EP	1.5 kV
MINI_SO_EP	1.0 kV
θ_{JA} , JEDEC 4-Layer Board	
SOIC_N_EP ¹	59°C/W
MINI_SO_EP ¹	43°C/W
Junction Temperature Range	-40°C to +150°C
Storage Temperature Range	-65°C to +150°C
Lead Temperature	
Soldering (10 sec)	300°C
Vapor Phase (60 sec)	215°C
Infrared (15 sec)	260°C

¹ θ_{JA} is measured per JEDEC standards, JESD51-2, JESD51-5, and JESD51-7, as appropriate with the exposed pad soldered to the PCB.


Stresses at or above those listed under absolute maximum ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

PIN CONFIGURATION AND FUNCTION DESCRIPTIONS



NOTES


1. THE EXPOSED PAD OF THE PACKAGE IS NOT DIRECTLY CONNECTED TO ANY PIN OF THE PACKAGE, BUT IT IS ELECTRICALLY AND THERMALLY CONNECTED TO THE DIE SUBSTRATE, WHICH IS THE GROUND OF THE DEVICE.

08

Figure 7. ADP3623/ADP3633 Pin Configuration

Table 3. ADP3623/ADP3633 Pin Function Descriptions

Pin No.	Mnemonic	Description
1	SD	Output Shutdown. When high, this pin disables normal operation, forcing OUTA and OUTB low.
2	INA	Inverting Input Pin for Channel A Gate Driver.
3	PGND	Ground. This pin should be closely connected to the source of the power MOSFET.
4	INB	Inverting Input Pin for Channel B Gate Driver.
5	OUTB	Output Pin for Channel B Gate Driver.
6	VDD	Power Supply Voltage. Bypass this pin to PGND with a ~1 μ F to 5 μ F ceramic capacitor.
7	OUTA	Output Pin for Channel A Gate Driver.
8	OTW	Overtemperature Warning Flag. Open drain, active low.



NOTES

1. THE EXPOSED PAD OF THE PACKAGE IS NOT DIRECTLY CONNECTED TO ANY PIN OF THE PACKAGE, BUT IT IS ELECTRICALLY AND THERMALLY CONNECTED TO THE DIE SUBSTRATE, WHICH IS THE GROUND OF THE DEVICE.


09

Figure 8. ADP3624/ADP3634 Pin Configuration

Table 4. ADP3624/ADP3634 Pin Function Descriptions

Pin No.	Mnemonic	Description
1	SD	Output Shutdown. When high, this pin disables normal operation, forcing OUTA and OUTB low.
2	INA	Input Pin for Channel A Gate Driver.
3	PGND	Ground. This pin should be closely connected to the source of the power MOSFET.
4	INB	Input Pin for Channel B Gate Driver.
5	OUTB	Output Pin for Channel B Gate Driver.
6	VDD	Power Supply Voltage. Bypass this pin to PGND with a ~1 μ F to 5 μ F ceramic capacitor.
7	OUTA	Output Pin for Channel A Gate Driver.
8	OTW	Overtemperature Warning Flag. Open drain, active low.

PIN CONFIGURATION AND FUNCTION DESCRIPTIONS



NOTES

1. THE EXPOSED PAD OF THE PACKAGE IS NOT DIRECTLY CONNECTED TO ANY PIN OF THE PACKAGE, BUT IT IS ELECTRICALLY AND THERMALLY CONNECTED TO THE DIE SUBSTRATE, WHICH IS THE GROUND OF THE DEVICE.

8

Figure 9. ADP3625/ADP3635 Pin Configuration

Table 5. ADP3625/ADP3635 Pin Function Descriptions

Pin No.	Mnemonic	Description
1	SD	Output Shutdown. When high, this pin disables normal operation, forcing OUTA and OUTB low.
2	INA	Inverting Input Pin for Channel A Gate Driver.
3	PGND	Ground. This pin should be closely connected to the source of the power MOSFET.
4	INB	Input Pin for Channel B Gate Driver.
5	OUTB	Output Pin for Channel B Gate Driver.
6	VDD	Power Supply Voltage. Bypass this pin to PGND with a ~1 μ F to 5 μ F ceramic capacitor.
7	OUTA	Output Pin for Channel A Gate Driver.
8	OTW	Overtemperature Warning Flag. Open drain, active low.

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 10. UVLO vs. Temperature




Figure 11. Rise and Fall Times vs. Temperature




Figure 12. Propagation Delay vs. Temperature








Figure 13. Rise and Fall Times vs. V_{DD} Figure 14. Propagation Delay vs. V_{DD} 

Figure 15. Shutdown Threshold vs. Temperature

TYPICAL PERFORMANCE CHARACTERISTICS



TEST CIRCUIT




Figure 20. Test Circuit

THEORY OF OPERATION

The ADP362x/ADP363x family of dual drivers is optimized for driving two independent enhancement N-channel MOSFETs or insulated gate bipolar transistors (IGBTs) in high switching frequency applications.

These applications require high speed, fast rise and fall times, as well as short propagation delays. The capacitive nature of the aforementioned gated devices requires high peak current capability as well.




Figure 21. Typical Application Circuit

INPUT DRIVE REQUIREMENTS (INA, INA, INB, INB, AND SD)

The ADP362x/ADP363x family inputs are designed to meet the requirements of modern digital power controllers; the signals are compatible with 3.3 V logic levels. At the same time, the input structure allows for input voltages as high as V_{DD} .

The signals applied to the inputs (INA, $\overline{\text{INA}}$, INB, and $\overline{\text{INB}}$) should have steep and clean fronts. It is not recommended to apply slow changing signals to drive these inputs because they can result in multiple switching when the thresholds are crossed, causing damage to the power MOSFET or IGBT.

An internal pull-down resistor is present at the input, which guarantees that the power device is off in the event that the input is left floating.

The SD input has a precision comparator with hysteresis and is therefore suitable for slow changing signals (such as a scaled down output voltage); see the [Shutdown \(SD\) Function](#) section for more details on this comparator.

LOW-SIDE DRIVERS (OUTA, OUTB)

The ADP362x/ADP363x family of dual drivers is designed to drive ground referenced N-channel MOSFETs. The bias is internally connected to the V_{DD} supply and PGND.

When the ADP362x/ADP363x family is disabled, both low-side gates are held low. An internal impedance is present between the OUTA/OUTB pins and GND, even when V_{DD} is not present; this feature ensures that the power MOSFET is normally off when bias voltage is not present.

When interfacing the ADP362x/ADP363x family to external MOSFETs, the designer should consider ways to make a robust design that minimizes stresses on both the driver and the MOSFETs.

These stresses include exceeding the short time duration voltage ratings on the OUTA and OUTB pins, as well as the external MOSFET.

Power MOSFETs are usually selected to have a low on resistance to minimize conduction losses, which usually implies a large input gate capacitance and gate charge.

SHUTDOWN (SD) FUNCTION

The ADP362x/ADP363x family features an advanced shutdown function, with accurate threshold and hysteresis.

The SD signal is an active high signal. An internal pull-up is present on this pin and, therefore, it is necessary to pull down the pin externally for drivers to operate normally.

In some power systems, it is sometimes necessary to provide an additional overvoltage protection (OVP) or overcurrent protection (OCP) shutdown signal to turn off the power devices (MOSFETs or IGBTs) in case of failure of the main controller.

An accurate internal reference is used for the SD comparator so that it can be used to detect OVP or OCP fault conditions.




Figure 22. Shutdown Function Used for Redundant OVP

OVERTEMPERATURE PROTECTIONS

The ADP362x/ADP363x family provides two levels of overtemperature protections:

► Overtemperature warning (OTW)

THEORY OF OPERATION

▶ Overtemperature shutdown

The overtemperature warning is an open-drain logic signal and is active low. In normal operation, when no thermal warning is present, the signal is high, whereas when the warning threshold is crossed, the signal is pulled low.




Figure 23. OTW Signaling Scheme Example

The OTW open-drain configuration allows connection of multiple devices to the same warning bus in a wire-OR'ed configuration, as shown in Figure 23.

The overtemperature shutdown turns off the device to protect it in the event that the die temperature exceeds the absolute maximum limit in Table 2.

SUPPLY CAPACITOR SELECTION

For the supply input (V_{DD}) of the ADP362x/ADP363x family, a local bypass capacitor is recommended to reduce the noise and to supply some of the peak currents that are drawn.

An improper decoupling can dramatically increase the rise times, cause excessive resonance on the OUTA and OUTB pins, and, in some extreme cases, even damage the device, due to inductive overvoltage on the VDD or OUTA/OUTB pins.

The minimum capacitance required is determined by the size of the gate capacitances being driven, but as a general rule, a $4.7\ \mu F$, low ESR capacitor should be used. Multilayer ceramic chip (MLCC) capacitors provide the best combination of low ESR and small size. Use a smaller ceramic capacitor ($100\ nF$) with a better high frequency characteristic in parallel to the main capacitor to further reduce noise.

Keep the ceramic capacitor as close as possible to the ADP362x/ADP363x device, and minimize the length of the traces going from the capacitor to the power pins of the device.

PCB LAYOUT CONSIDERATIONS

Use the following general guidelines when designing printed circuit boards (PCBs):

- ▶ Trace out the high current paths and use short, wide ($>40\ mil$) traces to make these connections.
- ▶ Minimize trace inductance between the OUTA and OUTB outputs and MOSFET gates.
- ▶ Connect the PGND pin of the ADP362x/ADP363x device as closely as possible to the source of the MOSFETs.
- ▶ Place the V_{DD} bypass capacitor as close as possible to the VDD and PGND pins.
- ▶ Use vias to other layers, when possible, to maximize thermal conduction away from the IC.

Figure 24 shows an example of the typical layout based on the preceding guidelines.




Figure 24. External Component Placement Example

Note that the exposed pad of the package is not directly connected to any pin of the package, but it is electrically and thermally connected to the die substrate, which is the ground of the device.

PARALLEL OPERATION

The two driver channels present in the ADP3623/ADP3633 or ADP3624/ADP3634 devices can be combined to operate in parallel to increase drive capability and minimize power dissipation in the driver.

The connection scheme for the ADP3624/ADP3634 devices is shown in Figure 25. In this configuration, INA and INB are connected together, and OUTA and OUTB are connected together.

Particular attention must be paid to the layout in this case to optimize load sharing between the two drivers.

THEORY OF OPERATION

$$T_J = T_A + \Delta T_J = 136.8^\circ\text{C} \leq T_{JMAX}$$

This estimated junction temperature does not factor in the power dissipated in the external gate resistor and, therefore, provides a certain guard band.

If a lower junction temperature is required by the design, the MINI_SO_EP package can be used, which provides a thermal resistance of $43^\circ\text{C}/\text{W}$, so that the maximum junction temperature is

$$\Delta T_J = 878.4 \text{ mW} \times 43^\circ\text{C}/\text{W} = 37.7^\circ\text{C}$$

$$T_J = T_A + \Delta T_J = 122.7^\circ\text{C} \leq T_{JMAX}$$

Other options to reduce power dissipation in the driver include reducing the value of the V_{DD} bias voltage, reducing switching frequency, and choosing a power MOSFET with smaller gate charge.

OUTLINE DIMENSIONS

Package Drawing Option	Package Type	Package Description
RD-8-4	SOIC_N_EP	8-Lead Standard Small Outline Package with Exposed Pad, Narrow Body
RH-8-1	MINI_SO_EP	8-Lead Mini Small Outline Package with Exposed Pad

For the latest package outline information and land patterns (footprints), go to [Package Index](#).

ORDERING GUIDE

Model ¹	Temperature Range	Package Description	Package Option	Packing Quantity	Marking Code
ADP3623ARDZ-RL	-40°C to +85°C	8-Lead Standard Small Outline Package (SOIC_N_EP), 13" Tape and Reel	RD-8-4	REEL, 2500	
ADP3623ARHZ-RL	-40°C to +85°C	8-Lead Mini Small Outline Package (MINI_SO_EP), 13" Tape and Reel	RH-8-1	REEL, 3000	P3
ADP3624ARDZ	-40°C to +85°C	8-Lead Standard Small Outline Package (SOIC_N_EP)	RD-8-4	TUBE, 98	
ADP3624ARDZ-RL	-40°C to +85°C	8-Lead Standard Small Outline Package (SOIC_N_EP), Tape Reel	RD-8-4	REEL, 2500	
ADP3624ARHZ	-40°C to +85°C	8-Lead Mini Small Outline Package (MINI_SO_EP)	RH-8-1	TUBE, 50	P4
ADP3624ARHZ-RL	-40°C to +85°C	8-Lead Mini Small Outline Package (MINI_SO_EP), Tape Reel	RH-8-1	REEL, 3000	P4
ADP3625ARDZ-RL	-40°C to +85°C	8-Lead Standard Small Outline Package (SOIC_N_EP), 13" Tape and Reel	RD-8-4	REEL, 2500	
ADP3625ARHZ-RL	-40°C to +85°C	8-Lead Mini Small Outline Package (MINI_SO_EP), 13" Tape and Reel	RH-8-1	REEL, 3000	P5
ADP3633ARDZ-RL	-40°C to +85°C	8-Lead Standard Small Outline Package (SOIC_N_EP), 13" Tape and Reel	RD-8-4	REEL, 2500	
ADP3633ARHZ-RL	-40°C to +85°C	8-Lead Mini Small Outline Package (MINI_SO_EP), 13" Tape and Reel	RH-8-1	REEL, 3000	L3
ADP3634ARDZ	-40°C to +85°C	8-Lead Standard Small Outline Package (SOIC_N_EP)	RD-8-4	TUBE, 98	
ADP3634ARDZ-RL	-40°C to +85°C	8-Lead Standard Small Outline Package (SOIC_N_EP), 13" Tape and Reel	RD-8-4	REEL, 2500	
ADP3634ARHZ	-40°C to +85°C	8-Lead Mini Small Outline Package (MINI_SO_EP)	RH-8-1	TUBE, 50	L4
ADP3634ARHZ-RL	-40°C to +85°C	8-Lead Mini Small Outline Package (MINI_SO_EP), 13" Tape and Reel	RH-8-1	REEL, 3000	L4
ADP3635ARDZ-RL	-40°C to +85°C	8-Lead Standard Small Outline Package (SOIC_N_EP), 13" Tape and Reel	RD-8-4	REEL, 2500	
ADP3635ARHZ-RL	-40°C to +85°C	8-Lead Mini Small Outline Package (MINI_SO_EP), 13" Tape and Reel	RH-8-1	REEL, 3000	L5

¹ Z = RoHS Compliant Part.

OUTLINE DIMENSIONS**UVLO OPTIONS**

Model ¹	UVLO Option
ADP3623ARDZ-RL	4.5 V
ADP3623ARHZ-RL	4.5 V
ADP3624ARDZ	4.5 V
ADP3624ARDZ-RL	4.5 V
ADP3624ARHZ	4.5 V
ADP3624ARHZ-RL	4.5 V
ADP3625ARDZ-RL	4.5 V
ADP3625ARHZ-RL	4.5 V
ADP3633ARDZ-RL	9.5 V
ADP3633ARHZ-RL	9.5 V
ADP3634ARDZ	9.5 V
ADP3634ARDZ-RL	9.5 V
ADP3634ARHZ	9.5 V
ADP3634ARHZ-RL	9.5 V
ADP3635ARDZ-RL	9.5 V
ADP3635ARHZ-RL	9.5 V

¹ Z = RoHS Compliant Part.

Legal Terms and Conditions

Information furnished by Analog Devices is believed to be accurate and reliable "as is". However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners. All Analog Devices products contained herein are subject to release and availability.