

Micropower, Single Supply Rail-to-Rail Output Instrumentation Amplifiers

FEATURES

- **Micropower: 95µA Supply Current Max**
- **Low Input Offset Voltage: 100µV Max**
- **Low Input Offset Voltage Drift: 0.5µV/°C Max**
- **Single Gain Set Resistor:**
 - G = 1 to 1000 (LT1789-1)
 - G = 10 to 1000 (LT1789-10)
- **Inputs Common Mode to V⁻**
- **Wide Supply Range: 2.2V to 36V Total Supply**
- **CMRR at G = 10: 96dB Min**
- **Gain Error: G = 10, 0.25% Max**
- **Gain Nonlinearity: G = 10, 40ppm Max**
- **Input Bias Current: 40nA Max**
- **PSRR at G = 10: 100dB Min**
- **1kHz Voltage Noise: 48nV/√Hz**
- **0.1Hz to 10Hz Noise: 1.5µV_{P-P}**

APPLICATIONS

- Portable Instrumentation
- Bridge Amplifiers
- Strain Gauge Amplifiers
- Thermocouple Amplifiers
- Differential to Single-Ended Converters
- Medical Instrumentation

DESCRIPTION

The LT[®]1789-1/LT1789-10 are micropower, precision instrumentation amplifiers that are optimized for single supply operation from 2.2V to 36V. The quiescent current is 95µA max, the inputs common mode to ground and the output swings within 110mV of ground. The gain is set with a single external resistor for a gain range of 1 to 1000 for the LT1789-1 and 10 to 1000 for the LT1789-10.


The high accuracy of the LT1789-1 (40ppm maximum non-linearity and 0.25% max gain error) is unmatched by other micropower instrumentation amplifiers. The LT1789-10 maximizes both the input common mode range and dynamic output range when an amplification of 10 or greater is required, allowing precise signal processing where other instrumentation amplifiers fail to operate. The LT1789-1/LT1789-10 are laser trimmed for very low input offset voltage, low input offset voltage drift, high CMRR and high PSRR. The output can handle capacitive loads up to 400pF (LT1789-1), 1000pF (LT1789-10) in any gain configuration while the inputs are ESD protected up to 10kV (human body).

The LT1789-1/LT1789-10 are offered in the 8-pin SO package, requiring significantly less PC board area than discrete multi op amp and resistor designs.

LT, LT, LTC, LTM, Linear Technology and the Linear logo are registered trademarks of Linear Technology Corporation. All other trademarks are the property of their respective owners.

TYPICAL APPLICATION

0.5A to 4A Voltage Controlled Current Source




LT1789-1/LT1789-10

ABSOLUTE MAXIMUM RATINGS

(Note 1)

| | |
|---|--|
| Supply Voltage (V^+ to V^-)..... | 36V |
| Input Differential Voltage | 36V |
| Input Current (Note 3)..... | $\pm 20\text{mA}$ |
| Output Short-Circuit Duration | Indefinite |
| Operating Temperature Range | -40°C to 85°C |
| Specified Temperature Range (Note 4) | |
| LT1789C-1, LT1789C-10 | -40°C to 85°C |
| LT1789I-1, LT1789I-10 | -40°C to 85°C |
| Storage Temperature Range | -65°C to 150°C |
| Lead Temperature (Soldering, 10 sec)..... | 300°C |

PIN CONFIGURATION



ORDER INFORMATION

| LEAD FREE FINISH | TAPE AND REEL | PART MARKING | PACKAGE DESCRIPTION | TEMPERATURE RANGE |
|-------------------|--------------------|--------------|---------------------|---|
| LT1789CS8-1#PBF | LT1789CS8-1#TRPBF | 17891 | 8-Lead Plastic SO | -40°C to 85°C |
| LT1789IS8-1#PBF | LT1789IS8-1#TRPBF | 1789I1 | 8-Lead Plastic SO | -40°C to 85°C |
| LT1789CS8-10#PBF | LT1789CS8-10#TRPBF | 178910 | 8-Lead Plastic SO | -40°C to 85°C |
| LT1789IS8-10#PBF | LT1789IS8-10#TRPBF | 789I10 | 8-Lead Plastic SO | -40°C to 85°C |
| LEAD BASED FINISH | TAPE AND REEL | PART MARKING | PACKAGE DESCRIPTION | TEMPERATURE RANGE |
| LT1789CS8-1 | LT1789CS8-1#TR | 17891 | 8-Lead Plastic SO | -40°C to 85°C |
| LT1789IS8-1 | LT1789IS8-1#TR | 1789I1 | 8-Lead Plastic SO | -40°C to 85°C |
| LT1789CS8-10 | LT1789CS8-10#TR | 178910 | 8-Lead Plastic SO | -40°C to 85°C |
| LT1789IS8-10 | LT1789IS8-10#TR | 789I10 | 8-Lead Plastic SO | -40°C to 85°C |

Consult LTC Marketing for parts specified with wider operating temperature ranges.

For more information on lead free part marking, go to: <http://www.linear.com/leadfree/>

For more information on tape and reel specifications, go to: <http://www.linear.com/tapeandreeel/>

3V AND 5V ELECTRICAL CHARACTERISTICS

$V_S = 3\text{V}, 0\text{V}; V_S = 5\text{V}, 0\text{V}; R_L = 20\text{k}, V_{CM} = V_{REF} = \text{half supply}, T_A = 25^\circ\text{C}$, unless otherwise noted.

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS |
|--------|----------------------------|--|----------|------|------|-----------|-----|------|-------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | |
| G | Gain Range | LT1789-1, $G = 1 + (200\text{k}/R_G)$ LT1789-10, $G = 10 \cdot [1 + (200\text{k}/R_G)]$ | 1 | | 1000 | 10 | | 1000 | |
| | Gain Error (Note 6) | $G = 1, V_0 = 0.1\text{V to } (+V_S) - 1\text{V}$ LT1789-1, $V_0 = 0.1\text{V to } (+V_S) - 0.3\text{V}$ LT1789-10, $V_0 = 0.2\text{V to } (+V_S) - 0.3\text{V}$ $G = 10$ (Note 2) $G = 100$ (Note 2) $G = 1000$ (Note 2) | | 0.02 | 0.20 | | | | % |
| | Gain Nonlinearity (Note 6) | $G = 1, V_0 = 0.1\text{V to } (+V_S) - 1\text{V}$ | | 35 | 100 | | | | ppm |
| | | LT1789-1, $V_0 = 0.1\text{V to } (+V_S) - 0.3\text{V}$ LT1789-10, $V_0 = 0.2\text{V to } 4.7\text{V}, V_S = 5\text{V}$ (Note 8) $G = 10$ $G = 100$ $G = 1000$ | | 12 | 40 | | 15 | 100 | ppm |
| | | | | 18 | 75 | | 20 | 100 | ppm |
| | | | | 90 | | | 100 | | ppm |

1789fc

3V AND 5V ELECTRICAL CHARACTERISTICS $V_S = 3V, 0V; V_S = 5V, 0V; R_L = 20k, V_{CM} = V_{REF} = \text{half supply}, T_A = 25^\circ C$, unless otherwise noted.

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS | |
|--|--|---|--------------|----------------|------------|--------------|----------------|--------------|------------------------|----|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | | |
| V_{OST} | Total Input Referred Offset Voltage | $V_{OST} = V_{OSI} + V_{OSO}/G$ | | | | | | | | |
| V_{OSI} | Input Offset Voltage | $G = 1000$ | | 15 | 100 | | 20 | 160 | μV | |
| V_{OSO} | Output Offset Voltage | $G = 1$ (LT1789-1), $G = 10$ (LT1789-10) | | 150 | 750 | | 650 | 3000 | μV | |
| I_{OS} | Input Offset Current | (Note 6) | | 0.2 | 4 | | 0.2 | 4 | nA | |
| I_B | Input Bias Current | (Note 6) | | 19 | 40 | | 19 | 40 | nA | |
| e_n | Input Noise Voltage, RTI (Referred to Input) | $G = 1, f_0 = 0.1\text{Hz to }10\text{Hz}$ $G = 10$ $G = 100, 1000$ | | 5.0 | | | | | μV_{P-P} | |
| | | | | 1.5 | | | 4.6 | | μV_{P-P} | |
| | | | | 1.0 | | | 1.1 | | μV_{P-P} | |
| Total RTI Noise = $\sqrt{e_{ni}^2 + (e_{no}/G)^2}$ | | | | | | | | | | |
| e_{ni} | Input Noise Voltage Density, RTI | $f_0 = 1\text{kHz}$ (Note 7) | | 48 | 85 | | 52 | 90 | nV/ $\sqrt{\text{Hz}}$ | |
| e_{no} | Output Noise Voltage Density, RTI | $f_0 = 1\text{kHz}$ (Note 3) | | 330 | | | 270 | | nV/ $\sqrt{\text{Hz}}$ | |
| i_n | Input Noise Current | $f_0 = 0.1\text{Hz to }10\text{Hz}$ | | 16 | | | 16 | | pA $_{P-P}$ | |
| | Input Noise Current Density | $f_0 = 1\text{kHz}$ | | 62 | | | 62 | | fA/ $\sqrt{\text{Hz}}$ | |
| R_{IN} | Input Resistance | $V_{IN} = 0V \text{ to } (+V_S) - 1V$ (Note 6) | 0.75 | 1.6 | | 0.75 | 1.6 | | G Ω | |
| C_{IN} | Input Capacitance | Differential Common Mode | | 1.6 | | | 1.6 | | pF | |
| | | | | 1.6 | | | 1.6 | | pF | |
| V_{CM} | Input Voltage Range | | 0 | | $+V_S - 1$ | 0 | | $+V_S - 1.2$ | V | |
| CMRR | Common Mode Rejection Ratio | 1k Source Imbalance (Note 6) LT1789-1, $V_{CM} = 0V \text{ to } (+V_S) - 1V$ LT1789-10, $V_{CM} = 0V \text{ to } (+V_S) - 1.2V$ $G = 1$ $G = 10$ $G = 100$ $G = 1000$ | | 79 | 88 | | | | | dB |
| | | | | 96 | 106 | | 88 | 105 | | dB |
| | | | | 100 | 114 | | 98 | 113 | | dB |
| | | | | 100 | 114 | | 98 | 113 | | dB |
| | | | | | | | | | | |
| PSRR | Power Supply Rejection Ratio | $V_S = 2.5V \text{ to } 12.5V, V_{CM} = V_{REF} = 1V$ $G = 1$ $G = 10$ $G = 100$ $G = 1000$ | | 90 | 100 | | | | | dB |
| | | | | 100 | 113 | | 94 | 109 | | dB |
| | | | | 102 | 116 | | 102 | 120 | | dB |
| | | | | 102 | 116 | | 102 | 120 | | dB |
| | | | | | | | | | | |
| | Minimum Supply Voltage | | | 2.2 | 2.5 | | 2.2 | 2.5 | V | |
| I_S | Supply Current | (Note 7) | | 67 | 95 | | 67 | 95 | μA | |
| V_{OL} | Output Voltage Swing LOW | (Note 7) | | 54 | 100 | | 62 | 110 | mV | |
| V_{OH} | Output Voltage Swing HIGH | (Note 7) | $+V_S - 0.3$ | $+V_S - 0.19$ | | $+V_S - 0.3$ | $+V_S - 0.19$ | | V | |
| I_{SC} | Short-Circuit Current | Short to GND Short to $+V_S$ | | 2.2 | | | 2.2 | | mA | |
| | | | | 8.5 | | | 8.5 | | mA | |
| BW | Bandwidth | $G = 1$ $G = 10$ $G = 100$ $G = 1000$ | | 60 | | | | | kHz | |
| | | | | 30 | | | 25 | | kHz | |
| | | | | 3 | | | 12 | | kHz | |
| | | | | 0.2 | | | 1.5 | | kHz | |
| SR | Slew Rate | $G = 10, V_{OUT} = 0.5V \text{ to } 4.5V$ | | 0.023 | | | 0.062 | | V/ μs | |
| | Settling Time to 0.01% | 4V Step | | 240 | | | 190 | | μs | |
| R_{REFIN} | Reference Input Resistance | | | 220 | | | 220 | | k Ω | |
| I_{REFIN} | Reference Input Current | $V_{REF} = 0V$ | | 2.7 | | | 2.7 | | μA | |
| AV_{REF} | Reference Gain to Output | | | 1 ± 0.0001 | | | 1 ± 0.0001 | | | |

LT1789-1/LT1789-10

ELECTRICAL CHARACTERISTICS

The ● denotes the specifications which apply over the temperature range of $0^{\circ}\text{C} \leq T_A \leq 70^{\circ}\text{C}$. $V_S = 3\text{V}, 0\text{V}$; $V_S = 5\text{V}, 0\text{V}$; $R_L = 20\text{k}$, $V_{\text{REF}} = \text{half supply}$, unless otherwise noted. (Note 4)

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS |
|--------------------|-------------------------------------|---|----------|---------------|--------------|---------------|----------------|--------------------------------|-------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | |
| | Gain Error (Note 6) | $G = 1, V_O = 0.3\text{V to } (+V_S) - 1\text{V}$ | ● | | 0.25 | | | % | |
| | | $V_O = 0.3\text{V to } (+V_S) - 0.5\text{V}$ | ● | | 0.53 | | 0.30 | % | |
| | | $G = 10$ (Note 2) $G = 100$ (Note 2) | ● | | 0.55 | | 0.53 | % | |
| | Gain Nonlinearity (Note 6) | $G = 1, V_O = 0.3\text{V to } (+V_S) - 1\text{V}$ | ● | | 185 | | | ppm | |
| | | LT1789-1, $V_O = 0.3\text{V to } (+V_S) - 0.5\text{V}$ LT1789-10, $V_O = 0.3\text{V to } 4.7\text{V}, V_S = 5\text{V}$ (Note 8) | ● | | 90 | | 130 | ppm | |
| | | $G = 10$ $G = 100$ | ● | | 120 | | 130 | ppm | |
| G/T | Gain vs Temperature | $G < 1000$ (Notes 2, 3) | ● | 5 | 50 | 5 | 50 | ppm/ $^{\circ}\text{C}$ | |
| V_{OST} | Total Input Referred Offset Voltage | $V_{\text{OST}} = V_{\text{OSI}} + V_{\text{OSO}}/G$ | | | | | | | |
| V_{OSI} | Input Offset Voltage | $G = 1000$ | ● | | 150 | | 190 | μV | |
| V_{OSIH} | Input Offset Voltage Hysteresis | (Notes 3, 5) | ● | 3 | 10 | 3 | 10 | μV | |
| V_{OSO} | Output Offset Voltage | $G = 1$ (LT1789-1), $G = 10$ (LT1789-10) | ● | | 950 | | 3700 | μV | |
| V_{OSOH} | Output Offset Voltage Hysteresis | (Notes 3, 5) | ● | 50 | 100 | 300 | 900 | μV | |
| V_{OSI}/T | Input Offset Voltage Drift (RTI) | (Note 3) | ● | 0.2 | 0.5 | 0.3 | 0.7 | $\mu\text{V}/^{\circ}\text{C}$ | |
| V_{OSO}/T | Output Offset Voltage Drift | (Note 3) | ● | 1.5 | 4 | 7 | 20 | $\mu\text{V}/^{\circ}\text{C}$ | |
| I_{OS} | Input Offset Current | (Note 6) | ● | | 4.5 | | 4.5 | nA | |
| I_{OS}/T | Input Offset Current Drift | | ● | 3 | | 3 | | pA/ $^{\circ}\text{C}$ | |
| I_{B} | Input Bias Current | (Note 6) | ● | | 45 | | 45 | nA | |
| I_{B}/T | Input Bias Current Drift | | ● | 50 | | 50 | | pA/ $^{\circ}\text{C}$ | |
| V_{CM} | Input Voltage Range | | ● | 0.2 | $(+V_S) - 1$ | 0.2 | $(+V_S) - 1.5$ | V | |
| CMRR | Common Mode Rejection Ratio | 1k Source Imbalance (Note 6) | ● | | | | | | |
| | | LT1789-1, $V_{\text{CM}} = 0.2\text{V to } (+V_S) - 1\text{V}$ | ● | 77 | | | | dB | |
| | | LT1789-10, $V_{\text{CM}} = 0.2\text{V to } (+V_S) - 1.5\text{V}$ | ● | 94 | | 85 | | dB | |
| | | $G = 1$ $G = 10$ $G = 100, 1000$ | ● | 98 | | 96 | | dB | |
| PSRR | Power Supply Rejection Ratio | $V_S = 2.5\text{V to } 12.5\text{V}, V_{\text{CM}} = V_{\text{REF}} = 1\text{V}$ | ● | | | | | | |
| | | $G = 1$ | ● | 88 | | | | dB | |
| | | $G = 10$ | ● | 98 | | 92 | | dB | |
| | | $G = 100, 1000$ | ● | 100 | | 100 | | dB | |
| | Minimum Supply Voltage | | ● | | 2.5 | | 2.5 | V | |
| I_{S} | Supply Current | (Note 7) | ● | | 115 | | 115 | μA | |
| V_{OL} | Output Voltage Swing LOW | (Note 7) | ● | | 110 | | 120 | mV | |
| V_{OH} | Output Voltage Swing HIGH | (Note 7) | ● | $+V_S - 0.38$ | | $+V_S - 0.38$ | | V | |

ELECTRICAL CHARACTERISTICS The ● denotes the specifications which apply over the temperature range of $-40^{\circ}\text{C} \leq T_A \leq 85^{\circ}\text{C}$. $V_S = 3\text{V}, 0\text{V}$; $V_S = 5\text{V}, 0\text{V}$; $R_L = 20\text{k}$, $V_{\text{REF}} = \text{half supply}$, unless otherwise noted. (Note 4)

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS |
|--------------------|-------------------------------------|---|----------|---------------|------------|---------------|--------------|--------------------------------|-------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | |
| | Gain Error (Note 6) | $G = 1, V_O = 0.3\text{V to }(+V_S) - 1\text{V}$ | ● | | 0.30 | | | | % |
| | | $V_O = 0.3\text{V to }(+V_S) - 0.5\text{V}$ | ● | | 0.57 | | 0.35 | % | |
| | | $G = 10$ (Note 2) $G = 100$ (Note 2) | ● | | 0.59 | | 0.62 | % | |
| | Gain Nonlinearity (Note 6) | $G = 1, V_O = 0.3\text{V to }(+V_S) - 1\text{V}$ | ● | | 250 | | | | ppm |
| | | LT1789-1, $V_O = 0.3\text{V to }(+V_S) - 0.5\text{V}$ LT1789-10, $V_O = 0.3\text{V to }4.7\text{V}, V_S = 5\text{V}$ (Note 8) | ● | | 105 | | 150 | ppm | |
| | | $G = 10$ $G = 100$ | ● | | 160 | | 170 | ppm | |
| G/T | Gain vs Temperature | $G < 1000$ (Notes 2, 3) | ● | 5 | 50 | 5 | 50 | ppm/ $^{\circ}\text{C}$ | |
| V_{OST} | Total Input Referred Offset Voltage | $V_{\text{OST}} = V_{\text{OSI}} + V_{\text{OSO}}/G$ | | | | | | | |
| V_{OSI} | Input Offset Voltage | $G = 1000$ | ● | | 175 | | 205 | μV | |
| V_{OSIH} | Input Offset Voltage Hysteresis | (Notes 3, 5) | ● | 3 | 10 | 3 | 10 | μV | |
| V_{OSO} | Output Offset Voltage | $G = 1$ (LT1789-1), $G = 10$ (LT1789-10) | ● | | 1050 | | 4000 | μV | |
| V_{OSOH} | Output Offset Voltage Hysteresis | (Notes 3, 5) | ● | 50 | 100 | 300 | 900 | μV | |
| V_{OSI}/T | Input Offset Voltage Drift (RTI) | (Note 3) | ● | 0.2 | 0.5 | 0.3 | 0.7 | $\mu\text{V}/^{\circ}\text{C}$ | |
| V_{OSO}/T | Output Offset Voltage Drift | (Note 3) | ● | 1.5 | 4 | 7 | 20 | $\mu\text{V}/^{\circ}\text{C}$ | |
| I_{OS} | Input Offset Current | (Note 6) | ● | | 5 | | 5 | nA | |
| I_{OS}/T | Input Offset Current Drift | | ● | 3 | | 3 | | $\text{pA}/^{\circ}\text{C}$ | |
| I_{B} | Input Bias Current | (Note 6) | ● | | 50 | | 50 | nA | |
| I_{B}/T | Input Bias Current Drift | | ● | 50 | | 50 | | $\text{pA}/^{\circ}\text{C}$ | |
| V_{CM} | Input Voltage Range | | ● | 0.2 | $+V_S - 1$ | 0.2 | $+V_S - 1.5$ | V | |
| CMRR | Common Mode Rejection Ratio | 1k Source Imbalance (Note 6) | | | | | | | |
| | | LT1789-1, $V_{\text{CM}} = 0.2\text{V to }(+V_S) - 1\text{V}$ | ● | 75 | | | | dB | |
| | | LT1789-10, $V_{\text{CM}} = 0.2\text{V to }(+V_S) - 1.5\text{V}$ | ● | 92 | | 84 | | dB | |
| | | $G = 1$ $G = 10$ $G = 100, 1000$ | ● | 96 | | 94 | | dB | |
| PSRR | Power Supply Rejection Ratio | $V_S = 2.5\text{V to }12.5\text{V}, V_{\text{CM}} = V_{\text{REF}} = 1\text{V}$ | ● | | | | | | |
| | | $G = 1$ | ● | 86 | | | | dB | |
| | | $G = 10$ | ● | 96 | | 90 | | dB | |
| | | $G = 100, 1000$ | ● | 98 | | 98 | | dB | |
| | Minimum Supply Voltage | | ● | | 2.5 | | 2.5 | V | |
| I_{S} | Supply Current | (Note 7) | ● | | 125 | | 125 | μA | |
| V_{OL} | Output Voltage Swing LOW | (Note 7) | ● | | 120 | | 130 | mV | |
| V_{OH} | Output Voltage Swing HIGH | (Note 7) | ● | $+V_S - 0.40$ | | $+V_S - 0.40$ | | V | |

LT1789-1/LT1789-10

ELECTRICAL CHARACTERISTICS

$V_S = \pm 15V$, $R_L = 20k$, $V_{CM} = V_{OUT} = 0V$, $T_A = 25^\circ C$, unless otherwise noted.

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS |
|--|-------------------------------------|---|------------|------------|------------|------------|------------|----------------|-------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | |
| G | Gain Range | LT1789-1, $G = 1 + (200k/R_G)$ LT1789-10, $G = 10 \cdot [1 + (200k/R_G)]$ | 1 | | 1000 | 10 | | 1000 | |
| | Gain Error | $V_O = \pm 10V$ $G = 1$ | | 0.01 | 0.10 | | | | % |
| | | $G = 10$ (Note 2) | | 0.04 | 0.15 | 0.01 | 0.15 | | % |
| $G = 100$ (Note 2) | | | 0.04 | 0.15 | 0.03 | 0.20 | | % | |
| $G = 1000$ (Note 2) | | | 0.07 | 0.20 | 0.03 | 0.25 | | % | |
| Gain Nonlinearity | $V_O = \pm 10V$ $G = 1$ | | 8 | 20 | | | | ppm | |
| | $G = 10$ | | 1 | 10 | 5 | 40 | | ppm | |
| | $G = 100$ | | 6 | 20 | 5 | 40 | | ppm | |
| | $G = 1000$ | | 20 | 100 | 25 | 160 | | ppm | |
| V_{OST} | Total Input Referred Offset Voltage | $V_{OST} = V_{OSI} + V_{OSO}/G$ | | | | | | | |
| V_{OSI} | Input Offset Voltage | $G = 1000$ | | 30 | 235 | 30 | 295 | μV | |
| V_{OSO} | Output Offset Voltage | $G = 1$ (LT1789-1), $G = 10$ (LT1789-10) | | 0.2 | 1 | 0.6 | 3.3 | mV | |
| I_{OS} | Input Offset Current | | | 0.2 | 4 | 0.2 | 4 | nA | |
| I_B | Input Bias Current | | | 17 | 40 | 17 | 40 | nA | |
| e_n | Input Noise Voltage, RTI | $f_0 = 0.1Hz$ to 10Hz | | | | | | | |
| | | $G = 1$ | | 5.0 | | | | μV_{P-P} | |
| | | $G = 10$ | | 1.5 | | 4.6 | | μV_{P-P} | |
| | | $G = 100, 1000$ | | 1.0 | | 1.1 | | μV_{P-P} | |
| Total RTI Noise = $\sqrt{e_{ni}^2 + (e_{no}/G)^2}$ | | | | | | | | | |
| e_{ni} | Input Noise Voltage Density, RTI | $f_0 = 1kHz$ | | 49 | 90 | 53 | 95 | nV/\sqrt{Hz} | |
| e_{no} | Output Noise Voltage Density, RTI | $f_0 = 1kHz$ | | 330 | | 270 | | nV/\sqrt{Hz} | |
| i_n | Input Noise Current | $f_0 = 0.1Hz$ to 10Hz | | 19 | | 19 | | pA_{P-P} | |
| | Input Noise Current Density | $f_0 = 1kHz$ | | 62 | | 62 | | fA/\sqrt{Hz} | |
| R_{IN} | Input Resistance | | 2 | 4.7 | | 2 | 4.7 | $G\Omega$ | |
| C_{IN} | Input Capacitance | Differential | | 20 | | 20 | | pF | |
| | | Common Mode | | 17 | | 17 | | pF | |
| V_{CM} | Input Voltage Range | | -15 | | -14 | -15 | | -14 | V |
| CMRR | Common Mode Rejection Ratio | 1k Source Imbalance, $V_{CM} = -15V$ to 14V | | | | | | | |
| | | $G = 1$ | 80 | 89 | | | | dB | |
| | | $G = 10$ | 98 | 108 | 93 | 108 | | dB | |
| PSRR | Power Supply Rejection Ratio | LT1789-1 $V_S = \pm 1.25V$ to $\pm 16V$ LT1789-10 $V_S = \pm 1.50V$ to $\pm 16V$ | | | | | | | |
| | | $G = 1$ | 94 | 107 | | | | dB | |
| | | $G = 10$ | 104 | 118 | 100 | 115 | | dB | |
| | Minimum Supply Voltage | | | | ± 1.25 | | ± 1.50 | V | |
| | | | | | | | | | |
| I_S | Supply Current | | | 85 | 130 | 85 | 130 | μA | |
| V_O | Output Voltage Swing | | ± 14.5 | ± 14.7 | | ± 14.5 | ± 14.7 | V | |
| I_{SC} | Short-Circuit Current | Short to $-V_S$ | | 2.2 | | 2.2 | | mA | |
| | | Short to $+V_S$ | | 8.5 | | 8.5 | | mA | |

ELECTRICAL CHARACTERISTICS

$V_S = \pm 15V$, $R_L = 20k$, $V_{CM} = V_{OUT} = 0V$, $T_A = 25^\circ C$, unless otherwise noted.

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS |
|-------------|----------------------------|---------------------|----------|----------------|-----|-----------|----------------|-----|------------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | |
| BW | Bandwidth | $G = 1$ | | 60 | | | | | kHz |
| | | $G = 10$ | | 30 | | | 25 | | kHz |
| | | $G = 100$ | | 3 | | | 12 | | kHz |
| | | $G = 1000$ | | 0.2 | | | 1.5 | | kHz |
| SR | Slew Rate | $V_{OUT} = \pm 10V$ | 0.012 | 0.026 | | 0.028 | 0.066 | | V/ μs |
| | Settling Time to 0.01% | 10V Step | | 460 | | | 270 | | μs |
| R_{REFIN} | Reference Input Resistance | | | 220 | | | 220 | | k Ω |
| I_{REFIN} | Reference Input Current | $V_{REF} = 0V$ | | 2.7 | | | 2.7 | | μA |
| AV_{REF} | Reference Gain to Output | | | 1 ± 0.0001 | | | 1 ± 0.0001 | | |

The ● denotes the specifications which apply over the temperature range of $0^\circ C \leq T_A \leq 70^\circ C$. $V_S = \pm 15V$, $R_L = 20k$, $V_{CM} = V_{REF} = 0V$, unless otherwise noted. (Note 4)

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS |
|-------------|-------------------------------------|--|----------|-------|------|-----------|-------|------|------------------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | |
| | Gain Error | $V_O = \pm 10V$ | | | | | | | |
| | | $G = 1$ | ● | | 0.15 | | | | % |
| | | $G = 10$ (Note 2) | ● | | 0.38 | | | 0.20 | % |
| | | $G = 100$ (Note 2) | ● | | 0.38 | | | 0.43 | % |
| | | $G = 1000$ (Note 2) | ● | | 0.43 | | | 0.48 | % |
| | Gain Nonlinearity | $V_O = \pm 10V$ | | | | | | | |
| | | $G = 1$ | ● | | 25 | | | | ppm |
| | | $G = 10$ | ● | | 15 | | | 45 | ppm |
| | | $G = 100$ | ● | | 25 | | | 45 | ppm |
| | | $G = 1000$ | ● | | 120 | | | 180 | ppm |
| G/T | Gain vs Temperature | $G < 1000$ (Notes 2, 3) | ● | 5 | 50 | | 5 | 50 | ppm/ $^\circ C$ |
| V_{OST} | Total Input Referred Offset Voltage | $V_{OST} = V_{OSI} + V_{OSO}/G$ | | | | | | | |
| V_{OSI} | Input Offset Voltage | $G = 1000$ | ● | | 285 | | | 325 | μV |
| V_{OSIH} | Input Offset Voltage Hysteresis | (Notes 3, 5) | ● | 8 | 30 | | 8 | 30 | μV |
| V_{OSO} | Output Offset Voltage | $G = 1$ | ● | | 1.2 | | | 4 | mV |
| V_{OSOH} | Output Offset Voltage Hysteresis | (Notes 3, 5) | ● | 50 | 120 | | 400 | 1000 | μV |
| V_{OSI}/T | Input Offset Voltage Drift (RTI) | (Note 3) | ● | 0.2 | 0.7 | | 0.3 | 0.8 | $\mu V/^\circ C$ |
| V_{OSO}/T | Output Offset Voltage Drift | (Note 3) | ● | 1.5 | 5 | | 8 | 22 | $\mu V/^\circ C$ |
| I_{OS} | Input Offset Current | | ● | | 4.5 | | | 4.5 | nA |
| I_{OS}/T | Input Offset Current Drift | | ● | 2 | | | 2 | | pA/ $^\circ C$ |
| I_B | Input Bias Current | | ● | | 45 | | | 45 | nA |
| I_B/T | Input Bias Current Drift | | ● | 35 | | | 35 | | pA/ $^\circ C$ |
| V_{CM} | Input Voltage Range | $G = 1$, Other Input Grounded | ● | -14.8 | 14 | | -14.8 | 14 | V |
| CMRR | Common Mode Rejection Ratio | 1k Source Imbalance, $V_{CM} = -14.8V$ to 14V | | | | | | | |
| | | $G = 1$ | ● | 78 | | | | | dB |
| | | $G = 10$ | ● | 96 | | | 91 | | dB |
| | | $G = 100, 1000$ | ● | 100 | | | 100 | | dB |

LT1789-1/LT1789-10

ELECTRICAL CHARACTERISTICS

The ● denotes the specifications which apply over the temperature range of $0^{\circ}\text{C} \leq T_A \leq 70^{\circ}\text{C}$. $V_S = \pm 15\text{V}$, $R_L = 20\text{k}$, $V_{CM} = V_{REF} = 0\text{V}$, unless otherwise noted. (Note 4)

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS |
|--------|------------------------------|---|-------------|------------------|------------|-------------|------------|------------------------|-------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | |
| PSRR | Power Supply Rejection Ratio | LT1789-1, $V_S = \pm 1.25\text{V}$ to $\pm 16\text{V}$ LT1789-10, $V_S = \pm 1.50\text{V}$ to $\pm 16\text{V}$ $G = 1$ ● $G = 10$ ● $G = 100, 1000$ ● | | 92 102 104 | | 98 104 | | dB dB dB | |
| | Minimum Supply Voltage | | | | ± 1.25 | | ± 1.50 | V | |
| I_S | Supply Current | | | | 150 | | 150 | μA | |
| V_O | Output Voltage Swing | | ± 14.25 | | | ± 14.25 | | V | |
| SR | Slew Rate | $V_{OUT} = \pm 10\text{V}$ | 0.010 | | | 0.026 | | $\text{V}/\mu\text{s}$ | |

The ● denotes the specifications which apply over the temperature range of $-40^{\circ}\text{C} \leq T_A \leq 85^{\circ}\text{C}$. $V_S = \pm 15\text{V}$, $R_L = 20\text{k}$, $V_{CM} = V_{REF} = 0\text{V}$, unless otherwise noted. (Note 4)

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS |
|-------------|-------------------------------------|--|----------|----------------|------------------------------|-----------|----------|----------------------|--------------------------------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | |
| | Gain Error | $V_O = \pm 10\text{V}$ $G = 1$ ● $G = 10$ (Note 2) ● $G = 100$ (Note 2) ● $G = 1000$ (Note 2) ● | | | 0.20 0.57 0.57 0.62 | | | 0.25 0.62 0.67 | % % % % |
| | Gain Nonlinearity | $V_O = \pm 10\text{V}$ $G = 1$ ● $G = 10$ ● $G = 100$ ● $G = 1000$ ● | | | 30 20 30 130 | | | 50 50 200 | ppm ppm ppm ppm |
| G/T | Gain vs Temperature | $G < 1000$ (Notes 2, 3) | | 5 | 50 | | 5 | 50 | $\text{ppm}/^{\circ}\text{C}$ |
| V_{OST} | Total Input Referred Offset Voltage | $V_{OST} = V_{OSI} + V_{OSO}/G$ | | | | | | | |
| V_{OSI} | Input Offset Voltage | $G = 1000$ | | | 305 | | | 340 | μV |
| V_{OSIH} | Input Offset Voltage Hysteresis | (Notes 3, 5) | | 8 | 30 | | 8 | 30 | μV |
| V_{OSO} | Output Offset Voltage | $G = 1$ | | | 1.3 | | | 4.2 | mV |
| V_{OSOH} | Output Offset Voltage Hysteresis | (Notes 3, 5) | | 50 | 120 | | 400 | 1000 | μV |
| V_{OSI}/T | Input Offset Voltage Drift (RTI) | (Note 3) | | 0.2 | 0.7 | | 0.3 | 0.8 | $\mu\text{V}/^{\circ}\text{C}$ |
| V_{OSO}/T | Output Offset Voltage Drift | (Note 3) | | 1.5 | 5 | | 8 | 22 | $\mu\text{V}/^{\circ}\text{C}$ |
| I_{OS} | Input Offset Current | | | | 5 | | | 5 | nA |
| I_{OS}/T | Input Offset Current Drift | | | 2 | | | 2 | | $\text{pA}/^{\circ}\text{C}$ |
| I_B | Input Bias Current | | | | 50 | | | 50 | nA |
| I_B/T | Input Bias Current Drift | | | 35 | | | 35 | | $\text{pA}/^{\circ}\text{C}$ |
| V_{CM} | Input Voltage Range | $G = 1$, Other Input Grounded | -14.8 | | 14 | -14.8 | | 14 | V |
| CMRR | Common Mode Rejection Ratio | 1k Source Imbalance, $V_{CM} = -14.8\text{V}$ to 14V $G = 1$ ● $G = 10$ ● $G = 100, 1000$ ● | | 76 94 98 | | | 89 98 | | dB dB dB |

ELECTRICAL CHARACTERISTICS

The ● denotes the specifications which apply over the temperature range of $-40^{\circ}\text{C} \leq T_A \leq 85^{\circ}\text{C}$. $V_S = \pm 15\text{V}$, $R_L = 20\text{k}$, $V_{\text{CM}} = V_{\text{REF}} = 0\text{V}$, unless otherwise noted. (Note 4)

| SYMBOL | PARAMETER | CONDITIONS | LT1789-1 | | | LT1789-10 | | | UNITS |
|--------|------------------------------|---|----------|-------------|------------|-------------|------------|------------------------|-------|
| | | | MIN | TYP | MAX | MIN | TYP | MAX | |
| PSRR | Power Supply Rejection Ratio | LT1789-1, $V_S = \pm 1.25\text{V}$ to $\pm 16\text{V}$ LT1789-10, $V_S = \pm 1.50\text{V}$ to $\pm 16\text{V}$ $G = 1$ $G = 10$ $G = 100, 1000$ | ● | 90 | | | | | dB |
| | | | ● | 100 | | 96 | | | dB |
| | | | ● | 102 | | 102 | | | dB |
| | | | | | | | | | |
| | Minimum Supply Voltage | | ● | | ± 1.25 | | ± 1.50 | V | |
| I_S | Supply Current | | ● | | 160 | | 160 | μA | |
| V_O | Output Voltage Swing | | ● | ± 14.15 | | ± 14.15 | | V | |
| SR | Slew Rate | $V_{\text{OUT}} = \pm 10\text{V}$ | ● | 0.008 | | 0.024 | | $\text{V}/\mu\text{s}$ | |

Note 1: Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. Exposure to any Absolute Maximum Rating condition for extended periods may affect device reliability and lifetime.

Note 2: Does not include the effect of the external gain resistor R_G .

Note 3: This parameter is not 100% tested.

Note 4: The LT1789C-1/ LT1789C-10 is guaranteed to meet specified performance from 0°C to 70°C and is designed, characterized and expected to meet these extended temperature limits, but is not tested at -40°C and 85°C . The LT1789I-1/ LT1789I-10 is guaranteed to meet the extended temperature limits.




Note 5: Hysteresis in offset voltage is created by package stress that differs depending on whether the IC was previously at a higher or lower temperature. Offset voltage hysteresis is always measured at 25°C , but the IC is cycled to 85°C I-grade (or 70°C C-grade) or -40°C I-grade (0°C C-grade) before successive measurement. 60% of the parts will pass the typical limit on the data sheet.

Note 6: $V_S = 5\text{V}$ limits are guaranteed by correlation to $V_S = 3\text{V}$ and $V_S = \pm 15\text{V}$ tests.

Note 7: $V_S = 3\text{V}$ limits are guaranteed by correlation to $V_S = 5\text{V}$ and $V_S = \pm 15\text{V}$ tests.


Note 8: This parameter is not tested at $V_S = 3\text{V}$ on the LT1789-10 due to an increase in sensitivity to test system noise. Actual performance is expected to be similar to performance at $V_S = 5\text{V}$.

TYPICAL PERFORMANCE CHARACTERISTICS (LT1789-1, LT1789-10)




TYPICAL PERFORMANCE CHARACTERISTICS (LT1789-1)

Output Voltage Swing vs Load Current




1789 G04

Gain vs Frequency




1789 G05

Slew Rate vs Temperature




1789 G06

Common Mode Rejection Ratio vs Frequency




1879 G07

Negative Power Supply Rejection Ratio vs Frequency




1789 G08

Positive Power Supply Rejection Ratio vs Frequency




1789 G09

Output Impedance vs Frequency




1789 G10

Overshoot vs Capacitive Load




1789 G11

Settling Time to 0.01% vs Output Step




1789 G12


TYPICAL PERFORMANCE CHARACTERISTICS (LT1789-1)




1789 G13




1789 G14




1789 G15



1789 G16




1789 G17



1789 G18


TYPICAL PERFORMANCE CHARACTERISTICS (LT1789-10)

Output Voltage Swing vs Load Current




1789 G21

Gain vs Frequency




1789 G22

Slew Rate vs Temperature




1789 G23

Common Mode Rejection Ratio vs Frequency




1789 G24

Negative Power Supply Rejection Ratio vs Frequency




1789 G25

Positive Power Supply Rejection Ratio vs Frequency




1789 G26

Output Impedance vs Frequency




1789 G27

Overshoot vs Capacitive Load



1789 G28


Settling Time to 0.01% vs Output Step



1789 G29


TYPICAL PERFORMANCE CHARACTERISTICS (LT1789-10)

Voltage Noise Density vs Frequency




1789 G30

Current Noise Density vs Frequency




1789 G31

0.1Hz to 10Hz Noise Voltage, RTI, G = 10




1789 G32

0.1Hz to 10Hz Noise Voltage, RTI, G = 1000




1789 G33

0.1Hz to 10Hz Noise Current



1789 G34


Turn-On Characteristics




1789 G59

TYPICAL PERFORMANCE CHARACTERISTICS (LT1789-1)


Large-Signal Transient Response
G = 1, 10, 100




Large-Signal Transient Response
G = 1000




Small-Signal Transient Response
G = 1




Small-Signal Transient Response
G = 10



Small-Signal Transient Response
G = 100




Small-Signal Transient Response
G = 1000




TYPICAL PERFORMANCE CHARACTERISTICS (LT1789-10)

Large-Signal Transient Response
G = 10, 100




$V_S = \pm 15V$
 $R_L = 20k$
 $C_L = 50pF$
 500µs/DIV
 1789 G44

Large-Signal Transient Response
G = 1000




$V_S = \pm 15V$
 $R_L = 20k$
 $C_L = 50pF$
 500µs/DIV
 1789 G45

Small-Signal Transient Response
G = 10




$V_S = 5V, 0V$
 $V_{REF} = 2.5V$
 $R_L = 20k$
 $C_L = 50pF$
 100µs/DIV
 1789 G46

Small-Signal Transient Response
G = 100



$V_S = 5V, 0V$
 $V_{REF} = 2.5V$
 $R_L = 20k$
 $C_L = 50pF$
 200µs/DIV
 1789 G47



Small-Signal Transient Response
G = 1000





$V_S = 5V, 0V$
 $V_{REF} = 2.5V$
 $R_L = 20k$
 $C_L = 50pF$
 2ms/DIV
 1789 G48

TYPICAL PERFORMANCE CHARACTERISTICS (LT1789-1)



Valid Output Voltage vs Input Common Mode Voltage
 $V_S = \pm 15V$





Valid Output Voltage vs Input Common Mode Voltage
 $V_S = \pm 2.5V$





Valid Output Voltage vs Input Common Mode Voltage
 $V_S = \pm 1.5V$



Valid Output Voltage vs Input Common Mode Voltage
 $V_S = 5V$





Valid Output Voltage vs Input Common Mode Voltage
 $V_S = 3V$





TYPICAL PERFORMANCE CHARACTERISTICS (LT1789-10)

Valid Output Voltage vs Input Common Mode Voltage
 $V_S = \pm 15V$





1789 G54

Valid Output Voltage vs Input Common Mode Voltage
 $V_S = \pm 2.5V$





1789 G55

Valid Output Voltage vs Input Common Mode Voltage
 $V_S = \pm 1.5V$





1789 G56

Valid Output Voltage vs Input Common Mode Voltage
 $V_S = 5V$



1789 G57

Valid Output Voltage vs Input Common Mode Voltage
 $V_S = 3V$



1789 G58

BLOCK DIAGRAM




Figure 1. Block Diagram

APPLICATIONS INFORMATION

Setting the Gain

The gain of the LT1789-1 and LT1789-10 is set by the value of resistor R_G , applied across pins 1 and 8. For the LT1789-1, the gain G will be:

$$G = 1 + 200k/R_G$$

and R_G can be calculated from the desired gain by

$$R_G = 200k/(G - 1)$$

For the LT1789-10, the gain G will be

$$G = 10 \cdot (1 + 200k/R_G)$$

and R_G can be calculated from the desired gain by

$$R_G = 200k/(0.1 \cdot G - 1)$$

For the lowest achievable gain, R_G may be set to infinity by leaving Pins 1 and 8 open.

Input and Output Offset Voltage

The offset voltage of the LT1789-1/LT1789-10 has two components: the output offset and the input offset. The total offset voltage referred to the input (RTI) is found by dividing the output offset by the programmed gain (G) and adding it to the input offset. At high gains the input offset voltage dominates, whereas at low gains the output offset voltage dominates. The total offset voltage is:

$$\text{Total input offset voltage (RTI)} = \text{input offset} + (\text{output offset}/G)$$

$$\text{Total output offset voltage (RTO)} = (\text{input offset} \cdot G) + \text{output offset}$$

APPLICATIONS INFORMATION

Reference Terminal

The output voltage of the LT1789-1/LT1789-10 (Pin 6) is referenced to the voltage on the reference terminal (Pin 5). Resistance in series with the REF pin must be minimized for best common mode rejection. For example, a 22Ω resistance from the REF pin to ground will not only increase the gain error by 0.02% but will lower the CMRR to 80dB.

Output Offset Trimming

The LT1789-1/LT1789-10 is laser trimmed for low offset voltage so that no external offset trimming is required for most applications. In the event that the offset needs to be adjusted, the circuit in Figure 2 is an example of an optional offset adjust circuit. The op amp buffer provides a low impedance to the REF pin where resistance must be kept to a minimum for best CMRR and lowest gain error.

Input Bias Current Return Path

The low input bias current of the LT1789-1/LT1789-10 (19nA) and the high input impedance (1.6GΩ) allow the use of high impedance sources without introducing significant offset voltage errors, even when the full common mode range is required. However, a path must be provided for the input bias currents of both inputs when a purely differential signal is being amplified. Without this path the inputs will float high and exceed the input common mode range of the LT1789-1/LT1789-10, resulting in a saturated input stage. Figure 3 shows three examples of an input bias current path. The first example is of a purely differential signal source with a 10kΩ input current path to ground. Since the impedance of the signal source is low, only one resistor is needed. Two matching resistors are needed for higher impedance signal sources as shown in the second example. Balancing the input impedance improves both common mode rejection and DC offset. The need for input resistors is eliminated if a center tap is present as shown in the third example.




Figure 2. Optional Trimming of Output Offset Voltage




Figure 3. Providing an Input Common Mode Current Path

APPLICATIONS INFORMATION

Output Voltage vs Input Common Mode Voltage

All instrumentation amplifiers have limiting factors that can cause an output to be invalid (the output is not equal to the input differential voltage multiplied by the gain) even though the output appears to be operating in a linear region. Limiting factors such as input voltage range and output swing can be easily measured, however, there are also internal nodes that can limit. These internal nodes cannot be measured externally and can lead to erroneous output readings.

To ensure a valid output for a given input common mode voltage and input differential voltage, the following four limiting factors must be taken into consideration (refer to the block diagram):

- 1) The input voltage ranges of the input amplifiers A1 and A2.
- 2) The output swings of the input amplifiers A1 and A2 (internal nodes).
- 3) The input voltage range of the output amplifier A3 (internal node).
- 4) The output swing of the output amplifier A3.

These limits can be determined using the relationships below.

- 1) The input voltage range limits can be found in the electrical tables.
- 2) The output voltages of the input amplifiers A1 and A2 can be found by the following formulas:

$$V_{OUT\ A1} = (V_D/2)(G)(R1/R2) + V_{CM} + 0.6V$$

$$V_{OUT\ A2} = (-V_D/2)(G)(R1/R2) + V_{CM} + 0.6V$$

Where V_D is the input differential voltage and V_{CM} is the input common mode voltage.

The typical output swing limits for A1 and A2 can be found in the Output Swing vs Load Current typical performance curve, using $R1 + R2$ as the load resistance.

This limitation usually becomes dominant when gain is taken in the input stage and the common mode input voltage is close to either supply rail.

The LT1789-10 is less susceptible to this limiting factor because the gain is taken in the output stage.

- 3) The voltage on the inputs to the output amplifier A3 can be determined by the following formula:

$$V_{IN\ A3} = (V_{OUT\ A1} - V_{REF})(R2/(R1 + R2))$$

The input voltage range of A3 has the same input limits as the LT1789-1. This limiting factor is more prevalent with single supplies, where both the reference voltage and input common mode voltage are near V^+ . This is also more of a concern with the LT1789-10 because the ratio of $R1:R2$ is 1:10 instead of 1:1.

- 4) The output voltage swing limits are also found in the electrical tables.

The Output Voltage vs Input Common Mode Voltage typical performance curves show the regions of operation for the three supply voltages specified.

Single Supply Operation


There are usually two types of input signals that need to be processed; differential signals, like the output of a bridge or single ended signals, such as the output from a thermistor. Both signals require special consideration when operating with a single supply.

When processing differential signals, REF (Pin 5) must be brought above the negative supply (Pin 4) to allow the output to process both the positive and negative going input signal. The maximum output operating range is obtained by setting the voltage on the REF pin to half supply. This must be done with a low impedance source to minimize CMRR and gain errors.

For single ended input signals, the REF pin can be at the same potential as the negative supply provided the output of the instrumentation amplifier remains inside the specified operating range. This maximizes the output range, however the smallest input signal that can be processed is limited by the output swing to the negative supply.


TYPICAL APPLICATIONS

Single Supply Positive Integrator



$V_S = 2.7V \text{ TO } 32V$
 TIME CONSTANT = $(R1)(C1) = 1 \text{ SECOND AS SHOWN}$





Avalanche Photo Diode Module Bias Current Monitor



- * = 0.1% METAL FILM RESISTOR
- 1µF 100V = TECATE CMC100105MX1825
- # CIRCLED NUMBERS = LTC1043 PIN NUMBER
- ➔ = 1N4148
- ⬆ = TP0610L

PACKAGE DESCRIPTION

S8 Package
8-Lead Plastic Small Outline (Narrow .150 Inch)
 (Reference LTC DWG # 05-08-1610)



- NOTE:
 1. DIMENSIONS IN INCHES (MILLIMETERS)
 2. DRAWING NOT TO SCALE
 3. THESE DIMENSIONS DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS. MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED .006" (0.15mm)


S08 0303

REVISION HISTORY (Revision history begins at Rev C)


| REV | DATE | DESCRIPTION | PAGE NUMBER |
|-----|------|--|-------------|
| C | 5/10 | Updated Input Noise Current Density Spec | 6 |

TYPICAL APPLICATION

Voltage Controlled Current Source



10°C to 40°C Thermometer



RELATED PARTS

| PART NUMBER | DESCRIPTION | COMMENTS |
|-----------------------|--|---|
| LTC1100 | Precision Chopper-Stabilized Instrumentation Amplifier | Best DC Accuracy |
| LT1101 | Precision, Micropower, Single Supply Instrumentation Amplifier | Fixed Gain of 10 or 100, $I_S < 105\mu\text{A}$ |
| LT1102 | High Speed, JFET Instrumentation Amplifier | Fixed Gain of 10 or 100, 30V/ μs Slew Rate |
| LT1167 | Single Resistor Gain Programmable, Precision Instrumentation Amplifier | Gain Error: 0.08% Max, Gain Nonlinearity: 10ppm Max, 60 μV Max Input Offset Voltage, 90dB Min CMRR |
| LT1168 | Low Power, Single Resistor Programmable Instrumentation Amplifier | $I_{SUPPLY} = 530\mu\text{A}$ Max |
| LTC [®] 1418 | 14-Bit, Low Power, 200ksps ADC with Serial and Parallel I/O | Single Supply 5V or $\pm 5V$ Operation, $\pm 1.5\text{LSB}$ INL and $\pm 1\text{LSB}$ DNL Max |
| LT1460 | Precision Series Reference | Micropower; 2.5V, 5V, 10V Versions; High Precision |
| LT1468 | 16-Bit Accurate Op Amp, Low Noise Fast Settling | 16-Bit Accuracy at Low and High Frequencies, 90MHz GBW, 22V/ μs , 900ns Settling |
| LTC1562 | Active RC Filter | Lowpass, Bandpass, Highpass Responses; Low Noise, Low Distortion, Four 2nd Order Filter Sections |
| LTC1605 | 16-Bit, 100ksps, Sampling ADC | Single 5V Supply, Bipolar Input Range: $\pm 10V$, Power Dissipation: 55mW Typ |