

# Dust Networks

ADDENDUM TO TEST REPORT 93690-13

**802.15.4 Wireless Mesh Mote**  
**Model: ETERNA1**

**Tested To The Following Standards:**

**ETSI EN 301 489-17 V2.1.1**

**Report No.: 93690-13A**

**Date of issue: December 12, 2012**



This test report bears the accreditation symbol indicating that the testing performed herein meets the test and reporting requirements of ISO/IEC 17025 under the applicable scope of EMC testing for CKC Laboratories, Inc.

We strive to create long-term, trust based relationships by providing sound, adaptive, customer first testing services. We embrace each of our customers' unique EMC challenges, not as an interruption to set processes, but rather as the reason we are in business.

## TABLE OF CONTENTS

Administrative Information .....	3
Test Report Information .....	3
Revision History .....	3
Report Authorization .....	3
Test Facility Information .....	4
Summary of Results .....	5
Conditions During Testing.....	5
Equipment Under Test.....	6
Peripheral Devices .....	6
ETSI EN 301 489-17 V2.1.1 .....	7
Conducted Emissions.....	7
Radiated Emissions .....	14
Harmonic Emissions.....	15
Voltage Fluctuation and Flicker Emissions.....	15
Immunity Performance Criteria Definitions .....	16
Immunity Setup and Monitoring .....	16
Radiated Immunity .....	17
Electrostatic Discharge .....	19
Electrical Fast Transients / Bursts .....	23
Transients and Surges in the Vehicle Environment .....	23
Conducted Immunity .....	24
Voltage Dips and Interrupts.....	24
Surge.....	24
Supplemental Information.....	25
Measurement Uncertainty .....	25
Emissions Test Details.....	25
Immunity Test Details.....	27

## ADMINISTRATIVE INFORMATION

### Test Report Information

**REPORT PREPARED FOR:**

Dust Networks  
30695 Huntwood Avenue  
Hayward, CA 94544

Representative: Gordon Charles  
Customer Reference Number: X9274F

**DATE OF EQUIPMENT RECEIPT:****DATE(S) OF TESTING:****REPORT PREPARED BY:**

Dianne Dudley  
CKC Laboratories, Inc.  
5046 Sierra Pines Drive  
Mariposa, CA 95338

Project Number: 93690

October 10, 2012

October 10-20, 2012

### Revision History

**Original:** Testing of THE 802.15.4 Wireless Mesh Mote, ETERNA1 to ETSI EN 301 489-17 V2.1.1.

**Addendum A:** To add correct frequency range for Radiated Immunity testing.

### Report Authorization

The test data contained in this report documents the observed testing parameters pertaining to and are relevant for only the sample equipment tested in the agreed upon operational mode(s) and configuration(s) as identified herein. Compliance assessment remains the client's responsibility. This report may not be used to claim product endorsement by A2LA or any government agencies. This test report has been authorized for release under quality control from CKC Laboratories, Inc.

A handwritten signature in black ink that reads "Steve Behm". The signature is written in a cursive style and is positioned above a horizontal line.

**Steve Behm**  
*Director of Quality Assurance & Engineering Services*  
*CKC Laboratories, Inc.*

## Test Facility Information



Our laboratories are configured to effectively test a wide variety of product types. CKC utilizes first class test equipment, anechoic chambers, data acquisition and information services to create accurate, repeatable and affordable test results.

TEST LOCATION(S):  
CKC Laboratories, Inc.  
110 Olinda Place  
Brea, CA 92823

## SUMMARY OF RESULTS

**Standard / Specification: ETSI EN 301 489-17 V2.1.1 / ETSI EN 301 489-1 V1.9.2**

Description	Test Procedure/Method	Results
Conducted Emissions	EN 301 489-17	Pass
Radiated Emissions	EN 301 489-17	NA
Harmonic Emissions	EN 61000-3-2 (2006) +A1	NA
Voltage Fluctuations and Flicker Emissions	EN 61000-3-3 (1995)	NA
Radiated Immunity	EN 61000-4-3 (2006)	Pass
Electrostatic Discharge	EN 61000-4-2 (2001)	Pass
Electrical Fast Transient Burst	EN 61000-4-4 (2004)	NA
Transients and Surges in the Vehicle Environment	ISO 7637-2 (2004)	NA
Conducted Immunity	EN 61000-4-6 (2005)	NA
Voltage Dips and Interrupts	EN 61000-4-11 (2004)	NA
Surge	EN 61000-4-5 (2006)	NA

NA = Not Applicable

## Conditions During Testing

This list is a summary of the conditions noted for or modifications made to the equipment during testing.

Summary of Conditions
None

## EQUIPMENT UNDER TEST

### EQUIPMENT UNDER TEST

#### 802.15.4 Wireless Mesh Mote

Manuf: Dust Networks

Model: ETERNA1

Serial: 000D67

### PERIPHERAL DEVICES

The EUT was tested with the following peripheral device(s):

#### Eterna Serial Programmer

Manuf: Dust Networks

Model: NA

Serial: NA

#### Laptop

Manuf: Lenovo

Model: X61

Serial: 7675CTO

## ETSI EN 301 489-17 V2.1.1

This report contains EMC emissions and immunity test results under European Union (CE) requirements.

### Conducted Emissions

Test Notes: Conducted Disturbances at Mains Terminals, LISN method.

#### Test Data Sheets

Test Location: CKC Laboratories, Inc. • 110 North Olinda Place • Brea, CA 92823 • 714-993-6112

Customer: **Dust Networks**

Specification: **EN 301 489-17 AC/DC Mains Input/Output - Average**

Work Order #: **93690**

Date: 10/10/2012

Test Type: **Conducted Emissions**

Time: 11:37:24

Equipment: **802.15.4 Wireless Mesh Mote**

Sequence#: 9

Manufacturer: Dust Networks

Tested By: E. Wong

Model: ETERNA1

230V 50Hz

S/N: 000D67

#### Test Equipment:

ID	Asset #	Description	Model	Calibration Date	Cal Due Date
	AN02869	Spectrum Analyzer	E4440A	2/12/2011	2/12/2013
T1	ANP01910	Cable	RG-142	2/6/2012	2/6/2014
T2	ANP06085	Attenuator	SA18N10W-09	12/8/2010	12/8/2012
T3	AN02343	High Pass Filter	HE9615-150K-50-720B	1/4/2011	1/4/2013
T4	AN02128	50uH LISN-L1 (dB)	3816/2NM	8/1/2011	8/1/2013
	AN02128	50uH LISN-L2 (dB)	3816/2NM	8/1/2011	8/1/2013

#### Equipment Under Test (\* = EUT):

Function	Manufacturer	Model #	S/N
802.15.4 Wireless Mesh Mote*	Dust Networks	ETERNA1	000D67

#### Support Devices:

Function	Manufacturer	Model #	S/N
Eterna Serial Programmer	Dust Networks	NA	NA
Laptop	Lenovo	X61	7675CTO

**Test Conditions / Notes:**

ETERNA1

The EUT seeking modular approval is installed atop a blank support PCB as intended. Placed on the test bench, the EUT is connected to a support laptop via a section of data cable and Serial Programmer. The Support laptop issues command to exercise the EUT, setting the EUT in continuous transmit mode.

Modulation: 802.15.4

Freq range: 2405-2475MHz

Freq: 2440MHz

Firmware power setting = 8dBm

Frequency range of measurement = 150kHz- 30MHz.

150 kHz-30 MHz; RBW=9 kHz, VBW=9kHz

Test environment conditions: 21°C, 52% relative humidity, 100kPa

Ext Attn: 0 dB

**Measurement Data:**

Reading listed by margin.


Test Lead: Black

#	Freq MHz	Rdng dBμV	T1 dB	T2 dB	T3 dB	T4 dB	Dist Table	Corr dBμV	Spec dBμV	Margin dB	Polar Ant
1	4.403M	38.7	+0.2	+5.7	+0.2	+0.1	+0.0	44.9	46.0	-1.1	Black
2	4.369M	38.7	+0.2	+5.7	+0.2	+0.1	+0.0	44.9	46.0	-1.1	Black
3	3.761M	38.6	+0.2	+5.7	+0.2	+0.1	+0.0	44.8	46.0	-1.2	Black
4	3.999M	27.5	+0.2	+5.7	+0.2	+0.1	+0.0	33.7	46.0	-12.3	Black
Ave											
^	3.999M	39.4	+0.2	+5.7	+0.2	+0.1	+0.0	45.6	46.0	-0.4	Black
6	3.880M	27.4	+0.2	+5.7	+0.2	+0.1	+0.0	33.6	46.0	-12.4	Black
Ave											
^	3.880M	39.8	+0.2	+5.7	+0.2	+0.1	+0.0	46.0	46.0	+0.0	Black
8	4.556M	26.3	+0.2	+5.7	+0.2	+0.1	+0.0	32.5	46.0	-13.5	Black
Ave											
^	4.556M	39.3	+0.2	+5.7	+0.2	+0.1	+0.0	45.5	46.0	-0.5	Black
10	4.437M	25.1	+0.2	+5.7	+0.2	+0.1	+0.0	31.3	46.0	-14.7	Black
Ave											
^	4.437M	39.9	+0.2	+5.7	+0.2	+0.1	+0.0	46.1	46.0	+0.1	Black
12	3.969M	20.8	+0.2	+5.7	+0.2	+0.1	+0.0	27.0	46.0	-19.0	Black
Ave											
^	3.969M	39.3	+0.2	+5.7	+0.2	+0.1	+0.0	45.5	46.0	-0.5	Black
14	3.909M	20.5	+0.2	+5.7	+0.2	+0.1	+0.0	26.7	46.0	-19.3	Black
Ave											
^	3.909M	39.4	+0.2	+5.7	+0.2	+0.1	+0.0	45.6	46.0	-0.4	Black
16	4.028M	19.3	+0.2	+5.7	+0.2	+0.1	+0.0	25.5	46.0	-20.5	Black
Ave											



^	4.028M	39.1	+0.2	+5.7	+0.2	+0.1	+0.0	45.3	46.0	-0.7	Black
18	3.850M	17.5	+0.2	+5.7	+0.2	+0.1	+0.0	23.7	46.0	-22.3	Black
Ave											
^	3.850M	39.7	+0.2	+5.7	+0.2	+0.1	+0.0	45.9	46.0	-0.1	Black
20	4.530M	17.4	+0.2	+5.7	+0.2	+0.1	+0.0	23.6	46.0	-22.4	Black
Ave											
^	4.530M	40.0	+0.2	+5.7	+0.2	+0.1	+0.0	46.2	46.0	+0.2	Black
22	4.462M	17.1	+0.2	+5.7	+0.2	+0.1	+0.0	23.3	46.0	-22.7	Black
Ave											
^	4.462M	39.1	+0.2	+5.7	+0.2	+0.1	+0.0	45.3	46.0	-0.7	Black

Date: 10/10/2012 Time: 11:37:24 Dust Networks WO#: 93690  
EN 301 489-17 AC/DC Mains Input/Output - Average Test Lead: Black 230V 50Hz Sequence#: 9 Ext ATTN: 0 dB



- Sweep Data
- Readings
- Peak Readings
- × QP Readings
- \* Average Readings
- ▼ Ambient
- 1 - EN 301 489-17 AC/DC Mains Input/Output - Average
- 2 - EN 301 489-17 AC/DC Mains Input/Output - Quasi-peak

Test Location: CKC Laboratories, Inc. • 110 North Olinda Place • Brea, CA 92823 • 714-993-6112

Customer: **Dust Networks**  
 Specification: **EN 301 489-17 AC/DC Mains Input/Output - Average**  
 Work Order #: **93690** Date: 10/10/2012  
 Test Type: **Conducted Emissions** Time: 11:27:22  
 Equipment: **802.15.4 Wireless Mesh Mote** Sequence#: 8  
 Manufacturer: Dust Networks Tested By: E. Wong  
 Model: ETERNA1 230V 50Hz  
 S/N: 000D67

**Test Equipment:**

ID	Asset #	Description	Model	Calibration Date	Cal Due Date
	AN02869	Spectrum Analyzer	E4440A	2/12/2011	2/12/2013
T1	ANP01910	Cable	RG-142	2/6/2012	2/6/2014
T2	ANP06085	Attenuator	SA18N10W-09	12/8/2010	12/8/2012
T3	AN02343	High Pass Filter	HE9615-150K-50-720B	1/4/2011	1/4/2013
	AN02128	50uH LISN-L1 (dB)	3816/2NM	8/1/2011	8/1/2013
T4	AN02128	50uH LISN-L2 (dB)	3816/2NM	8/1/2011	8/1/2013

**Equipment Under Test (\* = EUT):**

Function	Manufacturer	Model #	S/N
802.15.4 Wireless Mesh Mote*	Dust Networks	ETERNA1	000D67

**Support Devices:**

Function	Manufacturer	Model #	S/N
Eterna Serial Programmer	Dust Networks	NA	NA
Laptop	Lenovo	X61	7675CTO

**Test Conditions / Notes:**

ETERNA1  
 The EUT seeking modular approval is installed atop a blank support PCB as intended. Placed on the test bench, the EUT is connected to a support laptop via a section of data cable and Serial Programmer. The Support laptop issues command to exercise the EUT, setting the EUT in continuous transmit mode.

Modulation: 802.15.4  
 Freq range: 2405-2475MHz

Freq: 2440MHz  
 Firmware power setting = 8dBm

Frequency range of measurement = 150kHz- 30MHz.  
 150 kHz-30 MHz; RBW=9 kHz, VBW=9kHz

Test environment conditions: 21°C, 52% relative humidity, 100kPa

Ext Attn: 0 dB

**Measurement Data:**


Reading listed by margin.

Test Lead: White

#	Freq MHz	Rdng dB $\mu$ V	T1 dB	T2 dB	T3 dB	T4 dB	Dist Table	Corr dB $\mu$ V	Spec dB $\mu$ V	Margin dB	Polar Ant
1	4.573M	39.1	+0.2	+5.7	+0.2	+0.2	+0.0	45.4	46.0	-0.6	White
2	4.535M	38.8	+0.2	+5.7	+0.2	+0.2	+0.0	45.1	46.0	-0.9	White
3	4.250M	38.7	+0.2	+5.7	+0.2	+0.2	+0.0	45.0	46.0	-1.0	White
4	187.460k Ave	40.2	+0.1	+5.7	+0.2	+0.0	+0.0	46.2	54.1	-7.9	White
5	4.003M Ave	26.3	+0.2	+5.7	+0.2	+0.2	+0.0	32.6	46.0	-13.4	White
^	4.003M	39.3	+0.2	+5.7	+0.2	+0.2	+0.0	45.6	46.0	-0.4	White
7	3.977M Ave	20.3	+0.2	+5.7	+0.2	+0.2	+0.0	26.6	46.0	-19.4	White
8	3.952M Ave	18.4	+0.2	+5.7	+0.2	+0.2	+0.0	24.7	46.0	-21.3	White
^	3.952M	40.1	+0.2	+5.7	+0.2	+0.2	+0.0	46.4	46.0	+0.4	White
10	3.977M Ave	17.4	+0.2	+5.7	+0.2	+0.2	+0.0	23.7	46.0	-22.3	White
^	3.977M	40.1	+0.2	+5.7	+0.2	+0.2	+0.0	46.4	46.0	+0.4	White
12	3.901M Ave	15.8	+0.2	+5.7	+0.2	+0.2	+0.0	22.1	46.0	-23.9	White
^	3.901M	40.1	+0.2	+5.7	+0.2	+0.2	+0.0	46.4	46.0	+0.4	White
14	3.837M Ave	13.9	+0.2	+5.7	+0.2	+0.2	+0.0	20.2	46.0	-25.8	White
^	3.837M	40.3	+0.2	+5.7	+0.2	+0.2	+0.0	46.6	46.0	+0.6	White
16	3.769M Ave	13.4	+0.2	+5.7	+0.2	+0.2	+0.0	19.7	46.0	-26.3	White
^	3.769M	39.3	+0.2	+5.7	+0.2	+0.2	+0.0	45.6	46.0	-0.4	White
18	4.394M Ave	13.1	+0.2	+5.7	+0.2	+0.2	+0.0	19.4	46.0	-26.6	White
^	4.394M	39.3	+0.2	+5.7	+0.2	+0.2	+0.0	45.6	46.0	-0.4	White
20	4.513M Ave	12.9	+0.2	+5.7	+0.2	+0.2	+0.0	19.2	46.0	-26.8	White
^	4.513M	39.9	+0.2	+5.7	+0.2	+0.2	+0.0	46.2	46.0	+0.2	White
22	194.360k Ave	18.0	+0.1	+5.7	+0.2	+0.0	+0.0	24.0	53.8	-29.8	White
^	194.360k	47.8	+0.1	+5.7	+0.2	+0.0	+0.0	53.8	53.8	+0.0	White


24	199.450k	17.8	+0.1	+5.7	+0.1	+0.0	+0.0	23.7	53.6	-29.9	White
Ave											
^	199.450k	47.1	+0.1	+5.7	+0.1	+0.0	+0.0	53.0	53.6	-0.6	White

Date: 10/10/2012 Time: 11:27:22 Dust Networks WO#: 93690  
EN 301 489-17 AC/DC Mains Input/Output - Average Test Lead: White 230V 50Hz Sequence#: 8 Ext ATTN: 0 dB



- Sweep Data
- Readings
- Peak Readings
- × QP Readings
- \* Average Readings
- ▼ Ambient
- 1 - EN 301 489-17 AC/DC Mains Input/Output - Average
- 2 - EN 301 489-17 AC/DC Mains Input/Output - Quasi-peak

**Test Setup Photos**



## Radiated Emissions

Test Notes: Radiated disturbances emanating from enclosure.

Test Engineer:	E. Wong	Test Procedure:	ETSI EN 301 489-17
Test Level:	NA		
Declarations:			
8.2 Enclosure of ancillary equipment measured on a stand-alone basis. This test is only applicable to ancillary equipment not incorporated in the radio equipment and intended to be measured on a stand-alone basis, as declared by the manufacturer. This test shall be performed on a representative configuration of the ancillary equipment. This test is not applicable for ancillary equipment incorporated in the radio equipment, or for ancillary equipment intended to be measured in combination with the radio equipment. In these cases the requirements of the relevant product standard for the effective use of the radio spectrum shall apply. Product related conditions for combined testing of radio and ancillary equipment may be contained in the relevant part of EN 301 489 series [11] dealing with the particular type of radio equipment.			

## Harmonic Emissions

Test Notes: Conducted disturbances of current harmonics emanating from equipment power supply to low-voltage public power networks.

Test Engineer:	E. Wong	Test Procedure:	EN 61000-3-2
Test Level:	NA		
Declarations: The manufacturer declares the device is a module.			

## Voltage Fluctuation and Flicker Emissions

Test Notes: Conducted disturbances of voltage fluctuations and flicker emanating from equipment power supply to low-voltage public power networks.

Test Engineer:	E. Wong	Test Procedure:	EN 61000-3-3
Test Level:	NA		
Declarations: The manufacturer declares the device is a module.			

## Immunity Performance Criteria Definitions

Designation	Definition
Standard / Mfg.	Standard Requirement / Manufacturer's Declaration
A	The EUT shall operate without degradation of performance during and after the application of disturbance.
B	After the disturbance is removed, normal operation of the EUT is self-recoverable.
C	After the disturbance is removed, normal operation of the EUT can be restored by the operator.

## Immunity Setup and Monitoring

**Equipment Setup:** Three modules, ETERNA1, ETERNA2 and ETERNA2 with integral antenna are place on the test bench. The communication scheme is established, transmitting and receive to/from a support Manager and laptop at a predetermined time interval minimum of 15 sec seconds.

Standby mode: Another set of ETERNA 1, ETERNA2 and ETERNA2 with integral antenna are place on the test bench and connected to a dedicated transmit antenna. The EUTs are placed in standby mode, command: radio test on, waiting for a transmit command.

**Degradation Criteria:** Transmit mode: Lost of communication upon query from the manager.

Standby mode: Unintentional transmit as observed from the monitoring spectrum analyzer.

**Monitoring:** Transmit mode: Visual inspection of ping status on the support computer.

Stand-by mode: Spectrum analyzer with trace in Max hold tuned to 2.4 – 2.485 GHz. and a horn antenna connected to the spectrum analyzer.



## Radiated Immunity

<b>Test Engineer:</b>	E. Wong	<b>Test Procedure:</b>	EN 61000-4-3
<b>Test Level:</b>	80MHz to 1GHz and 1.4-2.7GHz (except exclusion band, if applicable), 3V/m @ 80% AM 1kHz		
<b>Declarations:</b>			

Test Equipment					
Asset #	Description	Manufacturer	Model	Cal Date	Cal Due
BC 61000 4 3	Chamber Cal	CKC	Brea	1/27/2011	1/27/2013
01370	BiLog Antenna	EMCO	3143	NCR	NCR
00627	Amplifier	AR	50W1000A	1/6/2011	1/6/2013
01612	Directional Coupler	Werlatone	C2630	10/12/2011	10/12/2013
05301	Directional Coupler 1-4GHz	ATM	C223E-20	7/27/2012	7/27/2014
02467	Spectrum Analyzer	E7405A	Agilent	4/5/2011	4/5/2013
02227	Signal Generator	2024	Marconi	7/6/2011	7/6/2013
00638	Field Probe	FP2000	AR	8/11/2011	8/11/2013
00636	Field Monitor	FM2000	AR	8/11/2011	8/11/2013
P04270	Cable	Hardline	Andrew	NCR	NCR
P04286	Cable	Hardline	Andrew	NCR	NCR
02710	Anechoic Chamber	NA	LM	1/27/2011	1/27/2013
02551	Signal Generator	HP	8673M	4/27/2011	4/27/2013
02043	Field Probe	AR	FP2080	12/16/2011	12/16/2013
02688	Amplifier	Ophir	5161F	10/11/2012	10/11/2014
00849	Horn Antenna	EMCO	3115	4/13/2012	4/13/2014
00838	Function Generator	HP	33120A	2/23/2011	2/23/2013


NCR = No Calibration Required.

Radiated Immunity Results		
Surface Tested	Test Results	Test Observations
Front	No degradation	
Back	No degradation	
Left Side	No degradation	
Right Side	No degradation	

Test Distance: 80-1000= 1.5 meters and 1.4-2.7GHz = 2.0 meters.

For this test, the EUT met performance criteria: CT/CR A

**Test Setup Photos**



TX



STANDBY

## Electrostatic Discharge

Test Engineer:	E. Wong	Test Procedure:	EN 61000-4-2
Test Level:	Contact: 4kV Air: 2, 4 and 8kV		
Declarations:			

<b>Temperature:</b>	23.4	°C
<b>Relative Humidity:</b>	51	%
<b>Atmospheric Pressure:</b>	100.8	kPa

## Test Equipment

Asset #	Description	Manufacturer	Model	Cal Date	Cal Due
01650	ESD Simulator	KeyTek	MZ-15/ec	12/18/2010	12/18/2012

## ESD Contact Discharge Results

Surface Tested	Test Results	Test Observations
Horizontal Coupling Plane	No degradation	
Vertical Coupling Plane	No degradation	
Front	NA	Non-conductive surfaces.
Back	NA	Non-conductive surfaces.
Left Side	NA	Non-conductive surfaces.
Right Side	NA	Non-conductive surfaces.
Top	NA	Non-conductive surfaces.
Bottom	NA	Non-conductive surfaces.

## ESD Air Discharge Results


Surface Tested	Test Results	Test Observations
Front	No discharge	No discharge at the removable antenna.
Back	NA	Device is a module
Left Side	NA	Device is a module
Right Side	NA	Device is a module
Top	NA	Device is a module
Bottom	NA	Device is a module

For this test, the EUT met performance criteria: TT/ TR A


**Test Setup Photos**



TX VIEW # 1



TX VIEW #2




TX VIEW # 3




STANDBY VIEW # 1





STANDBY VIEW # 2



STANDBY VIEW # 3

## Electrical Fast Transients / Bursts – AC/DC Mains Power Lines

<b>Test Engineer:</b>	E. Wong	<b>Test Procedure:</b>	EN 61000-4-4
<b>Test Level:</b>	AC Mains: NA DC Mains: NA		
<b>Declarations:</b> AC Mains: The manufacturer declares that the EUT is a module. DC Mains: The manufacturer declares that the EUT is a module.			

## Electrical Fast Transients / Bursts - IO Lines

<b>Test Engineer:</b>	E. Wong	<b>Test Procedure:</b>	EN 61000-4-4
<b>Test Level:</b>	IO Lines: NA		
<b>Declarations:</b> IO Lines: The manufacturer declares that the EUT is a module.			

## Transients and Surges in the Vehicle Environment – 12/24VDC Supply

<b>Test Engineer:</b>	E. Wong	<b>Test Procedure:</b>	ISO 7637-2 (2004)
<b>Test Level:</b>	NA		
<b>Declarations:</b> NA = Not Applicable because this test is only required for units that will be used in a vehicular environment.			

## Conducted Immunity

<b>Test Engineer:</b>	E. Wong	<b>Test Procedure:</b>	EN 61000-4-6
<b>Test Level:</b>	AC Mains: NA DC Mains: NA IO Lines: NA		
Declarations: AC Mains: The manufacturer declares that the EUT is a module. DC Mains: The manufacturer declares that the EUT is a module. IO Lines: The manufacturer declares that the EUT is a module.			

## Voltage Dips and Interrupts

<b>Test Engineer:</b>	E. Wong	<b>Test Procedure:</b>	EN 61000-4-11
<b>Test Level:</b>	NA		
<b>Declarations:</b> The manufacturer declares that the EUT is a module.			

## Surge

<b>Test Engineer:</b>	E. Wong	<b>Test Procedure:</b>	EN 61000-4-5
<b>Test Level:</b>	AC Mains: NA DC Mains: NA		
<b>Declarations:</b> AC Mains: The manufacturer declares that the EUT is a module. DC Mains: The manufacturer declares that the EUT is a module.			

## Surge IO Lines

<b>Test Engineer:</b>	E. Wong	<b>Test Procedure:</b>	EN 61000-4-5
<b>Test Level:</b>	IO Lines: NA		
<b>Declarations:</b> IO Lines: The manufacturer declares that the EUT is a module.			



## SUPPLEMENTAL INFORMATION

### Measurement Uncertainty

Uncertainty Value	Parameter
4.73 dB	Radiated Emissions
3.34 dB	Mains Conducted Emissions
3.30 dB	Disturbance Power

The reported measurement uncertainties are calculated based on the worst case of all laboratory environments from CKC Laboratories, Inc. test sites. Only those parameters which require estimation of measurement uncertainty are reported. The reported worst case measurement uncertainty is less than the maximum values derived in CISPR 16-4-2. Reported uncertainties represent expanded uncertainties expressed at approximately the 95% confidence level using a coverage factor of  $k=2$ . Compliance is deemed to occur provided measurements are below the specified limits.

### Emissions Test Details

#### TESTING PARAMETERS

Unless otherwise indicated, the following configuration parameters are used for equipment setup: The cables were routed consistent with the typical application by varying the configuration of the test sample. Interface cables were connected to the available ports of the test unit. The effect of varying the position of the cables was investigated to find the configuration that produced maximum emissions. Cables were of the type and length specified in the individual requirements. The length of cable that produced maximum emissions was selected.

The equipment under test (EUT) was set up in a manner that represented its normal use, as shown in the setup photographs. Any special conditions required for the EUT to operate normally are identified in the comments that accompany the emissions tables.

The emissions data was taken with a spectrum analyzer or receiver. Incorporating the applicable correction factors for distance, antenna, cable loss and amplifier gain, the data was reduced as shown in the table below. The corrected data was then compared to the applicable emission limits. Preliminary and final measurements were taken in order to ensure that all emissions from the EUT were found and maximized.

#### CORRECTION FACTORS

The basic spectrum analyzer reading was converted using correction factors as shown in the highest emissions readings in the tables. For radiated emissions in dB $\mu$ V/m, the spectrum analyzer reading in dB $\mu$ V was corrected by using the following formula. This reading was then compared to the applicable specification limit.

SAMPLE CALCULATIONS		
	Meter reading	(dBμV)
+	Antenna Factor	(dB)
+	Cable Loss	(dB)
-	Distance Correction	(dB)
-	Preamplifier Gain	(dB)
=	Corrected Reading	(dBμV/m)

#### TEST INSTRUMENTATION AND ANALYZER SETTINGS

The test instrumentation and equipment listed were used to collect the emissions data. A spectrum analyzer or receiver was used for all measurements. Unless otherwise specified, the following table shows the measuring equipment bandwidth settings that were used in designated frequency bands. For testing emissions, an appropriate reference level and a vertical scale size of 10 dB per division were used.

MEASURING EQUIPMENT BANDWIDTH SETTINGS PER FREQUENCY RANGE			
TEST	BEGINNING FREQUENCY	ENDING FREQUENCY	BANDWIDTH SETTING
CONDUCTED EMISSIONS	150 kHz	30 MHz	9 kHz
RADIATED EMISSIONS	30 MHz	1000 MHz	120 kHz
RADIATED EMISSIONS	1000 MHz	>1 GHz	1 MHz

#### SPECTRUM ANALYZER/RECEIVER DETECTOR FUNCTIONS

The notes that accompany the measurements contained in the emissions tables indicate the type of detector function used to obtain the given readings. Unless otherwise noted, all readings were made in the "positive peak" detector mode. Whenever a "quasi-peak" or "average" reading was recorded, the measurement was annotated with a "QP" or an "Ave" on the appropriate rows of the data sheets. In cases where quasi-peak or average limits were employed and data exists for multiple measurement types for the same frequency then the peak measurement was retained in the report for reference, however the numbering for the affected row was removed and an arrow or carrot ("^") was placed in the far left-hand column indicating that the row above takes precedence for comparison to the limit. The following paragraphs describe in more detail the detector functions and when they were used to obtain the emissions data.

##### Peak

In this mode, the spectrum analyzer or receiver recorded all emissions at their peak value as the frequency band selected was scanned. By combining this function with another feature called "peak hold," the measurement device had the ability to measure intermittent or low duty cycle transient emission peak levels. In this mode the measuring device made a slow scan across the frequency band selected and measured the peak emission value found at each frequency across the band.

##### Quasi-Peak

Quasi-peak measurements were taken using the quasi-peak detector when the true peak values exceeded or were within 2 dB of a quasi-peak specification limit. Additional QP measurements may have been taken at the discretion of the operator.

##### Average

Average measurements were taken using the average detector when the true peak values exceeded or were within 2 dB of an average specification limit. Additional average measurements may have been taken at the discretion of the operator. If the specification or test procedure requires trace averaging, then the averaging was performed using 100 samples or as required by the specification. All other average measurements are performed using video bandwidth averaging. To make these measurements, the test engineer reduces the video bandwidth on the measuring device until the modulation of the signal is filtered out. At this point the measuring device is set into the linear mode and the scan time is reduced.

## Immunity Test Details

### EN 61000-4-3 Field Intensity at 0.4m

Chamber (80-1000)	1V/m Testing	3V/m Testing	10V/m Testing	20V/m Testing	30V/m Testing
Fremont C1	0.7	2.8	8.2	NA	NA
Fremont C2	0.6	2.5	9.1	10.3	NA
Mariposa	1.9	6.2	19.4	NA	NA
Brea	1.0	3.0	17.4	NA	NA
Bothell C1	0.7	3.1	10.4	22.3	31.2
Bothell C2	1.1	3.3	11.9	NA	NA

NA = Not applicable because these levels are not performed in this chamber.